

Thread boring bars, internal, right

for holding thread turning inserts for internal machining

ATORN®

Application


For female thread machining for thread turning inserts.

Version

- precision-engineered steel support, burnished and hardened, with 1.5° pitch angle

Advantage

- top-quality and wear-resistant steel support with high-strength clamping screw
- precision-engineered insert seat provides extremely precise threads and excellent finish quality



Art. No.	17747 134
ISO name	SIR/L 0013 L11
Suitable for indexable insert size	11
Min. bore diameter	15 mm
Cutting edge diameter	13 mm
Shaft diameter	16 mm
Length	140 mm
Programming size	8.9 mm
Immersion depth	32 mm
Coolant supply	External
Tool design	Right

EAN-Code

4050293209259