

Scissor-type lifting platform with double scissors

Fixed sliding handle, sturdy variant

fetra
Transportgeräte

Execution:

- Profile steel/sheet steel construction
- Strong tubular push handle, firmly screwed-in
- Hydraulic pump with chrome-plated piston
- Actuated by foot pedal
- Use the hand lever to actuate the lowering valve sensitively
- 2 castors and 2 fixed castors, polyurethane tyre wheels, steering wheels with locking device
- Double scissor arms for particularly large lifting range
- Powder-coated, anthracite RAL 7016



Art. no.	50262 919
Brand	FETRA
Manufacturer Part Number	6837
Load-carrying capacity	500 kg
Min. table height	440 mm
Max. table height	1575 mm
Loading surface length	1010 mm
Loading-surface width	520 mm
Wheel diameter	150 mm
Material of wheel	Polyurethane
Length	1275 mm
Width	520 mm
Total stop optional	No
Gross Weight	168.000 kg
Product Group	5AE

EAN

4017976068374