

F204 A-63/0,03



Products Low Voltage Products and Systems Modular DIN Rail Products Residual Current Devices RCDs
Residual Current Devices RCDs

General Information

Extended Product Type:	F204 A-63/0,03
Product ID:	2CSF204101R1630
EAN:	8012542783602
Catalog Description:	F204 A-63/0,03 Residual Current Dev.
Long Description:	The RCCBs F200 series assures protection to people and installations against fault current to earth. A large offer for standard instantaneous and selective AC and A types is completed with some configurations for special applications.

Additional Information

Country of Origin:	Italy (IT)
Customs Tariff Number:	85389099
Data Sheet, Technical Information:	2CSC400002D0209
Declaration of Conformity - CE:	2CSC423001D2701
E-nummer:	2160127
EAN:	8012542783602
EPLAN Catalog Tree:	Electrical engineering / Protection devices / Ground fault current circuit breaker
EPLAN Function Definition:	Ground fault current circuit-breaker / Ground fault current circuit breakers, 8 connection points / Ground fault current circuit breaker, four-pole 1 2 3 4 5 6 7 8
ETIM 4:	EC000003 - Residual current circuit breaker (RCCB)
ETIM 5:	EC000003 - Residual current circuit breaker (RCCB)
ETIM 6:	EC000003 - Residual current circuit breaker (RCCB)
Environmental Information:	S-P-00081
Instructions and Manuals:	2CSF423001D6402
Invoice Description:	F204 A-63/0,03 Residual Current Dev.
Maximum Operating Voltage UL/CSA:	480Y/277 V AC
Minimum Order Quantity:	1 piece
Number of Poles:	4
Object Classification Code:	Q
Operating Characteristic:	Instantaneous
Options Provided:	-
Package Level 1 EAN:	8012542783602
Package Level 1 Gross Weight:	0.403 kg
Package Level 1 Height:	0.078 m
Package Level 1 Length:	0.096 m
Package Level 1 Units:	1 piece
Package Level 1 Width:	0.082 m
Position of Neutral Terminals:	Right
Power Loss:	at Rated Operating Conditions per Pole 4.4 W
Product Main Type:	F200
Product Name:	Residual Current Device
Product Net Depth:	0.069 m
Product Net Height:	0.085 m
Product Net Weight:	0.360 kg
Product Net Width:	0.070 m
Rated Current (I_n):	63 A

Rated Frequency (f):	50 ... 60 Hz
Rated Operational Voltage:	230 / 400 V AC
Rated Residual Current:	30 mA
Rated Voltage (U_r):	230/400 V
RoHS Information:	2CSC423001K0201
RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q3
Selling Unit of Measure:	piece
Short Description:	Residual Current Device F204 A-63/0,03
Standards:	IEC/EN 61008 UL 1053
Type of Residual Current:	A type
Accessories Available:	Yes

