

Product type designation

Product description

PROFIBUS bus connector, RS485, screw, without PG socket, 90°
 PROFIBUS bus connector, RS485, screw, without PG socket, 90°
 SIMATIC DP, BUS CONNECTOR FOR PROFIBUS UP TO 12
 MBIT/S 90 DEGREE ANGLE OUTGOING CABLE, 15,8 X 64 X 35,6
 MM (WXHXD), TERMINAT. RESIST. WITH ISOLAT. FUNCTION,
 WITHOUT PG SOCKET



Suitability for use

For connecting PROFIBUS nodes to the PROFIBUS bus cable

Transmission rate

Transfer rate / with PROFIBUS DP

9.6 kbit/s ... 12 Mbit/s

Interfaces

Number of electrical connections

- for PROFIBUS cables
- for network components or terminal equipment

2

1

Type of electrical connection

- for PROFIBUS cables
- for network components or terminal equipment

Screw

Sub-D connector (9-pin)

Mechanical data

Design of terminating resistor

Integrated resistor combination that can be selected with slide switch

Material / of the enclosure

plastic

Design, dimensions and weight

Type of cable outlet

90° cable outlet

Width

15.8 mm

Height

64 mm

Depth

35.6 mm

Net weight

10 g

Permitted ambient conditions

Ambient temperature

• during storage	-40 ... +70 °C
• during transport	-40 ... +70 °C
Protection class IP	IP20

Product properties, functions, components / general

Product property	
• silicon-free	Yes
Product component	
• PG connection socket	No
• strain relief	Yes

Standards, specifications, approvals

Certificate of suitability	
• RoHS conformity	Yes
• UL approval	Yes

last modified: 09.03.2015