

## Thread turning inserts, full profile, 60°, HC56 15

for male thread machining, right

**ATORN®**

### Application


For creating male threads on CNC machines for the material groups of steel, stainless steel, non-ferrous metal and cast iron at low to medium cutting speeds.

### Version

- ground thread turning insert with TiN coating

### Advantage

- ground thread turning insert, ensures good finish quality, cutting precision and thread with precise profile replication
- wide range of applications thanks to TiN coating
- high level of productivity and no need to deburr the thread



<b>Art. no.</b>	<b>17741 248</b>
<b>ISO name</b>	11 (ER/EL) 1.75 ISO
<b>Pitch</b>	1.75 mm
<b>Machining direction</b>	Right
<b>Carbide type</b>	HC56 15
<b>Material to be processed</b>	Steel, Stainless steel, Non-ferrous metal, Cast metal
<b>Min./max. Vc in steel</b>	75-110 m/min
<b>Min./max. Vc in stainless steel</b>	70-75 m/min
<b>Min./max. Vc in non-ferrous metals</b>	200-600 m/min
<b>Min./max. Vc in cast iron</b>	70-80 m/min

### EAN-Code

4050293216653

