

Micrometer

With 60° V-anvil and tapered spindle tip

Mitutoyo

Application:

For measuring e.g. Screw thread

Execution:

- Semi-gloss chrome-plated scale drum and sleeve
- Friction coupling for consistent, repeatable measuring force

Delivery:

Includes box, setting standard 60° (over 25 mm), adjustment wrench



Art. no.	32016 670
Brand	MITUTOYO
Manufacturer Part Number	125-111
Min./max. length measuring range	50-75 mm
Vernier scale	0.01 mm
Bracket depth	49 mm
Display	Nonius
Type	Measurable thread type 0.6-0.9 mm/44-28 TPI
Number of setting dimensions	1 PCS
Calibration Group	D
Gross Weight	0.445 kg
Product Group	3MA

EAN

4946368014319