

2.92mm (SMK) Series Adapters & Connectors Catalog







belfuse.com/cinch

Index

Specifications		 				
Connectors						
End Launch 2 Hole Flange 4 Hole Flange Field Replaceable Other	· · · · · · · · · · · · · · · · · · ·	 	· · · · · · · · · · · · · · · · · · ·	· · · · · · · · · · · · · · · · · · ·	· · · · · · · · · · · · · · · · · · ·	
Adapters Same Series Between Series		 				
Assembly Instructio	ons	 				 12 13

2.92mm Series



The Johnson[™] 2.92mm Series Connector provides an excellent solution for demanding applications requiring high frequency transmission. Although similar to the SMA interface, a smaller internal body diameter (2.92mm) and air dielectric provide a higher cutoff frequency and other key advantages:

- Precision manufacturing allows superior electrical performance to 40 GHz.
- Female contacts have a unique three-slot construction, which enhances connectivity by creating a more rugged connector while reducing the chance of intermittent connections.
- Precise assembly tooling assures excellent, repeatable contact and support bead location on cabled connectors.
- Connector mating interface per MIL-STD-348.
- Mating interface control provides consistent electrical performance.
- The plug connector VSWR is 1.20 Max to 40 GHz and a 12 inch 2.92mm plug to plug cable assembly performs better than 1.35 VSWR to 40 GHz.
- The Field Replaceable Jacks are teamed with a high quality hermetic seal feed thru for use in sealed circuit modules.
- The 2.92mm plug interface employs more precise dimensions than an SMA and uses a shorter snub nose male pin such that the connector bodies align before lhe contacts engage.

MATERIAL SPECIFICATIONS

Bodies: Stainless steel/passivated per QQ-8-626, gold plated per MIL-G-45204 .00005" min. or stainless steel/passivated per MIL-F-14072 B (EL) 300

Contacts: Female - beryllium copper per QQ-C-530, gold plated per MIL-G-45204 .00005" min.

Contact Support Beads: PTFE fluorocarbon per ASTM D 1710 and ASTM D 1457 or modified PPE resin

Seal Rings: Silicone rubber per ZZ-R-765

*All gold plated parts include a .00005" min. nickel underplate barrier layer.

MATING ENGAGEMENT:

2.92MM SERIES PER MIL-STD-348



MECHANICAL SPECIFICATIONS

Engagement Design: MIL-STD-348, Series 2.92mm

Engagement/Disengagement Force: 2 inch-pounds maximum

Mating Torque: 7 to 10 inch-pounds

Coupling Proof Torque: 15 inch-pounds minimum

Coupling Nut Retention: 60 pounds minimum

Contact Retention: 6 pounds minimum axial force (captivated contacts)

Cable Retention:	Axial Force (lbs)	Torque (in-oz)
.086 semi-rigid	30	16
.141 semi-rigid	60	55

Notes:

1. ID of contact shall meet VSWR and connectivity requirements when mated with dia. .0355-.0365 male pin.

ENVIRONMENTAL RATINGS

(Meets or exceeds the applicable paragraph of MIL-C-39012)

Temperature Range: -65°C to + 165°C

Thermal Shock: MIL-STD-202, Method 107, Condition B

Corrosion: MIL-STD-202, Method 101, Condition B

Shock: MIL-STD-202, Method 213, Condition I

Vibration: MIL-STD-202, Method 204, Condition D

Moisture Resistance: MIL-STD-202, Method 106

2.92mm Series

ELECTRICAL RATINGS

Impedance: 50 ohms					
Frequency Range: 0-40 GHz					
VSWR : $\{f = GHz\}$					
Semi-rigid straight cabled connected	ors and adapte	ers 120	Max		
Field replaceable (see typical return	loss graph)	N/A			
Working Voltage: (Vrms maximum)					
Connectors for Cable Type		Sea Level	/UK Feet		
.086 semi-rigid and field replaceabl	e 335	85			
.141 semi-rigid and adapters	500	125			
Dielectric Withstanding Voltage:	VRMS minimu	ım at sea lev	vel)		
.086 semi-rigid and field replaceabl	е	1000			
.141 semi-rigid and adapters		1500			
Corona Level: (Volts minimum al 7	0,000 feet)				
.086 semi-rigid.and field replaceabl	е	250			
.141 semi-rigid and adapters		375			
Insertion Loss: (dB maximum)					
Adapters	0.06 √f (GHz),	tested at 6	GHz		
Straight semi-rigid cable connectors	0.03 √f (GHz),	tested at 10	GHz		
Insulation Resistance: 5000 mego	hms minimum	ı			
Contact Resistance: (milliohms ma	aximum)		After		

	Initial	Environmental
Center contact straight cabled connectors	3.0*	4.0
Center contact adapters	4.0	6.0
Field replaceable connectors	6.0	8.0
Outer contact (all connectors)	2.0	N/A
Body to cable (gold plated connectors)	0.5	N/A
Body to cable (stainless steel/passivated connected	ors) 5.0	N/A
RF Leakage : (dB minimum, tested at 2.5 GHz)	-90dB	
RF High Potential Withstanding Voltage : (Vrms minimum, tested at 4 and 7 MHz)		
.086 semi-rigid and field replaceable	670	
.141 semi-rigid and adapters	1000	

Typical Return Loss





FIELD REPLACEABLE APPLICATION NOTES

The field replaceable connectors manufactured by Johnson[™], are easy to install and replace. The hermetic seal is mounted into the circuit module wall and the connector can be removed and replaced without destroying the hermeticity of the circuit housing.

The field replaceable connector creates a transition from microstrip circuitry to a coaxial transmission line. The 2.92mm seal pin diameter is .012 (.030) to minimize the capacitive effects on the circuit trace. For optimum electrical performance, ihe transition from the hermetic seal to the microstrip trace must be properly compensated. Compensation involves adjusting the microstrip trace width to minimize any Impedance discontinuities found in the transition area.

The plot shown below is representative of the typical return loss of a Johnson[™] field replaceable 2.92mm connector. To produce the data shown below, a test fixture is created using the Johnson[™] 2.92mm hermetic seal. The fixture consists of a suitably thick spacer plate with the hermetic seal mounted flush to both surfaces. Two connectors are mounted back to back around the fixture and the VSWR of this lest assembly is measured. The calculated return loss trace shown Is equivalent to the square root of the measured VSWR of the test assembly. Since the connectors tested are of identical design, it can be stated with fair accuracy that the calculated data shown represents the response of a single field replaceable connector and its transition to the hermetic seal.

Although Johnson[™] does not publish a VSWR specification for field replaceable connectors, typical connector return loss can be expected to be less than -20 dB through 40 GHz. A VSWR specification is not stated because an Industry standard method for testing field replaceable connectors does not exist. The actual performance of the connector is dependent upon the following:

1. For optimum electrical performance, Johnson[™] recommends the use of our standard 142-1000-033 hermetic seal with a pin diameter of .0120 (0.305) +/ - .0005 (0.013).

2. It is recommended that the hermetic seal be mounted flush with the circuit housing. Tolerance variations between the hermetic seal and machined housing do not always guarantee an optimum transition to the connector. Some manufacturers recommend an additional counterbore in the circuit housing to accommodate a solder washer during installation of the seal. Johnson[™] does not recommend this type of installation because if the counterbore is not completely filled with solder, electrical discontinuities may be created.

3. The transition between the hermetic seal pin and the microstrip trace will effect electrical performance, as stated above. Several different methods of hermetic seal mounting and seal pin to microstrip trace attachment are used in lbe industry.

Field Replaceable Test Assembly



2.92mm Connectors



End Launch Jack - Screw-On Type



End Launch Plug - Screw-On Type



End Launch Jack - Solder Type

Stainless Steel/Passivated	Impedance	Max Frequency	VSWR
145-0701-811	50 Ohms	40GHz	1.50









2.92mm Connectors



2-Hole Flange Mount Jack and Plug Receptacle

Gold Plated	Stainless Steel/Passivated	Туре	Impedance	Max Frequency	VSWR
145-0701-601	145-0701 -602	Jack	50 Ohms	40GHz	1.20 (Test result seen on Rogers 3003
	145-0801-602	Plug	50 Onins	4000	board with 0.062" board thickness
0					
0			1/4.36UNS-28	.315 HEX	¢.165 Ø.526 Ø.526 €.526

4-Hole Flange Mount Jack and Plug Receptacle

Gold Plated	Stainless Steel/Passivated	Туре	Impedance	Max Frequency	VSWR	
145-0701-611	145-0701 -612	Jack	50 Ohma	40047	1.20 (Test result seen on Rogers 3003	
	145-0801-612	Plug	50 Onins	ns 40GHZ	40GHz board with 0.062" board thickne	board with 0.062" board thickness



2.92mm Connectors



Jack Receptacle - Thread Mount Field Replaceable



Hermetic Seal Feedthru

Part Number	Item 1 - Outer Ring	Item 2 - Insulator	Item 3 - Pin	Environmental	Electrical
142-1000-033	Kovar	Glass	Kovar	Hermeticity:	Impedance: 50 Ohms
	Gold pl .00005 min_over Nickel	Corning 7070	Gold pl .00005 min_over Nickel	1x10 ⁻⁸ cc/sec at one atmosphere	Frequency Range: DC to 40 GHz
	pl .00005 min. pl .00005 min. pl .00005 min.	Solderability:	VSWR: Dependent upon application		
				MIL-STD-202, Method 209 Operating	Working Voltage:
				Temperature:	250 Vrms max at sea level
				-55° C to 165° C	Dielectric Withstanding Voltage: 500 Vrms min. at sea level
					Insulation Resistance: 5000 Megohm min.
					Insertion Loss: 0.2 dB may at 40 GHz
Notes:					

1. The hermetic seal should be mounted as flush as possible with the housing. Excessive recession will create a high impedance air gap between connection and housing which degrades electrical performance.

2. The use of an additional counterbore to accommodate a solder ring for seal mounting is not recommended. A slight chamfer may be used if care is taken to completely fill the area with solder - **avoid air gaps**.









Straight Solder Type Plug - with contact, slide-on nut

Cable Type		Gold Plated	Stainless Steel/Passivated
.086 Semi-Rigid (F	RG-405)	145-0693-001	145-0693-002
.141 Semi-Rigid (F	RG-402)	145-0694-001	145-0694-002

Notes:

1. Stainless steel/passivated coupling nut & gold plated body.

2. Assembly instructions on page 12.





2.92mm Adapters Same Series Adapters



2.92mm Adapters are offered in Same Series and Between Series configurations. They are precision manufactured to RF component industry specifications, with a maximum frequency of 40 GHz.

Plug to Plug Same-Series Adapter



Plug to Jack Same-Series Adapter

Gold Plated	Impedance	Max Frequency	VSWR
145-0901-821	50 Ohms	40GHz	1.20
			.693 (17.60) .250 (6.35) ACROSS FLATS 2X HEX .312 (7.92)

Jack to Jack Same-Series Adapter

Gold Plated	Impedance	Max Frequency	VSWR
145-0901-801	50 Ohms	40GHz	1.20
Composition			

2.92mm to SMP Adapters

Between Series Adapters

Johnson

-.896 REF ----

Between-Series, 2.92mm Jack To SMA Jack

Туре	Stainless Steel/Passivated	Impedance	Max Frequency	VSWR
2.92mm/SMA	134-1010-000	50 Ohms	26.5GHz	1.30
	A CONTRACTOR		1/4-36UNS-2A	MARK.*134101000* 1/4-36UNS-2A

Between-Series, 2.92mm Jack To SMA Plug

Туре	Stainless Steel/Passivated	Impedance	Max Frequency	VSWR
2.92mm/SMA	134-1010-001	50 Ohms	26.5GHz	1.30
	Como		1/4-36UNS-2A	.744 REF

Between-Series, 2.92mm Plug To SMA Jack

Туре	Stainless Steel/Passivated	Impedance	Max Frequency	VSWR	
2.92mm/SMA	134-1010-002	50 Ohms	26.5GHz	1.30	
			1/4-36UNS-28	.744 REF	1/4-36UNS-2A
Between-Series, 2.92	2mm Plug To SMA Plug				

Туре	Stainless Steel/Passivated	Impedance	Max Frequency	VSWR
2.92mm/SMA	134-1010-003	50 Ohms	26.5GHz	1.30
		1/4-36UNS-2B	.744 REF	LASER MARK."1341010003"

2.92mm to SMA Adapters

Between Series Adapters



Between-Series, 2.92mm Jack To SMP Jack

Туре	Stainless Steel/Passivated	Impedance	Max Frequency	VSWR
2.92mm/SMP	134-1000-000	50 Ohms	40GHz	1.25
			LASER MARK " 134100	
0			1/4-36UNS-2A	.514 Ø 276
			-	.236 A/F/ .590

Between-Series, 2.92mm Jack To SMP Plug

Туре	Stainless Steel/Passivated	Impedance	Max Frequency	VSWR
2.92mm/SMP	134-1000-001	50 Ohms	40GHz	1.25
			LASER MARK:"1341000001"	
			1/4-36UNS-2A	.514 Ø 276

Between-Series, 2.92mm Plug To SMP Jack

Туре	Stainless Steel/Passivated	Impedance	Max Frequency	VSWR
2.92mm/SMP	134-1000-002	50 Ohms	40GHz	1.25
			1/4-36UNS-2B	.514





- 703 -

Between-Series, 2.92mm Plug To SMP Plug

Туре	Stainless Steel/Passivated	Impedance	Max Frequency	VSWR
2.92mm/SMP	134-1000-003	50 Ohms	40GHz	1.25
			1/4-36UNS-28 LASER MARK:"1341000003"	514 Ø 276 236 A/F

2.92mm Adapters

Between Series Adapters



-.861 REF-

.944 REF

Between-Series, 2.92mm Jack To SMPM Jack

Туре	Stainless Steel/Passivated	Impedance	Max Frequency	VSWR
2.92mm/SMPM	134-1000-004	50 Ohms	40GHz	1.25
				785 LASER MARK*134100004* Ø 315 Ø 354

Between-Series, 2.92mm Jack To SMPM Plug



Between-Series, 2.92mm Plug To SMPM Jack

Туре	Stainless Steel/Passivated	Impedance	Max Frequency	VSWR	
2.92mm/SMPM	134-1000-006	50 Ohms	40GHz	1.25	
Comp	and the second s		1/4-36UNS-2B	.785	- Ø.315 Ø.354
Between-Series, 2.92	mm Plug To SMPM Plug			990 KEF	

Туре **Stainless Steel/Passivated** Impedance **Max Frequency VSWR** 2.92mm/SMPM 134-1000-007 50 Ohms 40GHz 1.25 1/4-36UNS-2B-ДЦ. ø .315 Ø.354 .315 HEX 309 A/F .272 A/F LASER MARK:"1341000007" .972 REF

Assembly Instructions



2.92mm Solder Type Straight Plugs For Semi-rigid Cable



Tooling



2.92mm Tools

Accurate assembly of the 2.92mm Cabled Connectors is obtained with the tools listed below. Industry standard devices are used if possible for customer convenience and tool compatibility.



Item	Part Number	Description
A	140-0000-962	Semi-rigid Cable Vise (does not include inserts(B) or Vise Stop (F))
В	140-0000-964 140-0000-965	Cable Clamp Inserts, .086 Semi-rigid Cable Clamp Inserts, .141 Semi-rigid
С	140-0000-960 140-0000-961	Contact Soldering Tool, .086 Plug Contact Soldering Tool, .141 Plug
D	140-0000-958 140-0000-959	Body Soldering Tool, .086 Plug Body Soldering Tool, .141 Plug
E	140-0000-957	Bead Assembly Tool, Semi-rigid Plugs, All Cables
F	140-0000-968	Vise Stop, (2.92mm)



Cinch Connectivity Solutions North America Office

T +1 507.833.8822 ccsorders@us.cinch.com

Cinch Connectivity Solutions Ltd European Office

T +44 (0) 1245 342060 CinchConnectivity@eu.cinch.com

Cinch Connectivity Solutions Asia Pacific Office

T +86 21 5442 7668 ccs.asia.sales@as.cinch.com

Innovative Interconnect Solutions Across the Globe

In operation since 1917, Cinch supplies high quality, high performance connectors and cables globally to the Aerospace, Military/Defense, Commercial Transportation, Oil & Gas, High End Computer, and other markets. We provide custom solutions with our creative, hands on engineering and end to end approach.

Our diverse product offerings include: connectors, enclosures and cable assemblies utilizing multiple contact technologies including copper and fiber optics. Our product engineering and development activities employ cutting edge technologies for design and modeling, and our various technologies and expertise enable us to deliver custom solutions and products for our strategic partnerships. We also serve a broad range of commercial markets, largely through our highly efficient distribution network.

We aim to exceed our customer's expectations, and to continually provide innovative solutions to the rapidly changing needs of the markets, and customers, we serve. For more information, visit **belfuse.com/cinch**

