

Torque wrench
MANOSKOP® 755 series



Application:

For holding plug-in tools no. 52286, suitable for working on production lines or for series production work.



Execution:

- Double stop signal
- No adjustment scale, adjustment via testers
- Automatic audible and perceptible release when the set value is reached
- Made from square steep pipe
- **IMPORTANT:** Supplied WITHOUT calibration certificate. This is only created when the wrench settings are fixed at the factory.

Advantage:

- Long-term accuracy

Art. no.	52284 120
Brand	STAHlwILLE
Manufacturer Part Number	50010030
Min. torque	60 Nm
Max. torque	300 Nm
Min./max. torque	60-300 Nm
Insert shank square	14 x 18 mm
Length	609 mm
Error limit (%)	4 %
With scale	No
Gross Weight	1.305 kg
Product Group	531

EAN

4018754031658