

RFSSMAA4JAAD Datasheet

Product Name // SSMA Straight Jack 4 Hole Flange RF Connector

[View Product Page](#)



// Product Description:	
SSMA Straight Jack 4 Hole Flange RF Connector	Dielectric withstanding Voltage: >500V
Maximum Voltage: 335V	Impedance: 50Ohm
Temperature range: -65Â°C to +165Â°C	Body Material: Stainless Steel Passivation
Frecuency range: 0GHz - 40GHz	Contact Material: Beryllium Copper
VSWR:	

// General Information:	
Product Display Title:	SSMA Series Socket 4 Hole Flange
Product Family:	Radio Frequency Connectors
Product Series:	SSMA Series
Body Length:	10.20mm
Body Material:	Stainless Steel Passivation
Centre Contact Retention Force:	>26.7N
Contact Pin Material:	Beryllium Copper
Min Coupling Torque:	0.80Nm
Max Coupling Torque:	1.10Nm
Dielectric Withstanding Voltage:	>500V
Durability:	>500 cycles
Flange Mount Length:	9.50mm
Function:	Female Flange Mount RF Connector
Impedance:	50Ohm
Insulation Resistance:	>5000MOhm
Insulator:	Adapter ASTM D 1710
Max Operating Temperature:	+165°C
Min Operating Temperature:	-65°C
Mount Hole Distance:	6.35mm
Min Operating Frequency:	0GHz
Max Operating Frequency:	40GHz
Socket Diameter:	0.46mm
Thread Size:	10 36UNS 2A
Voltage Max:	335V
Vswr:	<1.30

// Product PDF Links

[SSMA Series Product Datasheet](#)