

### INVERTED MOUNT FOR OUTWARD RADIATION WITH EXCEPTIONAL RF PERFORMANCE



This industry-first inverted FlexPIFA™ (i-FlexPIFA™) antenna design (patented) delivers strong performance in challenging environments, providing you unmatched flexibility to solve your real-world antenna design challenges. Designed for rapid integration into space-constrained devices and housings, the flexible, adhesive backed antennas are available with MHF1 and MHF4 connector options.

The **i-FlexPIFA series** is designed with the radiating element facing outward when adhered to a plastic enclosure interior. This orientation gives more flexibility by granting different mounting options, like the underside of an enclosure. The i-FlexPIFA outperforms competitors' solutions in these orientations, expanding the FlexPIFA family offerings.

i-FlexPIFA antenna technology provides consistent performance across the 2.4GHz ISM band, always ensuring a solid and reliable connection.

- **Coverage** – 2.4GHz-2.48GHz Operation
- **Performance** – Exceptional performance with 3.4 dB gain and 2.5:1 VSWR, outperforming competitors' solutions
- **Versatile** – Flexible, peel-and-stick adhesive backed antenna for a variety of space-constrained IoT devices.
- **Reliable** – PIFA technology is easy to integrate into IoT devices and less likely to detune in proximity of metal or a human body.
- **Quality** – Designed and built to exacting specifications.

#### ELECTRICAL SPECIFICATIONS

Operating Frequency (MHz)	2400-2480
VSWR (Max)	<2.5:1
Peak Gain (dBi)	3.4
Nominal Impedance (Ohms)	50
Polarization	Linear
Antenna Type	Inverted Ground Flexible Planar Inverted F Antenna (i-FlexPIFA)
Radiation Pattern	Omnidirectional

#### MECHANICAL SPECIFICATIONS

Dimensions – diameter x height – mm (inches)	40.9 x 11 x 2.9 (1.61 x 0.43 x 0.114)
Connector Options	MHF1 (U.FL) & MHF4

#### ENVIRONMENTAL SPECIFICATIONS

Operating Temperature – °C (°F)	-40 to +85°C (-40 to +185°F)
---------------------------------	------------------------------

## ORDERING INFORMATION

PART NUMBER	CABLE LENGTH	CONNECTOR
EFG2400A3S-10MHF1	100 mm	MHF1
EFG2400A3S-10MHF4	100 mm	MHF4

## APPLICATION AREAS



**Industrial IoT**



**Smart Metering and Utilities**



**Rugged Handheld Scanners**



**Medical Devices**



**EV Charging Stations**



**Telematics / Logistics Devices**

**Note:** This product is currently in development, and this product brief is preliminary. All data and specifications are subject to change