

General Information

Extended Product Type:	MSHD-LTB
Product ID:	1SAM201920R1011
EAN:	4013614441820
Catalog Description:	MSHD-LTB Handles
Long Description:	MSHD-LTB Handle, IP64, black, 3 times lockable, defeatable, 0-TRIP-I Suitable for Manual Motor Starter

Categories

Products » Low Voltage Products and Systems » Control Products » Manual Motor Starters » Manual Motor Starters Accessories

Ordering

Minimum Order Quantity:	1 piece
Customs Tariff Number:	85389099
EAN:	4013614441820

Container Information

Package Level 1 Length:	70 mm
Package Level 1 Height:	170 mm
Package Level 1 Gross Weight:	0.1 kg
Package Level 1 Units:	1 piece
Package Level 1 Width:	130 mm

Dimensions

Product Net Height:	65.5 mm
Product Net Depth:	57.9 mm
Product Net Weight:	0.065 kg
Product Net Width:	65.6 mm

Technical

Contact Position Indication:	ON / OFF / TRIP
Actuator Type:	Rotary Handle
Shaft Diameter:	6x6 mm
Color:	black
Degree of Protection:	IP64
Tightening Torque:	0.12 N·m
Product Name:	Handles
Suitable For:	MS116 MS132 MO132 MS450 MS451 MS495 MS496 MS497 MO450 MO495 MO496
Suitable for Product Class:	Manual Motor Starter

Environmental

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
--------------	---

Technical UL/CSA

Enclosure Type UL/CSA:	1 12 3R
Tightening Torque UL/CSA:	1.06 in·lb

Certificates and Declarations (Document Number)

Instructions and Manuals:	2CDC131033M6801
Data Sheet, Technical Information:	1SBC100173C0201
Declaration of Conformity - CE:	1SAD938516-0060

1SAD938502-0188
1SAD938504-0183
1SAD938510-0125
1SAD938504-0021

RoHS Information: 1SAA963001-4407

Classifications

ETIM 4:	EC002498 - Accessories for low-voltage switch technology
ETIM 5:	EC002498 - Accessories for low-voltage switch technology
ETIM 6:	EC002498 - Accessories for low-voltage switch technology
eClass:	7.0 27379201

Accessories [Show accessory images](#)

1 Products			Filter	<input type="text"/>
Identifier	Description	Type	Qty	Unit Of Measure
1SAM201920R1000	MSH-AR Shaft Alignment Ring	MSH-AR	1	piece

