

## SCLC steel boring bar set, offset, positive right

For facing and longitudinal turning using CC indexable inserts

**ORION**<sup>®</sup>

### Application:

For facing and longitudinal turning using CC 80° indexable inserts.

### Execution:

- Precision-manufactured boring bar, **steel**, without internal cooling, offset, type C, pitch angle 95°, tip angle 80°, clearance angle 7°

### Advantage:

- Universal use for facing and longitudinal turning
- Positive body geometry ensures low cutting forces



<b>Art. no.</b>	<b>17846 110</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	17846110
<b>ISO name</b>	SCLC R06
<b>Material</b>	Steel
<b>Composition of set</b>	1 each A0608H, A0810J, A1012K, A1216M (without internal cooling)
<b>Number of pieces in assortment/set</b>	4 PCS
<b>Suitable for indexable inserts</b>	CC.. 0602..
<b>Machining direction</b>	Right
<b>DIN</b>	8024
<b>Gross Weight</b>	0.397 kg
<b>Product Group</b>	186

### EAN

4053625705429