

DIAPOINT single-diamond dressing tools with 3-5 natural points, few impurities (2nd. quality)

For dressing ceramic grinding wheels




Application:

Suitable for all machines with corresponding holder. **Chucking:** Inclination of dressing tool to sanding disc centre from 5° to 15° required. We recommend **selecting the appropriate diamond weight** for individual diamond dressing tools according to the following diagram depending on the sanding disc to be adjusted.

Version:

- Universal, traditional dressing tool with a single diamond with protruding working tip



Art. no.	61135 100
Shank style	Morse taper
Morse taper size	MK 0
Natural tip quality	2
Weight of diamond	1 carat
Min./max. side feed per revolution	0.05-0.15 m/s
Min./max supply per throughput	0.01-0.03 mm
Number of pieces per packet	1 PCS
DIN	228