



HP w19b 19-inch Wide Flat Panel Monitor with Brightview Technology

Datasheet

- **Brightview Technology**
- **Tilt adjustment for easy viewing**
- **Sleek clean design with side controls**
- **Easily wall-mountable-light-weight with detachable base¹**



Brilliant picture quality

- The BrightView panel provides more than just great technology. The HP w19b provides an affordable flat panel monitor featuring BrightView technology panel for crisp clear images.
- BrightView panel technology brings everything brilliantly to life.
- The wide aspect ratio and high resolution bring gaming and internet surfing brilliantly alive when you plug into your HP PC.
- Fast response time makes gaming even more enjoyable.
- Resolution of 1440 x 900 and a wide workspace provides just what you need to edit photos, surf the net or play a game on your PC.
- Work easily between multiple software windows or on two-page layouts with less scrolling.
- Dual inputs support true digital (DVI-D) and traditional analog (VGA) signals.
- Integrated speakers frees up desk space for a clean look.
- Easily share the screen with family and friends, it's wide viewing angle provides what you need.

High Resolution Picture Quality and Ultimate flexibility

- Creative and technical users can maximize project productivity with this wide screen. View two pages side by side for editing graphic layouts, or working with wider spread sheets.
- Extreme resolution at 1440 x 900 for bright, awesome graphic quality perfect for multimedia viewing, photo editing or gaming on your PC.
- Standard 15-pin D-sub analog and advanced DVI-D digital interfaces for optimal graphic performance.

Stylish Design for Home Entertainment or Home Office

- The wide viewing angle and tilt makes it easy to adjust the monitor to work or play comfortably.
- The slim profile and integrated speakers minimizes desk clutter.
- The best complement for your HP Pavilion home PC in style and functionality backed by HP's quality and reliability.

Easy to use

- Less need to scroll side to side with the wide view.
- Wide screen provides space to keep small windows like calendars, post its etc on the side.
- Wide viewing angle for multi-viewer applications.
- Large, on-screen picture with digital user controls for custom tuning.
- Plug and play for quick and easy installation, no drivers required.

Award winning support from HP²

- Buy any HP product and you get more than just great technology. You get the peace of mind of HP's award-winning product help and support.
- Enjoy the benefits of Total Care. 24/7 access online and off. Prompt service-real time chat with a support technician and as fast as one-hour email responses.
- Direct knowledgeable assistance by phone, agents in English and Spanish in US, or English or French in Canada. 1-800-HPINVENT.

Recycle

- HP makes it easy to recycle PCs, monitors and peripherals, any brand or manufacturer. Reduce, reuse and recycle. www.hp.com/recycle.



HP Total Care is a J.D. Power and Associates Certified Technology Service and Support Center, recognized for consistently providing "An Outstanding Customer Service Experience." *

¹ Mounting hardware sold separately. ² 14th straight Readers' Choice selection for service, reliability and customer satisfaction by PC Magazine. * J.D. Power and Associates Certified Technology Service and Support ProgramSM, developed in conjunction with the Service & Support Professionals Association (SSPA). For more information, visit www.jdpower.com or thesspa.com.

HP w19b 19-inch Wide Flat Panel Monitor with Brightview Technology

Datasheet

Key Monitor Specifications

LCD Panel Type	19" Wide Thin-Film Transistor LCD active matrix
Viewable Area	163.2 sq in
Native Resolution (recommended)	1440 x 900
Contrast Ratio (typical)	up to 700:1
Brightness (typical)	up to 300 nits
Pixel Pitch	0.285 mm
Response Time (typical)	5 ms
Signal Input Connectors	VGA and DVI-D connections; VGA cable included
Power Supply	Internal AC Adapter
Maximum Power Rating	<37W
Energy Saving Mode	<2W in sleep mode
Tilt	Yes; -5 to +20 degrees
Detachable Base	Yes (Alloy Metallic)
VESA Mounting	Standard 4 hole pattern 75mm x 75mm screw-mounting option; pedestal is removable
Dimensions Unpacked	17.26 (w) x 14.03 (h) x 8.30 (d) in. (438.5 x 356.5 x 211 mm)
Weight Unpacked	10.69 lbs (4.85 Kg)
Dimensions Packed	20.47(w) x 15.43(h) x 7.48(d) in. (520 x 392 x 190 mm)
Weight Packed	14.21 lbs. (6.45 Kg)
Languages	English, German, France, Spanish, Portuguese, Chinese
Energy Star Compliant	Yes

Key Speaker Specifications

Type	Integrated front bezel
Output Power	1w x 2

Accessories, Warranty and Agency Approvals

Supplied Accessories	A/C power cable; VGA cables; Limited Warranty Card; Audio cable
Warranty	Limited 1 year warranty. Availability varies by region. Certain restrictions and exclusions apply.
Agency Approvals	UL, C-UL or CSA (Canada), GS Mark (German ergonomic), NOM, BSMI, PSB, C-tick, EPA, MIC (South Korea), CE Marking, CB, FCC-B approval, TCO '99 (emissions, ergonomics, environment), ICES-003、Windows certified (Microsoft Windows 2000 and Microsoft Windows XP), UL listed



Visit www.hp.com for more details!

