

**Pin Configuration:**

- 1. Emitter
- 2. Base
- 3. Collector

**Features:**

- NPN silicon planar epitaxial transistors
- General purpose transistors, best suited for use in driver stages of audio amplifiers, of tape recorders. Low noise input stages, Hi-Fi amplifiers, signal processing circuits of television receivers

**Absolute Maximum Ratings**

Parameters	Symbol	Value	Unit
Collector Emitter Voltage	$V_{CEO}$	30	V
Collector Base Voltage	$V_{CBO}$		
Emitter Base Voltage	$V_{EBO}$		
Collector Current Continuous	$I_C$	100	mA
Power Dissipation at $T_a = 25^\circ\text{C}$ Derate above $25^\circ\text{C}$	$P_D$	625	mW
Power Dissipation at $T_C = 25^\circ\text{C}$ Derate above $25^\circ\text{C}$		5	mW/ $^\circ\text{C}$
Operating and Storage Junction Temperature Range	$T_j, T_{stg}$	-55 to +150	$^\circ\text{C}$

**Thermal Resistance**

Junction to Ambient	$R_{th(j-a)}$	200	$^\circ\text{C}/\text{W}$
Junction to Case	$R_{th(j-c)}$	83.3	

## Electrical Characteristics ( $T_a = 25^\circ\text{C}$ unless otherwise specified)


Parameters	Symbol	Test Condition	Min.	Typ.	Max.	Units
Collector Emitter Voltage	$V_{CEO}$	$I_C = 1\text{mA}, I_B = 0$	30	-	-	V
Collector Base Voltage	$V_{CBO}$	$I_C = 10\mu\text{A}, I_E = 0$		-	-	
Emitter Base Voltage	$V_{EBO}$	$I_E = 10\mu\text{A}, I_C = 0$	5	-	-	
Collector Cut off Current	$I_{CBO}$	$V_{CB} = 30\text{V}, I_E = 0$ $V_{CB} = 30\text{V}, I_E = 0,$ $T_a = +125^\circ\text{C}$	-	-	15 5	nA $\mu\text{A}$
Emitter Cut off Current	$I_{EBO}$	$V_{EB} = 4\text{V}, I_C = 0$	-	-	15	nA
DC Current Gain	$h_{FE}$	$V_{CE} = 5\text{V}, I_C = 10\mu\text{A}$ $V_{CE} = 5\text{V}, I_C = 2\text{mA}$	100 420	270 500	- 800	-
Collector Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C = 10\text{mA}, I_B = 0.5\text{mA}$ $I_C = 10\text{mA}, I_B = \text{see note 1}$ $I_C = 100\text{mA}, I_B = 5\text{mA}^*$	-	0.075 0.3 0.25	0.25 0.6 0.6	V
Base Emitter Saturation Voltage	$V_{BE(sat)}$	$I_C = 10\text{mA}, I_B = 5\text{mA}^*$	-	1.1	-	
Base Emitter on Voltage	$V_{BE(on)}$	$I_C = 10\mu\text{A}, V_{CE} = 5\text{V}$ $I_C = 100\mu\text{A}, V_{CE} = 5\text{V}$ $I_C = 2\text{mA}, V_{CE} = 5\text{V}$	0.55	0.52 0.55 0.62	0.7	

## Dynamic Characteristics

Transition Frequency	$f_T$	$I_C = 10\text{mA}, V_{CE} = 5\text{V},$ $f = 100\text{MHz}$	-	250	-	MHz
Collector Output Capacitance	$C_{cbo}$	$I_E = 0, V_{CE} = 10\text{V}$ $f = 1\text{MHz}$	-	2.5	-	pF
Noise Figure	$NF_1^*$	$V_{CE} = 5\text{V}, I_C = 200\mu\text{A}$ $R_S = 2\text{K}\Omega,$ $f = 30\text{Hz} - 15\text{kHz}$	-	0.6	2.5 10	dB
	$NF_2$	$V_{CE} = 5\text{V}, I_C = 200\mu\text{A}$ $R_S = 100\text{K}\Omega, f = 1\text{kHz}$				
Small Signal Current Gain	$h_{fe}$	$V_{CE} = 5\text{V}, I_C = 2\text{mA}$ $f = 1\text{kHz}$	450	600	900	-

Note 1:  $I_B$  is value for which  $I_C = 11\text{mA}$  at  $V_{CE} = 1\text{V}$

\*Pulse Condition: = Pulse Width  $\leq 300\mu\text{s}$ , Duty Cycle  $\leq 2\%$ .



Dimensions	Min.	Max.
A	4.32	5.33
B	4.45	5.2
C	3.18	4.19
D	0.41	0.55
E	0.35	0.5
F	5°	
G	1.14	1.4
H		1.53
K	12.7	-
L	1.982	2.082

Dimensions : Millimetres

**Pin Configuration:**

- 1. Emitter
- 2. Base
- 3. Collector

**Part Number Table**

Description	Part Number
Transistor, NPN, TO-92	BC549C

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
 Farnell.com/multicomp-pro  
 Element14.com/multicomp-pro