




Nanonics

TE Internal #: 6-1589487-2

PCB Mount Receptacle, Horizontal, Wire-to-Board, 65 Position, .64mm [.025in] Centerline, 2 Row, Tin-Lead, Natural Housing Color, Printed Circuit Board

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Receptacle**

PCB Mount Orientation: **Horizontal**

Connector System: **Wire-to-Board**

Number of Positions: **65**

Centerline (Pitch): **.64 mm [.025 in]**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Standoffs	4
PCB Mount Orientation	Horizontal
Number of Positions	65
Number of Rows	2

Contact Features

Contact Retention Within Housing	Without
PCB Contact Termination Area Plating Material	Tin-Lead
Contact Base Material	Brass
Contact Mating Area Plating Material	Tin-Lead
Contact Mating Area Plating Material Thickness	1.27 – 2.28 μm[50 – 90 μin]
Contact Type	Socket

Termination Features

Rectangular Termination Post & Tail Thickness	.18 mm[.008 in]
---	-----------------



Rectangular Termination Post & Tail Width	.23 mm[.009 in]
Termination Post & Tail Length	2.29 mm[.09 in]
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

Surface Mount Extended Leads	Without
Mounting/Mating Hardware	With
Strain Relief	Without
Mating Alignment Type	Polarization
Mating Alignment	With
Hardware Type	1.0 mm X .200" Mounting Screw
Panel Mount Feature	Without
Mating Retention Type	Jackscrew
PCB Mount Alignment	Without
Mating Retention	With
PCB Mount Retention	Without
Connector Mounting Type	Board Mount

Housing Features

Housing Plating Material	Nickel
Centerline (Pitch)	.64 mm[.025 in]
Housing Color	Natural
Housing Material	LCP (Liquid Crystal Polymer)

Dimensions

Connector Length	25.62 mm[1.009 in]
Screw & Hole Diameter	1 mm[.039 in]
Connector Height	3.17 mm[.125 in]
Row-to-Row Spacing	1.02 mm[.04 in]

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2017 (174) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not lead free process capable



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



Customers Also Bought



Documents

Product Drawings

STM065M6KN = THRU-HOLE

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_6-1589487-2_T_c-6-1589487-2-t.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-1589487-2_T_c-6-1589487-2-t.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-1589487-2_T_c-6-1589487-2-t.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

STM065M6KN

PCB Mount Receptacle, Horizontal, Wire-to-Board, 65 Position, .64mm [.025in]
Centerline, 2 Row, Tin-Lead, Natural Housing Color, Printed Circuit Board



[1589487 Nanonics Cross Reference](#)

English