

DATA SHEET

1.5MIN

5.5-7.5


unit: mm

Туре	Rechargeable Nickel Metal
	Hydride Cylindrical Cell
Nominal Dimension	Φ = 26.2mm
(with Sleeve)	H = 50.0mm
Applications	Recommended discharge current
	300mA to 9A
Nominal Voltage	1.2V
Capacity	Rated: 3000mAh
	Typical: 3100mAh
	When discharged at 600mA to 1.0V at
	20℃
	300mA for 16 hrs at 20°C
Fast Charge	1500mA to 3000mA (0.5 to 1C)
	charge termination control recommended
	control parameters:
	-∆V : 0-5mV
	DT/dt : 0.8°C/min (0.5 to 0.9C)
	0.8 - 1°C/min (1C)
	TCO : 45 - 50°C
	Timer : 105% nominal input
	(for ref. only)
	>500 cycles (IEC standard)
Continuous	300mA maximum current for 1 year.
Overcharge	No conspicuous deformation and/or
	Leakage
Weight	59.0g
Internal Resistance	Average $40 \text{m}\Omega$ upon fully charged
	(Max 45mΩ) at 1000Hz
	1.5V at 300mA charging
Ambient Temperature	Standard Charge : 0 to 40°C
Range	Fast Charging : 10 to 40°C
	Discharge : -20 to 50°C
	Storage : -20 to 35°C
	Storage (1week) : -20 to 60°C

+0


26.2 -1.3

50.0 -1.4




Model No.: GP300CHC

Fast Charge (Charge Control required)



High Rate Discharge



The information (subject to change without prior notice) contained in this document is for reference only and should not be used as a basis for product guarantee or warranty. For applications other than those described here, please consult your nearest GP Sales and Marketing Office or Distributors.

www.gpbatteries.com

MRS6160 rev02