


- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

STANDARD EXECUTIONS

- **DIN 6335-GG-C:** cast iron, H7 reamed blind hole.
- **DIN 6335-GG-D:** cast iron, threaded pass-through hole.
- **DIN 6335-GG-E:** cast iron, threaded blind hole.
- **DIN 6335-GG-D-ZB:** zinc-plated cast iron, threaded pass-through hole.
- **DIN 6335-GG-E-ZB:** zinc-plated cast iron, threaded blind hole.
- **DIN 6335-NI-E:** Cast AISI CF-8 stainless steel, sandblasted matte finish, threaded blind hole.

SPECIAL EXECUTIONS ON REQUEST

- Solid hub (DIN 6335-GG-A).
- H7 reamed pass-through hole (DIN 6335-GG-B).
- Aluminium, glossy finish (DIN 6335-AL-PL).
- Aluminium, matte finish (DIN 6335-AL-MT).



DIN 6335-GG-C

| Code | Description | d1 | d3 H7 | d4 | h2 | t1 min | h4 | △△ |
|----------|-----------------------|-----|-------|----|----|--------|----|-----|
| GN.10763 | DIN 6335-GG-32-B6-C | 32 | 6 | 12 | 20 | 12 | 9 | 29 |
| GN.10767 | DIN 6335-GG-40-B8-C | 40 | 8 | 14 | 25 | 15 | 13 | 49 |
| GN.10773 | DIN 6335-GG-50-B10-C | 50 | 10 | 18 | 32 | 18 | 18 | 103 |
| GN.10777 | DIN 6335-GG-63-B12-C | 63 | 12 | 20 | 40 | 22 | 23 | 169 |
| GN.10783 | DIN 6335-GG-80-B16-C | 80 | 16 | 25 | 50 | 28 | 28 | 341 |
| GN.10787 | DIN 6335-GG-100-B20-C | 100 | 20 | 32 | 63 | 36 | 36 | 682 |


DIN 6335-GG-D

| Code | Description | d1 | d2 | d4 | h2 | t2 | h4 | △△ |
|----------|-----------------------|-----|-----|----|----|----|----|-----|
| GN.10761 | DIN 6335-GG-32-M6-D | 32 | M6 | 12 | 20 | 10 | 9 | 28 |
| GN.10765 | DIN 6335-GG-40-M8-D | 40 | M8 | 14 | 25 | 12 | 13 | 60 |
| GN.10771 | DIN 6335-GG-50-M10-D | 50 | M10 | 18 | 32 | 16 | 18 | 101 |
| GN.10775 | DIN 6335-GG-63-M12-D | 63 | M12 | 20 | 40 | 20 | 23 | 180 |
| GN.10781 | DIN 6335-GG-80-M16-D | 80 | M16 | 25 | 50 | 30 | 28 | 329 |
| GN.10785 | DIN 6335-GG-100-M20-D | 100 | M20 | 32 | 63 | 38 | 36 | 640 |

DIN 6335-GG-E

| Code | Description | d1 | d2 | d4 | h2 | t1 min | h4 | △△ |
|----------|-----------------------|-----|-----|----|----|--------|----|-----|
| GN.10762 | DIN 6335-GG-32-M6-E | 32 | M6 | 12 | 20 | 12 | 9 | 30 |
| GN.10766 | DIN 6335-GG-40-M8-E | 40 | M8 | 14 | 25 | 15 | 13 | 60 |
| GN.10772 | DIN 6335-GG-50-M10-E | 50 | M10 | 18 | 32 | 18 | 18 | 105 |
| GN.10776 | DIN 6335-GG-63-M12-E | 63 | M12 | 20 | 40 | 22 | 23 | 200 |
| GN.10782 | DIN 6335-GG-80-M16-E | 80 | M16 | 25 | 50 | 28 | 28 | 350 |
| GN.10786 | DIN 6335-GG-100-M20-E | 100 | M20 | 32 | 63 | 36 | 36 | 715 |

Clamping elements



DIN 6335-GG-D-ZB

| Code | Description | d1 | d2 | d4 | h2 | t2 | h4 | ⚖ |
|----------|-------------------------|----|-----|----|----|----|----|-----|
| GN.10005 | DIN 6335-GG-32-M6-D-ZB | 32 | M6 | 12 | 20 | 10 | 9 | 33 |
| GN.10009 | DIN 6335-GG-40-M8-D-ZB | 40 | M8 | 14 | 25 | 13 | 13 | 52 |
| GN.10017 | DIN 6335-GG-50-M10-D-ZB | 50 | M10 | 18 | 32 | 16 | 18 | 104 |
| GN.10034 | DIN 6335-GG-63-M12-D-ZB | 63 | M12 | 20 | 40 | 20 | 23 | 170 |
| GN.10041 | DIN 6335-GG-80-M16-D-ZB | 80 | M16 | 25 | 50 | 20 | 28 | 329 |

DIN 6335-GG-E-ZB

| Code | Description | d1 | d2 | d4 | h2 | t1 min | h4 | ⚖ |
|----------|-------------------------|----|-----|----|----|--------|----|-----|
| GN.10007 | DIN 6335-GG-32-M6-E-ZB | 32 | M6 | 12 | 20 | 12 | 9 | 34 |
| GN.10011 | DIN 6335-GG-40-M8-E-ZB | 40 | M8 | 14 | 25 | 15 | 13 | 55 |
| GN.10019 | DIN 6335-GG-50-M10-E-ZB | 50 | M10 | 18 | 32 | 18 | 18 | 149 |
| GN.10036 | DIN 6335-GG-63-M12-E-ZB | 63 | M12 | 20 | 40 | 22 | 23 | 200 |
| GN.10043 | DIN 6335-GG-80-M16-E-ZB | 80 | M16 | 25 | 50 | 28 | 28 | 340 |

DIN 6335-NI-E



| Code | Description | d1 | d2 | d4 | h2 | t1 min | h4 | ⚖ |
|----------|----------------------|----|-----|----|----|--------|----|-----|
| GN.10757 | DIN 6335-NI-32-M6-E | 32 | M6 | 12 | 20 | 12 | 9 | 38 |
| GN.10758 | DIN 6335-NI-40-M8-E | 40 | M8 | 14 | 25 | 15 | 13 | 62 |
| GN.10759 | DIN 6335-NI-50-M10-E | 50 | M10 | 18 | 32 | 18 | 18 | 119 |
| GN.10760 | DIN 6335-NI-63-M12-E | 63 | M12 | 20 | 40 | 22 | 23 | 205 |