

Switch

EHSS001

Part Number




- 5 Ethernet ports
- Rugged aluminium housing

Ethernet

Technical Data

Electrical Data	
Supply Voltage	12...48 V
Current Consumption (U _b = 24 V)	0,16 A
Temperature Range	-10...60 °C
Overload Protection	yes
Reverse Polarity Protection	yes
Number of Gigabit Ethernet RJ45	5
Baud Rate	10/100/1000 Mbit/s
Transmission Mode	Full/Half Duplex
Switch Mode	Store & Forward
Auto-Crossover	yes
Auto-Negotiating	yes
Auto-Polarity	yes
Mechanical Data	
Material	Aluminum
Weight	290 g
Degree of Protection	IP30
DIN-Rail mounting	35 mm
Connection	Terminal Block

This switch allows simple connecting of up to five Ethernet products.



All dimensions in mm (1 mm = 0.03937 Inch)