

electric chain hoist Pro/DC-Pro, infinitely variable

load capacity: 125-2000 kg

DEMAG

Application:

Infinitely adjustable speed controls mean that valuable and delicate parts can be lifted, lowered and positioned more gently and securely, e.g. fluid containers or breakable products. Installation and insertion processes can be controlled more precisely. Lifting movements can be performed much more rapidly thanks to the double nominal speed of Pro-lift in the partial load range.

Execution:

- Plug and lift—all chain block electric connections are plug-in
- With a hinged, universal suspension bracket, the tension can simply be suspended in the wheel set
- The length of the control cable can be adjusted without any additional wiring effort
- Fatigue-free operation due to ergonomically optimised and robust control switch DSC
- Fast change of the entire chain drive without dismantling the motor or transmission parts
- Contactor protection 24 V, degree of protection IP55
- Operating hour meter
- Operation limit switch for top-most/bottom-most hook position



Art. no.	77080 190
Brand	DEMAG
Manufacturer Part Number	93157046
Load-carrying capacity	250 kg
Lift height	5 m
Stroke speed control	Continuous
Stroke speed at nominal load	16 m/min
Stroke speed without load	30 m/min
Min. stroke speed	0.15 m/min
Number of load chains	1 PCS
Construction height	364 mm
Length	502 mm
Depth	268 mm
Model	DCS-Pro 2-250 VS16-30
FEM group	2 m+
Colour	Azure blue RAL 5009
Gross Weight	0.001 kg
Product Group	774