

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 04.03.2022

Version number 304 (replaces version 303)

Revision: 04.03.2022

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier** 600023
- **Trade name:** Brake cleaning agent E-COLL
- **Article number:** 4317784234405
- **UFI:** 73ER-9XFW-XCOX-TE2S
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
- **Sector of Use**
SU21 Consumer uses: Private households / general public / consumers
SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)
- **Application of the substance / the mixture** Cleaning agent/ Cleaner
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
E/D/E - Einkaufsbuero Deutscher Eisenhaendler GmbH
EDE Platz 1
D-42389 Wuppertal
Germany

Tel. +49 202 6096-0
e-mail: sdb@ede.de
- **Further information obtainable from:** Product safety department
- **1.4 Emergency telephone number:** Giftinformationszentrum Mainz – Tel.: +49 (6131) 19240

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**
Flam. Liq. 2 H225 Highly flammable liquid and vapour.
Skin Irrit. 2 H315 Causes skin irritation.
STOT SE 3 H336 May cause drowsiness or dizziness.
Asp. Tox. 1 H304 May be fatal if swallowed and enters airways.
Aquatic Chronic 2 H411 Toxic to aquatic life with long lasting effects.

2.2 Label elements

- **Labelling according to Regulation (EC) No 1272/2008**
The product is classified and labelled according to the CLP regulation.

Hazard pictograms

GHS02 GHS07 GHS08 GHS09

(Contd. on page 2)

EU

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 04.03.2022

Version number 304 (replaces version 303)

Revision: 04.03.2022

Trade name: Brake cleaning agent E-COLL

(Contd. of page 1)

Signal word Danger**Hazard-determining components of labelling:**

Naphtha (petroleum), hydrotreated light (Benzene < 0.1%)

Hazard statements

H225 Highly flammable liquid and vapour.

H315 Causes skin irritation.

H336 May cause drowsiness or dizziness.

H304 May be fatal if swallowed and enters airways.

H411 Toxic to aquatic life with long lasting effects.

Precautionary statements

P101 If medical advice is needed, have product container or label at hand.

P102 Keep out of reach of children.

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P243 Take action to prevent static discharges.

P261 Avoid breathing dust/fume/gas/mist/vapours/spray.

P264 Wash thoroughly after handling.

P271 Use only outdoors or in a well-ventilated area.

P273 Avoid release to the environment.

P301+P310 IF SWALLOWED: Immediately call a POISON CENTER/ doctor.

P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water [or shower].





P332+P313 If skin irritation occurs: Get medical advice/attention.

P403+P233 Store in a well-ventilated place. Keep container tightly closed.

P405 Store locked up.

P501 Dispose of contents/container in accordance with local/regional/national/international regulations.

2.3 Other hazards**Results of PBT and vPvB assessment****PBT:** Not applicable.**vPvB:** Not applicable.**SECTION 3: Composition/information on ingredients****3.2 Mixtures****Description:** Mixture of substances listed below with nonhazardous additions.**Dangerous components:**

EC number: 921-024-6 Reg.nr.: 01-2119475514-35-xxxx	hydrocarbons, C6-C7, n-alkanes,  Flam. Liq. 2, H225  Asp. Tox. 1, H304  Aquatic Chronic 2, H411  Skin Irrit. 2, H315; STOT SE 3, H336	50-100%
--	---	---------

Regulation (EC) No 648/2004 on detergents / Labelling for contents30 % and more
aliphatic hydrocarbons

(Contd. on page 3)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 04.03.2022

Version number 304 (replaces version 303)

Revision: 04.03.2022

Trade name: Brake cleaning agent E-COLL

(Contd. of page 2)

- **Additional information:** For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures**4.1 Description of first aid measures**

- **General information:** Personal protection for the First Aider.

After inhalation:

Supply fresh air.

Seek medical treatment in case of complaints.

In case of unconsciousness place patient stably in side position for transportation.

After skin contact:

Immediately wash with water and soap and rinse thoroughly.

If skin irritation continues, consult a doctor.

After eye contact:

Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.

After swallowing:

Rinse out mouth and then drink plenty of water.

Do not induce vomiting; call for medical help immediately.

4.2 Most important symptoms and effects, both acute and delayed

No further relevant information available.

4.3 Indication of any immediate medical attention and special treatment needed

If swallowed or in case of vomiting, danger of entering the lungs.

SECTION 5: Firefighting measures**5.1 Extinguishing media****Suitable extinguishing agents:**CO₂, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.

- **For safety reasons unsuitable extinguishing agents:** Water with full jet

- **5.2 Special hazards arising from the substance or mixture** No further relevant information available.

5.3 Advice for firefighters

- **Protective equipment:** Wear self-contained respiratory protective device.

Additional information

Collect contaminated fire fighting water separately. It must not enter the sewage system.

EU
(Contd. on page 4)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 04.03.2022

Version number 304 (replaces version 303)

Revision: 04.03.2022

Trade name: Brake cleaning agent E-COLL

(Contd. of page 3)

SECTION 6: Accidental release measures**· 6.1 Personal precautions, protective equipment and emergency procedures**

Wear protective equipment. Keep unprotected persons away.
Ensure adequate ventilation
Keep away from ignition sources.

· 6.2 Environmental precautions:

Inform respective authorities in case of seepage into water course or sewage system.
Prevent seepage into sewage system, workpits and cellars.
Do not allow to enter sewers/ surface or ground water.

· 6.3 Methods and material for containment and cleaning up:

Ensure adequate ventilation.
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).

· 6.4 Reference to other sections

See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

*** SECTION 7: Handling and storage****· 7.1 Precautions for safe handling** Use only in well ventilated areas.**· Information about fire - and explosion protection:**

Fumes can combine with air to form an explosive mixture.



Keep ignition sources away - Do not smoke.

Protect against electrostatic charges.

· 7.2 Conditions for safe storage, including any incompatibilities**· Storage:**

· **Requirements to be met by storerooms and receptacles:** Provide floor trough without outlet.

· **Information about storage in one common storage facility:** Store away from oxidising agents.

· Further information about storage conditions:

Keep container tightly sealed.
Protect from heat and direct sunlight.
Store in a cool place.

· **Storage class:** -

· **7.3 Specific end use(s)** No further relevant information available.

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 04.03.2022

Version number 304 (replaces version 303)

Revision: 04.03.2022

Trade name: Brake cleaning agent E-COLL

(Contd. of page 4)

SECTION 8: Exposure controls/personal protection**8.1 Control parameters****Ingredients with limit values that require monitoring at the workplace:**

The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.

DNELs**hydrocarbons, C6-C7, n-alkanes,**

Oral	DNEL Langzeitwert Verbraucher	699 mg/kg/d (cus)
Dermal	Long term value for employees	773 mg/kg bw/Tag (industrial use)
Inhalative	Long term value for employees	2,035 mg/m ³ (industrial use)

Additional information: The lists valid during the making were used as basis.

8.2 Exposure controls

Appropriate engineering controls No further data; see item 7.

Individual protection measures, such as personal protective equipment

General protective and hygienic measures:

Keep away from foodstuffs, beverages and feed.
Wash hands before breaks and at the end of work.
Do not inhale gases / fumes / aerosols.
Avoid contact with the eyes and skin.

Hand protection

Protective gloves

Material of gloves

Nitrile rubber, NBR
Recommended thickness of the material: ≥ 0.4 mm

Penetration time of glove material

Value for the permeation: Level < 480 min

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

Eye/face protection Safety glasses

Body protection: Protective work clothing

SECTION 9: Physical and chemical properties**9.1 Information on basic physical and chemical properties****General Information****Physical state**

Fluid

(Contd. on page 6)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 04.03.2022

Version number 304 (replaces version 303)

Revision: 04.03.2022

Trade name: Brake cleaning agent E-COLL

(Contd. of page 5)

· Colour:	Colourless
· Odour:	Petrol-like
· Odour threshold:	Not determined.
· Melting point/freezing point:	Undetermined.
· Boiling point or initial boiling point and boiling range	78 °C
· Flammability	Not applicable.
· Lower and upper explosion limit	
· Lower:	0.8 Vol %
· Upper:	8 Vol %
· Flash point:	-1 °C
· Ignition temperature:	260 °C
· Decomposition temperature:	Not determined.
· pH	Not determined.
· Viscosity:	
· Kinematic viscosity	Not determined.
· Kinematic: 23 °C - 4 mm (ISO 2431)	
· Dynamic:	Not determined.
· Solubility	
· water:	Not miscible or difficult to mix.
· Partition coefficient n-octanol/water (log value)	Not determined.
· Vapour pressure at 20 °C:	2,800 hPa
· Density and/or relative density	
· Density at 20 °C:	0.7 g/cm ³
· Relative density	Not determined.
· Vapour density	Not determined.
9.2 Other information	
· Appearance:	
· Form:	Fluid
· Important information on protection of health and environment, and on safety.	
· Auto-ignition temperature:	Product is not selfigniting.
· Explosive properties:	Product is not explosive. However, formation of explosive air/vapour mixtures are possible.
· Solvent separation test:	
· Organic solvents:	90.0 %
· Change in condition	
· Softening point/range	
· Oxidising properties	Not determined.
· Evaporation rate	Not determined.
Information with regard to physical hazard classes	
· Explosives	Void
· Flammable gases	Void
· Aerosols	Void
· Oxidising gases	Void
· Gases under pressure	Void
· Flammable liquids	Highly flammable liquid and vapour.
· Flammable solids	Void
· Self-reactive substances and mixtures	Void
· Pyrophoric liquids	Void
· Pyrophoric solids	Void

(Contd. on page 7)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 04.03.2022

Version number 304 (replaces version 303)

Revision: 04.03.2022

Trade name: Brake cleaning agent E-COLL

(Contd. of page 6)

- **Self-heating substances and mixtures** Void
- **Substances and mixtures, which emit flammable gases in contact with water** Void
- **Oxidising liquids** Void
- **Oxidising solids** Void
- **Organic peroxides** Void
- **Corrosive to metals** Void
- **Desensitised explosives** Void

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**
No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** Reacts with strong oxidising agents.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

SECTION 11: Toxicological information

- **11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008**
- **Acute toxicity** Based on available data, the classification criteria are not met.

- **LD/LC50 values relevant for classification:**

hydrocarbons, C6-C7, n-alkanes,

Oral	LD50	>5,000 mg/kg (rat)
Dermal	LD50	2,800-3,100 mg/kg (rat)
Inhalative	LC50/4h	25.2 ppm (rat)

- **Skin corrosion/irritation** Causes skin irritation.
- **Serious eye damage/irritation** Based on available data, the classification criteria are not met.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** May cause drowsiness or dizziness.

(Contd. on page 8)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 04.03.2022

Version number 304 (replaces version 303)

Revision: 04.03.2022

Trade name: Brake cleaning agent E-COLL

(Contd. of page 7)

- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** May be fatal if swallowed and enters airways.
- **11.2 Information on other hazards**

· Endocrine disrupting properties

None of the ingredients is listed.

SECTION 12: Ecological information**· 12.1 Toxicity****· Aquatic toxicity:****hydrocarbons, C6-C7, n-alkanes,**

LC50 (96h)	1-10 mg/L (Pimephales promelas)
EC50 (48h)	1-10 mg/L (daphnia)
NOEC (21d)	1 mg/l (daphnia)
NOEC	2.045 mg/l /28 Days (Oncorhynchus mykiss)

- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Endocrine disrupting properties**
The product does not contain substances with endocrine disrupting properties.

· 12.7 Other adverse effects**· Remark:** Toxic for fish**· Additional ecological information:****· General notes:**

Toxic for aquatic organisms
Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water
Do not allow product to reach ground water, water course or sewage system.
Also poisonous for fish and plankton in water bodies.

SECTION 13: Disposal considerations**· 13.1 Waste treatment methods:**

Containers can be recycled if completely empty; if not, dispose product/containers as dangerous waste.
Observe local regulations.

(Contd. on page 9)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 04.03.2022

Version number 304 (replaces version 303)

Revision: 04.03.2022

Trade name: Brake cleaning agent E-COLL

(Contd. of page 8)

· European waste catalogue

07 06 04* other organic solvents, washing liquids and mother liquors

*** SECTION 14: Transport information****· 14.1 UN number or ID number****· ADR, IMDG, IATA**

UN3295

· 14.2 UN proper shipping name**· ADR**UN3295 HYDROCARBONS, LIQUID, N.O.S.,
ENVIRONMENTALLY HAZARDOUS**· IMDG**HYDROCARBONS, LIQUID, N.O.S. (hydrocarbons,
C6-C7, n-alkanes,), MARINE POLLUTANT**· IATA**

HYDROCARBONS, LIQUID, N.O.S.

· 14.3 Transport hazard class(es)**· ADR****· Class**

3 (F1) Flammable liquids.

· Label

3

· IMDG**· Class**

3 Flammable liquids.

· Label

3

· IATA**· Class**

3 Flammable liquids.

· Label

3

· 14.4 Packing group**· ADR, IMDG, IATA**

II

· 14.5 Environmental hazards:**· Marine pollutant:**

Yes

Symbol (fish and tree)

· Special marking (ADR):

Symbol (fish and tree)

· 14.6 Special precautions for user

Warning: Flammable liquids.

· Hazard identification number (Kemler code):

33

· EMS Number:

F-E,S-D

(Contd. on page 10)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 04.03.2022

Version number 304 (replaces version 303)

Revision: 04.03.2022

Trade name: Brake cleaning agent E-COLL

(Contd. of page 9)

· Stowage Category	B
· 14.7 Maritime transport in bulk according to IMO instruments	Not applicable.
· Transport/Additional information:	

· ADR	
· Limited quantities (LQ)	1L
· Excepted quantities (EQ)	Code: E2 Maximum net quantity per inner packaging: 30 ml Maximum net quantity per outer packaging: 500 ml
· Transport category	2
· Tunnel restriction code	D/E

· IMDG	
· Limited quantities (LQ)	1L
· Excepted quantities (EQ)	Code: E2 Maximum net quantity per inner packaging: 30 ml Maximum net quantity per outer packaging: 500 ml
· UN "Model Regulation":	UN 3295 HYDROCARBONS, LIQUID, N.O.S., 3, II, ENVIRONMENTALLY HAZARDOUS

SECTION 15: Regulatory information

- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.
- **Directive 2012/18/EU**
- **Named dangerous substances - ANNEX I Methanol**
- **Qualifying quantity (tonnes) for the application of lower-tier requirements** 200 t
- **Qualifying quantity (tonnes) for the application of upper-tier requirements** 500 t
- **REGULATION (EC) No 1907/2006 ANNEX XVII** Conditions of restriction: 3

· DIRECTIVE 2011/65/EU on the restriction of the use of certain hazardous substances in electrical and electronic equipment – Annex II

None of the ingredients is listed.

· REGULATION (EU) 2019/1148**· Annex I - RESTRICTED EXPLOSIVES PRECURSORS (Upper limit value for the purpose of licensing under Article 5(3))**

None of the ingredients is listed.

· Annex II - REPORTABLE EXPLOSIVES PRECURSORS

None of the ingredients is listed.

· National regulations:**· Information about limitation of use:**

Employment restrictions concerning pregnant and lactating women must be observed.

· Exposure scenario(s)

Exposure scenario(s) of ingredients (if present) are available on request at:

(Contd. on page 11)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 04.03.2022

Version number 304 (replaces version 303)

Revision: 04.03.2022

Trade name: Brake cleaning agent E-COLL

sdb@ede.de

(Contd. of page 10)

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· Relevant phrases

- H225 Highly flammable liquid and vapour.
- H304 May be fatal if swallowed and enters airways.
- H315 Causes skin irritation.
- H336 May cause drowsiness or dizziness.
- H411 Toxic to aquatic life with long lasting effects.

· Department issuing SDS: Product safety department

- **Contact:** sdb@ede.de
- **Date of previous version:** 04.03.2022
- **Version number of previous version:** 303

· Abbreviations and acronyms:

ADR: Accord relatif au transport international des marchandises dangereuses par route (European Agreement Concerning the International Carriage of Dangerous Goods by Road)
IMDG: International Maritime Code for Dangerous Goods
IATA: International Air Transport Association
GHS: Globally Harmonised System of Classification and Labelling of Chemicals
EINECS: European Inventory of Existing Commercial Chemical Substances
ELINCS: European List of Notified Chemical Substances
CAS: Chemical Abstracts Service (division of the American Chemical Society)
DNEL: Derived No-Effect Level (REACH)
LC50: Lethal concentration, 50 percent
LD50: Lethal dose, 50 percent
PBT: Persistent, Bioaccumulative and Toxic
vPvB: very Persistent and very Bioaccumulative
Flam. Liq. 2: Flammable liquids – Category 2
Skin Irrit. 2: Skin corrosion/irritation – Category 2
STOT SE 3: Specific target organ toxicity (single exposure) – Category 3
Asp. Tox. 1: Aspiration hazard – Category 1
Aquatic Chronic 2: Hazardous to the aquatic environment - long-term aquatic hazard – Category 2

· * Data compared to the previous version altered.