

Within Series Adaptor 34_QMA-50-0-2/133_N

Description

Bulkhead adaptor jack/jack
QMA jack (female) / QMA jack (female)

QuickLock Interface

Interface standard
Series QMA - QMA QLF compliant



Technical Data

Electrical Data

Impedance	50 Ω	
Interface frequency max.	18 GHz	
Frequency range	DC to 2.5 GHz	2.5 to 6 GHz
Return loss	≥ 30 dB	≥ 25 dB

Mechanical Data

Number of matings	100
Weight	0.0075 kg

Environmental Data

Operating temperature	-40 °C to 85 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - QMA jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Bronze	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (ELCA)	
Gasket	VMQ (Silicone rubber)	

Interface - QMA jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Bronze	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (ELCA)	
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00067384
Mounting hole	DOU-00008860

Ordering Information

Single package	34_QMA-50-0-2/133_NE
----------------	----------------------

Within Series Adaptor
34_QMA-50-0-2/133_N