

Data Sheet

powered by RICH BAY

Dimensions:
 Top view: 44.0, 42.1, 2.0±0.05, 24.0^{+0.5}/₀, 14.0±0.2, 4.0±0.2, 16.0^{+0.5}/₀, 27.4, 30.0
 Side view: (29.6), 18.7, 17.0⁺⁰/_{1.0}, 15.0^{+0.5}/₀, 4.0±0.1, 0.8t, 12.0^{+1.0}/_{0.5}, A, (23.5)
 Front view: 28.0, 14.0±0.2, 42.2, 27.2
 Panel cut-out: R2.0, 28.0, 42.4
 Bottom view: 4.2, 2.0, 19.7, 3.3, 2.7, 4.8

XX	A
1.5	1.6
1.7	1.8
2.0	2.1
2.5	2.6

SPECIFICATION:
 1. INSULATION RESISTANCE: OVER 100MΩ 500V DC.
 2. DIELECTRIC STRENGTH: 2000V AC ONE MINUTE.
 3. Body Materil: Black Glass-Fiber Thermoplastic . UL 94V-2~0

Rating:AC 15A 250V	
Mark	Safety Regulation
cULus	cULus
Rating:AC 10A 250V	
Mark	Safety Regulation
	VDE
	CCC
	ENEC

SPECIFICATION (SWITCH) :
 1.CIRCUIT : DPST ON-OFF.
 2.CONTACT RESISTANCE : 30MΩ Max.
 3.INSULATION RESISTANCE : DC 500V 100MΩ Min.
 4.WITHSTAND VOLTAGE : AC 1000V 1 Minute.
 5.OPERATION FORCE : 800±300g.
 6.ELECTRICAL LIFE : 10,000 Cycles At Full Load.
 7.OPERATING TEMPERATURE RANGE : -25°C ~ +85°C.
 8.SOLDERING : 280°C FOR 3 Sec.
 9.DIELECTRIC STRENGTH: 2000V AC 1 Minute.
 10.BODY MATERIAL : Black Glass-Fiber Thermoplastic. UL 94V-2-0.

IMPORTANT THIS DRAWING FOR REFERENCE ONLY 注意:此圖只供參考用

	UNIT	UNIT QTY	SCALE	TOLERANCE	XXX±0.1 XX.XX±0.2 XXX.XX±0.3	PRODUCT NO.	R-301SN(B07)	REV
	mm	1	1:1					
DRAWN BY	李	APPROVED BY	羅	ID NO	11112305Q	INTERIM NO.		F
	2011.11.23 小英		2011.11.23 士凱	DESCRIPTION		NEW NO.		