

Multilevel installation terminal block; with operating slots and push-button; 2.5 mm<sup>2</sup>; N/L/PE; green-yellow lower deck; Push-in CAGE CLAMP®; 2,50 mm<sup>2</sup>; gray



https://www.wago.com/2203-6546





Color: gray

### Electrical data

Ratings per IEC/EN	
Ratings (note)	Potential – ground
Nominal voltage (III/3)	250 V
Rated impulse voltage (III/3)	4 kV
Rated current	24 A
Ratings (note) 2	Potential – potential
Rated voltage (III/3) 2	400 V
Rated surge voltage (III/3) 2	6 kV
Rated current 2	31 A
Legend (ratings)	(III / 3) ≙ Overvoltage category III / Pollution degree 3

Connection data	
Total number of connection points	5
Total number of potentials	3
Number of levels	3

Connection 1	
Connection technology	Push-in CAGE CLAMP®
Actuation type	Push-in Operating tool
Connectable conductor materials	Copper
Nominal cross-section	2.5 mm²
Solid conductor	0.25 4 mm² / 22 12 AWG
Solid conductor; push-in termination	0.75 4 mm² / 18 12 AWG
Fine-stranded conductor	0.25 4 mm² / 22 12 AWG
Fine-stranded conductor; with insulated ferrule	0.25 2.5 mm² / 22 14 AWG
Fine-stranded conductor; with ferrule; push-in termination	1 2.5 mm² / 18 14 AWG
Note (conductor cross-section)	Depending on the conductor characteri- stic, a conductor with a smaller cross- section can also be inserted via push-in termination.
Strip length	10 12 mm / 0.39 0.47 inch
Wiring direction	Front-entry wiring

https://www.wago.com/2203-6546



Connection 2

Actuation type 2 Push-in

Push-button

Physical data

Width 5.2 mm / 0.205 inch Height 109.7 mm / 4.319 inch Depth from upper-edge of DIN-rail 46.5 mm / 1.831 inch

Mechanical data

Potential marking N/L/PE DIN-35 rail Mounting type

Marking level Center/side marking

Material data

Note (material data) Information on material data can be found here

Color

Polyamide (PA66) Insulation material

Flammability class per UL94 V0

Fire load 0.307 MJ

Weight 20.2 g

Commercial data

PU (SPU) 50 Pieces

Packaging type Box Country of origin VKOrg Germany DE

**GTIN** 4066966165531

Customs tariff number VKOrg Germany 85369010000

### Approvals and certificates

### **Country specific Approvals**



Approval Standard Certificate name

C22.2 80093552 CSA

DEKRA Certification B.V.

https://www.wago.com/2203-6546



### Downloads

### **Environmental Product Compliance**

### Compliance Search

Environmental Product Compliance 2203-6546



### **Documentation**

### **Additional Information**

**Technical Section** 

pdf 2142.18 KB

### CAD/CAE-Data

### CAD data

2D/3D Models 2203-6546



### 1 Compatible products

### 1.1 Required accessories

### 1.1.1 End plate

### 1.1.1.1 End plate



Item no.: 2203-6692

End and intermediate plate; 0.8 mm thick; orange

### 1.2 Optional accessories

### 1.2.1 DIN-rail

Item no.: 210-196

### 1.2.1.1 Mounting accessories



# Item no.: 210-198

Aluminum carrier rail; 35 x 8.2 mm; 1.6 mm thick; 2 m long; unslotted; similar to EN 60715; silver-colored



### Copper carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to EN 60715; copper-colored



### Item no.: 210-197

Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; slotted; similar to EN 60715; silver-colored



### Item no.: 210-114

Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; unslotted; similar to EN 60715; silver-colored



### Item no.: 210-118

Steel carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to EN 60715; silver-colored



Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; according to EN 60715; "Hole width 18 mm; silver-colored



Steel carrier rail;  $35 \times 7.5$  mm; 1 mm thick; 2 m long; slotted; according to EN 60715; "Hole width 25 mm; silver-colored



Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; unslotted; according to EN 60715; silver-colored

https://www.wago.com/2203-6546

### 1.2.2 Ferrule

### 1.2.2.1 Ferrule

### Item no.: 216-241

Ferrule; Sleeve for 0.5 mm<sup>2</sup> / 20 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; white

Item no.: 216-263 Ferrule; Sleeve for 1 mm<sup>2</sup> / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; red



### Item no.: 216-266

Ferrule; Sleeve for 2.5 mm<sup>2</sup> / AWG 14; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228. Part 4/09.90: blue

### Item no.: 216-242

Ferrule; Sleeve for 0.75 mm<sup>2</sup> / 18 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray



### Item no.: 216-244

Ferrule: Sleeve for 1.5 mm<sup>2</sup> / AWG 16: insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black

Ferrule; Sleeve for 0.75 mm<sup>2</sup> / 18 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray



### Item no.: 216-264

Ferrule: Sleeve for 1.5 mm<sup>2</sup> / AWG 16: insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black

Ferrule; Sleeve for 1 mm<sup>2</sup> / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; red



### Item no.: 216-246

Ferrule: Sleeve for 2.5 mm<sup>2</sup> / AWG 14: insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; blue

### 1.2.3 Installation

Item no.: 2009-304

### 1.2.3.1 Mounting accessories



Busbar carrier; not suitable for use as end

stop; for DIN 35 rail; 1.5 mm thick; blue





Busbar carrier; with end stop function and detachable separator plate; for DIN 35 rail; 7.5 mm thick; blue



### Item no.: 709-169

Cover carrier; Type 3; gray



### Item no.: 709-156

Cover; Type 3; suitable for cover carrier, type 3; 1 m long; transparent

### 1.2.4 Insulation stop

### 1.2.4.1 Insulation stop





Item no.: 2002-423/000-006

Continuous jumper; from 1 to 3; insulated;

### Item no.: 2002-171 Insulation stop; 0.25 - 0.5 mm<sup>2</sup>; 5 pieces/ strip; light gray



### Item no.: 2002-172

Insulation stop; 0.75 - 1 mm<sup>2</sup>; 5 pieces/ strip; dark gray

### 1.2.5 Jumper

### 1.2.5.1 Jumper



Continuous jumper; 2-way; insulated; light gray



### Item no.: 2002-410/000-006

Item no.: 2002-406/020-000 Delta jumper; insulated; light gray

Item no.: 2002-402/000-006

Jumper; 2-way; insulated; blue



### Item no.: 2002-402

blue

Jumper; 2-way; insulated; light gray

Jumper; 10-way; insulated; blue



### Item no.: 2002-423

Continuous jumper; from 1 to 3; insulated; light gray



### Item no.: 2002-423/000-005

Continuous jumper; from 1 to 3; insulated; red



Item no.: 2002-410

Jumper; 10-way; insulated; light gray



### Item no.: 2002-410/000-005

Jumper; 10-way; insulated; red



### Item no.: 2002-402/000-005

Jumper; 2-way; insulated; red

Item no.: 2002-403/000-006

Jumper; 3-way; insulated; blue

https://www.wago.com/2203-6546



### 1.2.5.1 Jumper









Item no.: 2002-403

Jumper; 3-way; insulated; light gray

Item no.: 2002-403/000-005 Jumper; 3-way; insulated; red Item no.: 2002-404/000-006 Jumper; 4-way; insulated; blue Item no.: 2002-404

Jumper; 4-way; insulated; light gray



Item no.: 2002-404/000-005

Item no.: 2002-405/000-006

Jumper; 4-way; insulated; red

Jumper; 5-way; insulated; blue

Item no.: 2002-405

Jumper; 5-way; insulated; light gray

Item no.: 2002-405/000-005 Jumper; 5-way; insulated; red



Item no.: 2002-406/000-006

Jumper; 6-way; insulated; blue

Item no.: 2002-406

Jumper; 6-way; insulated; light gray

Item no.: 2002-406/000-005

Jumper; 6-way; insulated; red

Item no.: 2002-407/000-006 Jumper; 7-way; insulated; blue



Item no.: 2002-407 Jumper; 7-way; insulated; light gray Item no.: 2002-407/000-005

Item no.: 2002-408/000-006

Jumper; 8-way; insulated; blue

Item no.: 2002-408

Jumper; 8-way; insulated; light gray



Item no.: 2002-408/000-005 Jumper; 8-way; insulated; red Item no.: 2002-409/000-006

Jumper; 7-way; insulated; red

Item no.: 2002-409

Jumper; 9-way; insulated; light gray



Jumper; 9-way; insulated; blue

Jumper; 9-way; insulated; red



Item no.: 2002-440

Jumper; from 1 to 10; insulated; light gray

Item no.: 2002-433

Jumper; from 1 to 3; insulated; light gray

Item no.: 2002-434

Jumper; from 1 to 4; insulated; light gray

Item no.: 2002-435

Jumper; from 1 to 5; insulated; light gray



Item no.: 2002-436

Jumper; from 1 to 6; insulated; light gray

Item no.: 2002-437

Jumper; from 1 to 7; insulated; light gray

Item no.: 2002-438

Jumper; from 1 to 8; insulated; light gray

SECTION AND SECTION AS A SECTIO

Item no.: 2002-439

Jumper; from 1 to 9; insulated; light gray



Item no.: 2002-480

Staggered jumper; 10-way; insulated; light gray

NINE CONTRACTOR OF THE PERSON OF THE PERSON

Item no.: 2002-481 Staggered jumper; 11-way; insulated; light gray

light gray

gray

Item no.: 2002-482 Staggered jumper; 12-way; insulated;

Item no.: 2002-473/011-000

Staggered jumper; 2-way; from 1 to 3; insulated; light gray



Item no.: 2002-472 Staggered jumper; 2-way; insulated; light gray

Item no.: 2002-473 Staggered jumper; 3-way; insulated; light gray

Item no.: 2002-475/011-000 Staggered jumper; 3-way; insulated; light Item no.: 2002-474

Staggered jumper; 4-way; insulated; light gray



Staggered jumper; 5-way; insulated; light

Item no.: 2002-476 Staggered jumper; 6-way; insulated; light

Item no.: 2002-477



Staggered jumper; 7-way; insulated; light gray

Item no.: 2002-478

Staggered jumper; 8-way; insulated; light gray



gray

Item no.: 2002-479

Item no.: 2002-475

gray

Staggered jumper; 9-way; insulated; light gray

Item no.: 2002-477/011-000 Staggered jumper; insulated; light gray Item no.: 2002-479/011-000 Staggered jumper; insulated; light gray

Item no.: 2002-481/011-000 Staggered jumper; insulated; light gray



Item no.: 2002-405/011-000 Star point jumper; 3-way; insulated; light gray

Item no.: 210-103 Wire commoning chain; insulated; black

Item no.: 210-123 Wire commoning chain; insulated; blue

https://www.wago.com/2203-6546

# N/AGO

### 1.2.6 Marking

### 1.2.6.1 Group marker carrier



Ī

Ī

Item no.: 2009-191

Group marker carrier; gray

Item no.: 2009-192
Group marker carrier; gray

<u>Item no.: 2009-193</u> Group marker carrier; gray

### 1.2.6.2 Marker

### Item no.: 2009-145/000-006

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; blue

### Item no.: 2009-145/000-007

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; gray

### Item no.: 2009-145/000-023

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; green

### Item no.: 2009-145/000-012

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; orange

### Item no.: 2009-145/000-005

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; red

## Item no.: 2009-145/000-024 Mini-WSB Inline: for Smart Pr

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; violet

### Item no.: 2009-145

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white

### Item no.: 2009-145/000-002

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; yellow



### Item no.: 248-501/000-006

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; blue

### Item no.: 248-501/000-007

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; gray

Mini-WSB marking card; as card; not

### Item no.: 248-501/000-023

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; green

### Item no.: 248-501/000-017

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; light green



### Item no.: 248-501/000-012

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; orange

# stretchable; plain; snap-on type; red

Item no.: 248-501/000-005

### Item no.: 248-501/000-024

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; violet

### Item no.: 248-501

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; white



### Item no.: 248-501/000-002

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; yellow

# Item no.: 793-5501/000-006

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; blue

### Item no.: 793-5501/000-014

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; brown

### Item no.: 793-5501/000-007

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; gray



### Item no.: 793-5501/000-017

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; green

## Item no.: 793-5501/000-023

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; light green

### Item no.: 793-5501/000-012

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; orange

### Item no.: 793-5501/000-005

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; red



Item no.: 793-5501/000-024

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; violet

### Item no.: 793-5501

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; white

### Item no.: 793-5501/000-002

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; yellow

### Item no.: 793-501/000-006

WMB marking card; as card; not stretchable; plain; snap-on type; blue



### Item no.: 793-501/000-007

WMB marking card; as card; not stretchable; plain; snap-on type; gray

# Item no.: 793-501/000-023

WMB marking card; as card; not stretcha-

### Item no.: 793-501/000-017

WMB marking card; as card; not stretchable; plain; snap-on type; light green

### # 100 mm

### Item no.: 793-501/000-012

WMB marking card; as card; not stretchable; plain; snap-on type; orange



# Item no.: 793-501/000-005

WMB marking card; as card; not stretchable; plain; snap-on type; red

4

# - - 700 504/0

ble; plain; snap-on type; green

### Item no.: 793-501/000-024

WMB marking card; as card; not stretchable; plain; snap-on type; violet

4



### Item no.: 793-501

WMB marking card; as card; not stretchable; plain; snap-on type; white

4



### Item no.: 793-501/000-002

WMB marking card; as card; not stretchable; plain; snap-on type; yellow



### Item no.: 2009-115/000-006

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; blue

### Item no.: 2009-115/000-007

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; gray

Item no.: 2009-115/000-023

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; green

Item no.: 2009-115/000-017 WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; light green



Version 13.04.2022

https://www.wago.com/2203-6546



### 1.2.6.2 Marker

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; red

Item no.: 2009-115/000-024

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; violet

Item no.: 2009-115

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white



WMB-Inline; for Smart Printer; 1500 pie-

ces on roll; stretchable 5 - 5.2 mm; plain;

Item no.: 2009-115/000-002

snap-on type; orange

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snapon type; yellow

### 1.2.6.3 Marker carrier



Item no.: 2009-198 Adaptor; gray

### 1.2.6.4 Marking strip

Item no.: 2009-110

Marking strips; for Smart Printer; on reel; not stretchable; plain; snap-on type; white

### 1.2.7 Push-in type wire jumper

### 1.2.7.1 Jumper



Push-in type wire jumper; 1.5 mm²; insulated; 110 mm long; black

Item no.: 2009-414/000-005

Push-in type wire jumper; 1.5 mm²; insulated; 110 mm long; black

Item no.: 2009-416

Push-in type wire jumper; 1.5 mm<sup>2</sup>; insulated; 250 mm long; black

Item no.: 2009-414/000-006

Push-in type wire jumper; insulated; 110 mm long; black



<u>Item no.: 2009-412</u>

Push-in type wire jumper; insulated; 60 mm long; black

### 1.2.8 Test and measurement

### 1.2.8.1 Testing accessories

Item no.: 2009-174

Test plug adapter; for 4 mm Ø test plugs; for testing TOPJOB®S rail-mounted terminal blocks; gray

Item no.: 210-136

Test plug; 2 mm Ø; with 500 mm cable;

Item no.: 2009-182

Testing tap; for max. 2.5 mm²; tool-free connection for individual test wires 0.08 - 2.5 mm; gray

https://www.wago.com/2203-6546



### 1.2.9 Tool

### 1.2.9.1 Operating tool



#### Item no.: 210-658

Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; angled; short; multicoloured

#### 2010 720

Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; multicoloured

#### ,

Operating tool; Blades: 3.5 x 0.5 mm and 2.5 x 0.4 mm; for TOPJOB®S installation terminal blocks

#### Itom no : 2000 210

Operating tool; Blades: 3.5 x 0.5 mm and 5.5 x 0.8 mm; for TOPJOB®S installation terminal blocks; green

### Installation notes

### Conductor termination



All conductor types at a glance



Conductor termination



Inserting a conductor via push-in termination.

Solid conductors with cross-sections from either one size above, or up to two sizes below, the rated cross-section can be simply pushed in – no tools needed.




Inserting a conductor via operating tool. Connecting fine-stranded conductors without ferrules, or small cross-sectional conductors that cannot be pushed in, is performed similarly to the original CAGE CLAMP® – just use an operating tool.

### Commoning



Commoning two potentials in one single jumper slot via extremely slim staggered jumpers.



Removing a staggered jumper: Insert the operating tool between the staggered jumpers, then lift up the jumper.



The 1-to-3 adjacent jumper for continuous commoning enables every other terminal block to be commoned. For example, positive and negative potentials can be accommodated alongside each other.



Adjacent Jumpers for Continuous Commoning (2002-400)

### **Testing**



Testing

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com

Page 8/8 Version 13.04.2022