

Potential bridge - FBS-PV UT - 3047358


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Vertical potential bridge, to connect the upper and lower level



Key Commercial Data

Packing unit	50 STK
GTIN	 4 046356 094733
GTIN	4046356094733
Custom tariff number	85389099

Technical data

Technical data

Color	black
Material	Copper
Number of positions	1
Maximum load current	22 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.)
Flammability rating according to UL 94	V0
Ambient temperature (operation)	125 °C

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Approvals

Approvals

Potential bridge - FBS-PV UT - 3047358


Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		EAC-Zulassung
-----	---	---------------
