

A23d DIN 41612 IDC TYPE MALE TRIPLE ROW (A+C)

PITCH: 2.54mm * 2.54mm


SPECIFICATIONS

Material


Insulator : PBT, glass reinforced, rated UL 94V-0
 Contact : Phosphor Bronze

Electrical

Current Rating : 1 Amp
 Contact Resistance : 30 mΩ max.
 Insulation Resistance : 3000 MΩ min.
 Dielectric Withstanding Voltage : 500V AC for 1minute
 Operating Temperature : -40°C to +105°C
 ▶ Terminated with L01-1.27mm pitch flat ribbon cable.
 ▶ Mating Suggestion : A23b series.



| POSITION | A | B | C | D |
|----------|----|----|-------|------|
| 32(A+C) | 55 | 50 | 38.10 | 44.8 |
| 64(A+C) | 95 | 90 | 78.74 | 85.4 |



How to order: A23d - 1 - 2 - 3 - 4 - 5 - G(RoHS)

| 1.NO. OF CONTACT | 2.CONTACT TYPE | 3.CONTACT MATERIAL | 4.CONTACT PLATING | 5.INSULATOR COLOR |
|------------------|----------------|--------------------|---|-------------------|
| 32 64 | M: MALE | B: PHOSPHOR BRONZE | T: TIN PLATED S: SELECTIVE G: GOLD FLASH A: 5u" INCH GOLD B: 10u" INCH GOLD C: 15u" INCH GOLD D: 30u" INCH GOLD | 2. GREY |