

SSRC clamping holder, positive, right

For longitudinal turning with CC indexable insert

ATORN[®]

Application

For longitudinal turning with CC indexable insert, 80°

Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 75°, tip angle 90°, clearance angle 7°

Advantage

- Robust geometry for longitudinal turning
- positive body geometry ensures low cutting forces
- Very good surface quality for medium infeed and finishing



Art. no.	17830 802
ISO name	SCRC R/L 1010 E06
Shaft height	10 mm
Shank width	10 mm
Length	70 mm
Length of head	14 mm
Programming size	11 mm
Suitable for indexable inserts	CC.. 0602..
Tool design	Right

EAN-Code

4050293562644