

Sling swivels, hoist rings

CARTEC

Application:

Attachment point for lifting loads.

Execution:

- Suitable for secure raising of loads according to Machinery Directive
- 2006/42/EC
- constructed, tested and certified according to GS-OA 15-04 - EN 1677
- DGUV certification
- Magnaflux crack tested to 100%
- can be rotated 360°

Advantage:

- load direction 90°, with minimal space requirement
- Durable corrosion protection of screw
- designed for a load of 20,000 load changes



Art. no.	77239 136
Brand	CARTEC
Manufacturer Part Number	C806X36T07
Thread dimension	M36
Load-carrying capacity	7 t
External width	109 mm
Internal width	66 mm
Width of support plate	60 mm
Bracket diameter	22.5 mm
Usable thread length	50 mm
Bracket height	145 mm
Width across flats	50 mm
Distance between lower edge of retainer holder and retainer	55 mm
Gross Weight	3.300 kg
Product Group	775

EAN

8013429871139