

3823HL.B




Models Versions

Models	Versions
3823HL.B	black w/foam
3823HL.BE	black empty
3823HL.O	orange w/foam
3823HL.OE	orange empty
3823HL.G	mil. green w/foam
3823HL.GE	mil. green empty
3823HL.D	des. sand w/foam
3823HL.DE	des. sand empty
3823HL.N	blue navy w/foam
3823HL.NE	blue navy empty
3823HL.Y	yellow w/foam
3823HL.YE	yellow empty

Medium size watertight case, with increased depth, injected with proprietary copolymer PP that makes it more resistant and lightweight than other similar products. IP67 and MIL Stan certified to be resistant to impact, liquids, shocks. Ideal container for documents, laptops, emergency kits, optical equipment and electronic devices, water sport equipments and more.

- Metal reinforced padlock holes
- Single block high performance injected O-ring
- Automatic pressure valve
- Soft rubber handle grip
- Removable lid
- Anti-tilt support
- Certified to grant constant performances between -33°C and +90 °C.
- Six standard colors available

Technical Features		L	W	D		
		Length	Width	Depth	Lid	Base
Internal dim.	mm	380	270	230	57	173
External dim.	mm	420	340	252		
Weight empty		Kg 2,82				
Weight w/foam		Kg 3,39				
Weight w/---		Kg ---				
Volume		lt 23,6				
Buoyancy		Kg/max 16				
Temp. rating		°C min -33 max +90				



Certifications	* Designed to comply with:
	2002/95/EC Conformity with the Directive 2002/95/EC
	DEF STAN 81-41 (level J)
	IP67 Dustproof - Waterproof
	STANAG 4280 (edition 2)

* Pending certification release