

226781-1 ✓ ACTIVE

COAXICON

TE Internal #: 226781-1

Rack & Panel Contacts, Socket, 15 Shell Size, Coax, Gold, Wire & Cable

[View on TE.com >](#)



Connectors > PCB Connectors > Backplane Connectors > Rack & Panel Backplane > Rack & Panel Contacts



Contact Type: **Socket**

Rack & Panel Connector Contact Size: **15**

Rack & Panel Connector Contact Style: **Coax**

Contact Mating Area Plating Material: **Gold**

Connector & Contact Terminates To: **Wire & Cable**

Features

Product Type Features

Compatible With RF Cable Type	RG 188, RG 316
Connector & Contact Terminates To	Wire & Cable

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Contact Shell Base Material	Beryllium Copper
Contact Removal Style	Rear Release
Shell Plating Material	Gold

Contact Features

Contact Mating Area Plating Material Thickness	1.27 μm[50 μin]
Contact Orientation	Straight
Ferrule Plating Material	Tin
Crimp Type	O Crimp
Contact Base Material	Beryllium Copper
Contact Type	Socket
Rack & Panel Connector Contact Size	15
Rack & Panel Connector Contact Style	Coax
Contact Mating Area Plating Material	Gold

Termination Features



Termination Method to Wire & Cable

Crimp

Mechanical Attachment

Contact Retention Type Within Housing

Snap-In

Packaging Features

Packaging Method

Package

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2021 (211)
 Candidate List Declared Against: JUN 2020 (209)
 SVHC > Threshold:
 Pb (4% in Contact/Component)

Article Safe Usage Statements:
 Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



Documents

Product Drawings

ARINC SIZE 15 SOCKET

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_226781-1_F.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_226781-1_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_226781-1_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[ARINC 600 Next Generation Receptacle Connector](#)

English

Product Specifications

[Product Specification](#)

English

[COAXICON Contacts for use in RM or RME Connectors](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[ARINC 404 RACK-AND-PANEL CONNECTORS SERIES R, RM, RME, M, MM, MME](#)

English

[Instruction Sheet \(U.S.\)](#)

English

[AMP* COAXICON* CONTACTS FOR USE IN RM \(ARINC SPEC. 404\) OR RME \(MIL-C-](#)

English