

Levelling Feets 340


Material Version 340: Steel, zinc-plated, chromated.
 Rubber pad: NBR, hardness 80° +/-5° Shore A, black.

Type AG: Steel zinc-plated, with rubber pad.

Material Version 340.5: Base: Stainless steel 1.4301 (AISI 304).
 Bolt: Stainless steel 1.4305 (AISI 303).
 Rubber pad: NBR, hardness 80° +/-5° Shore A, black.

Type NG: Stainless Steel, with rubber pad.

STAINLESS



Ordering Details: e.g.: Product No. 655 741 00 Levelling Foot 340 Type AG, 50 x M16 x 75

Product No. Version 340 Zinc-plated	Product No. Version 340.5 Stainless Steel	d ₁ mm	d ₂ mm	l ₁ mm	l ₂ mm	l ₃ mm	approx.			sw ₁ mm	sw ₂ mm	Static Load*		Weight g
							l ₄ mm	l ₅ mm	l ₆ mm			Vers. 340 kN	Vers. 340.5 kN	
655 741 00	655 997 41	50	M16	75	29	25,5	14,5	11	3,5	8	12	16	28	193
655 742 00	655 997 42	50	M16	100	29	25,5	14,5	11	3,5	8	12	16	28	270
655 743 00	655 997 43	50	M16	125	29	25,5	14,5	11	3,5	8	12	16	28	290
655 744 00	655 997 44	50	M16	150	29	25,5	14,5	11	3,5	8	12	16	28	310
655 751 00	655 997 51	60	M16	75	30	26	16	12	4	8	12	16	28	280
655 752 00	655 997 52	60	M16	100	30	26	16	12	4	8	12	16	28	300
655 753 00	655 997 53	60	M16	125	30	26	16	12	4	8	12	16	28	320
655 754 00	655 997 54	60	M16	150	30	26	16	12	4	8	12	16	28	340
655 761 00	655 997 61	80	M16	75	32	27	18	13	5	8	12	12	19	400
655 762 00	655 997 62	80	M16	100	32	27	18	13	5	8	12	12	19	450
655 763 00	655 997 63	80	M16	125	32	27	18	13	5	8	12	12	19	470
655 764 00	655 997 64	80	M16	150	32	27	18	13	5	8	12	12	19	500
655 765 00	655 997 65	80	M20	75	33	28	18	13	5	10	15	12	19	490
655 766 00	655 997 66	80	M20	100	33	28	18	13	5	10	15	12	19	525
655 767 00	655 997 67	80	M20	125	33	28	18	13	5	10	15	12	19	570
655 768 00	655 997 68	80	M20	150	33	28	18	13	5	10	15	12	19	630
655 771 00	655 997 71	100	M20	75	35	29	20	14	6	10	15	11	17	610
655 772 00	655 997 72	100	M20	100	35	29	20	14	6	10	15	11	17	660
655 773 00	655 997 73	100	M20	125	35	29	20	14	6	10	15	11	17	680
655 774 00	655 997 74	100	M20	150	35	29	20	14	6	10	15	11	17	780
655 775 00	655 997 75	100	M24	100	38	32	20	14	6	12	19	11	17	840
655 776 00	655 997 76	100	M24	125	38	32	20	14	6	12	19	11	17	890
655 777 00	655 997 77	100	M24	150	38	32	20	14	6	12	19	11	17	940

* Static Load

The static load is limited by any deformation of the steel base (3 mm thick). The bolt has a strength of min. 500 N/mm².

The load figures specified in the table above are based on a series of tests in which a vertical load was applied on the base. At the values stated in the table, a slight deformation of the base might occur.

General

A feature of the leveling feet is the inlayed rubber pad in the steel base, fixed by a screw.

The bolt can be adjusted either at the hexagon at the upper end or at the spanner flats at the bottom end.