

Note: This datasheet may be out of date. Please download the latest datasheet of BLM21SP601SN1# from the official website of Murata Manufacturing

Co., Ltd.

https://www.murata.com/en-eu/products/productdetail?partno=BLM21SP601SN1%23

BLM21SP601SN1#

"#" indicates a package specification code.







< List of part numbers with package codes >

BLM21SP601SN1D BLM21SP601SN1J BLM21SP601SN1B




Appearance & Shape



Features





The chip ferrite beads BLM series is designed to function nearly as a resistor at noise frequencies, which greatly reduces the possibility of resonance and leaves signal wave forms undistorted.

BLM series is effective in circuits without stable ground lines because BLM series does not need a connection to ground.

The nickel barrier structure of the external electrodes provides excellent solder heat resistance. BLM21SP series can be used in high current circuits due to its low DC resistance.



Other Usage

For general



Packaging Information

Packaging	Specifications	Minimum Order Quantity
D	180mm Paper Tape	4000
J	330mm Paper Tape	10000
В	Bulk(Bag)	1000

1 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/

Last updated :2019/09/11

$\underline{ Please \ download \ the \ latest \ data sheet \ of \ BLM21SP601SN1\# \ from \ the \ of ficial \ website \ of \ Murata \ Manufacturing}$ Co., Ltd. https://www.murata.com/en-eu/products/productdetail?partno=BLM21SP601SN1%23

BLM21SP601SN1#

"#" indicates a package specification code.

Note: This datasheet may be out of date



Shape	SMD
Size Code (in mm)	2012
Size Code (in inch)	0805
Length	2.0mm
Length Tolerance	±0.2mm
Width	1.25mm
Width Tolerance	±0.2mm
Thickness	0.85mm
Thickness Tolerance	±0.2mm
Impedance (at 100MHz)	600Ω
Impedance (at 100MHz) Tolerance	±25%
Rated Current (at 85°C)	2.3A
Rated Current (at 125°C)	1.5A
DC Resistance(max.)	0.06Ω
Operating Temperature Range	-55°C to 125°C
Mass(typ.)	0.01g
Number of Circuit	1

2 of 3

Attention

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/


^{1.} This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

https://www.murata.com/en-eu/products/productdetail?partno=BLM21SP601SN1%23

BLM21SP601SN1#


"#" indicates a package specification code.






In operating temperature exceeding +85°C, derating of current is necessary for BLM21SP series. Please apply the derating curve shown in chart according to the operating temperature.

Derating of Rated Current



Impedance-Frequency Characteristics





Equivalent Circuit

3 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/

Last updated :2019/09/11