

knurl cutter HSSE-PM 30°

For use on knurl cutter tools 19100



Application:

For producing straight knurls in accordance with DIN 82 RAA (in holders with 1 knurl) in steel, stainless steel, non-ferrous metals and cast iron material groups.

Execution:

- HSSE PM 30°, ground tooth flanks, uncoated

Advantage:

- High precision with ground teeth and good cutting performance, even with difficult materials
- Very good surface quality and long service life with high-quality HSSE-PM cutting material



Art. no.	19171 005
Brand	QUICK
Manufacturer Part Number	42000172
Knurling wheel diameter	8.9 mm
Partition	0.5 mm
Machining direction	Left
Surface	Uncoated
Gross Weight	0.002 kg
Product Group	192