

## Type ER screw tap collets

GERC-GBDD DIN ISO 15488-A with square drive for CENTRO P and SYNCHRO T seal for internal cooling and spray nozzle

**FAHRION®**  
FAIR BEYOND PRECISION

### Application:


For thread cutting with Centro P precision collet chucks or with synchronous tapping chuck.

### Execution:

- With square drive for positive engagement of the screw tap.
- For internal cooling (can be used up to 120 bar).
- Concentricity < 10 µm.
- Concentricity less than 10 µm.

### Delivery:

1x type ER screw tap collet chuck set.



|                                 |                                 |
|---------------------------------|---------------------------------|
| <b>Art. no.</b>                 | <b>23323 771</b>                |
| <b>Brand</b>                    | FAHRION                         |
| <b>Manufacturer Part Number</b> | 13833010450                     |
| <b>Clamping diameter</b>        | 4.5 mm                          |
| <b>Square width</b>             | 3.55 mm                         |
| <b>Collet type</b>              | 4031E GERC16-GBDD               |
| <b>Outer diameter</b>           | 16.7 mm                         |
| <b>Length</b>                   | 27.5 mm                         |
| <b>Coolant supply</b>           | Inner cooling and spray nozzles |
| <b>Gross Weight</b>             | 0.025 kg                        |
| <b>Product Group</b>            | 235                             |

### EAN

4054631177545