

Drawer cabinets

Stationary

LISTA
making workspace work

Application:

For day-to-day heavy-duty use in workshops

Execution:

- All drawers with full extension
- Individual drawer lock as standard feature to prevent the cabinet from tipping over
- Perforated, slotted drawers provide a secure hold
- Very robust construction for a wide variety of applications and very demanding requirements

Advantage:

- Optimum wall height to keep items from falling out and getting lost
- Folding handle strips for simple, clean and protected labelling
- High quality - made in Germany and Swiss-made
- Runs perfectly smoothly and easily due to the lack of crossbars on the differential extension slide
- Full extension - clear overview and optimal access



Art. no.	50301 687
Brand	LISTA
Manufacturer Part Number	78.803.010
Number of drawers	6 PCS
Height	850 mm
Width	1023 mm
Depth	725 mm
Height x width x depth	850 x 1023 x 725 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	900 x 600 mm
Load-carrying capacity per drawer	200 kg
Drawer lock	Standard
Drawer front height	2 x 75 mm, 2 x 100 mm, 1 x 150 mm, 1 x 250 mm
Cabinet colour	Light blue RAL 5012
Colour of front	Light blue RAL 5012
Opening/closing system	Code Lock
Clear height	750 mm
LISTA unit	54 x 36 E
Gross Weight	165.000 kg
Product Group	5AN