



LITHIUM BATTERY

UHE-ER26500-H

C size bobbin cell (energy type)

Technical Datasheet

The ABLE Advantage

Better technology. Our batteries enable us to design leading-edge solutions for the world's most demanding applications.



SPECIFICATIONS

Part No	UHE-ER26500-H
Alternative models	LS26500/TL4920/SB-C01/SB-C02
Voltage Range	2.0 to 3.7 V
Nominal Voltage	3.6 V
Nominal Capacity	9Ah @ 2mA to 2.0 V @ 23° C
Max. Discharge	200 mA continuous
Pulse Capability	Up to 400 mA Varies according to pulse characteristics, temperature, cell history and the application. Consult ABLE.
Typical Weight	54 grams
Operating Temp	-55° C to 85° C Operation at extreme ranges (temperature or current) may lead to reduced capacity and lower voltage readings at beginning of pulses. Consult with Able.
Storage Temp	30° C MAX, for additional conditions, please consult ABLE.
Exterior/Housing	Stainless steel
Terminals/Connector	Radial tabs/ radial pins/axial leads/flying leads
Safety	AL-MSDS/RD-002.
Transportation	Class 9 – see note 1
Note 1	For a complete description of transportation regulations and definitions of the transportation classifications "Excepted" and "Class 9," refer to the Ultralife web site at www.ultralifecorporation.com .


FEATURES

- High and stable operating voltage
- Superior drain capability
- Low self-discharge rate (less than 2% after 1 year of storage at 23° C)
- Hermetic glass-to-metal sealing
- Non-flammable electrolyte

APPLICATIONS

- Radio communication and other military applications
- Alarms and security systems
- Transmitters
- GPS
- LED lighting applications
- Others

DIMENSIONS



Unit:mm

PERFORMANCE GRAPHS

