

AMP

TE Internal #: 720725-1

Portable Crimp Tools, Premium Crimp Tooling, Not Releasable,
Not Adjustable, Fixed In Tool, TE Product Specification (114-),
Battery / Manual

[View on TE.com >](#)

Application Tooling > Portable Crimp Tools

Tool Grade: **Premium Crimp Tooling**Ratchet Configuration: **Not Releasable, Not Adjustable**Die Sets Type: **Fixed In Tool**Specification Type: **TE Product Specification (114-)**TE Certification: **Yes – Certificate Included**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Premium Crimp Tooling
Ratchet Configuration	Not Releasable, Not Adjustable
Die Sets Type	Fixed In Tool
Specification Type	TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Manual
Tooling Type	Double Action Hand Tool

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free











Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 60279-2 FASTON 250 14-18AWG TPBR</p>	 <p>TE Part # 42241-2 FF 250 TAB 18-14 AWG .032 TPBR</p>	 <p>TE Part # 170153-2 FF 250 TAB 18-14AWG PTBR LP</p>	 <p>TE Part # 42241-1 FF 250 TAB 18-16AWG BR</p>
 <p>TE Part # 160450-2 FF 250 TAB 18-14AWG TPPB</p>	 <p>TE Part # 160457-2 FF 250 TAB 18-14AWG TPPB</p>	 <p>TE Part # 42741-2 FASTON 250 PIGGY-BACK REC 18-14 AWG TPBR</p>	 <p>TE Part # 42098-1 FF 250 TAB 18-14 AWG .032 BR</p>
 <p>TE Part # 42460-1 FF 250 TAB 18-14AWG BR</p>	 <p>TE Part # 42098-2 FF 250 TAB 18-14 AWG PTPB</p>	 <p>TE Part # 160457-3 FF 250 TAB 18-14AWG PB SILVER PL</p>	 <p>TE Part # 42460-2 FF 250 TAB 18-14AWG TPBR</p>




TE Part # 170340-1
FF 250 TAB 20-14AWG BR WITHOUT LATCH



TE Part # 170151-2
FF 250 TAB 18-14AWG TPBR



TE Part # 170092-4
FF 250 REC 18-14AWG TPBR REREELING



TE Part # 280081-2
FF 250 TAB 0.8-2MM2 TPBR



TE Part # 170340-3
FF 250 TAB 20-14AWG TPBR WITHOUT LATCH



TE Part # 170030-1
FF 250 TAB 20-14AWG BR



TE Part # 280098-2
FF 250 REC 1-2.5MM2 TPPB



TE Part # 170030-2
FF 250 TAB 20-14AWG TPBR

Customers Also Bought




TE Part #1-917659-8
DYNAMIC 3200 REC AND TAB HSG



TE Part #917511-2
DYNAMIC 3000 CONTACT



TE Part #1276716-1
EXT-TOOL FOR DYNAMIC D2 CONN



TE Part #170153-2
FF 250 TAB 18-14AWG TPBR LP



TE Part #170340-1
FF 250 TAB 20-14AWG BR WITHOUT LATCH



TE Part #170108-4
FF 250 REC 18-14AWG TPBR LP



TE Part #1-456402-4
CRIMPER WIRE .055 F



TE Part #1-456407-3
CRIMPER, WIRE .100 F



TE Part #170289-1
MIC REC LP

Documents



Datasheets & Catalog Pages

[CERTI-CRIMP II-Premium-August-1-1773864-7](#)

English

[Crimp Term Whitepaper-Use the Right Tool 1-1773953-1](#)

English

[Bottoming Dies](#)

English

[CRIMPING WHERE FORM MEETS FUNCTION](#)

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

Japanese

[Instruction Sheet \(non U.S.\)](#)

Japanese