



ATEX reduction adaptors, metric-metric


ATEX Reduzierungen, metrisch-metrisch



Form A



Form B



Explosion protection: II 2 G Ex e II
II 2 D Ex tD A21 IP66
Certificates: PTB 04 ATEX 1040 X
Protection class to EN 60 529: IP 66
Temperature range: -20°C to 70°C
Material: Polyamide, reinforced glass fibre

Explosionsschutz: II 2 G Ex e II
II 2 D Ex tD A21 IP66
Bescheinigungen: PTB 04 ATEX 1040 X
Schutzart gemäß EN 60 529: IP 66
Einsatztemperatur: -20°C bis 70°C
Material: Polyamid, glasfaserverstärkt

Type	WISKA No. RAL 9005 ■ 100.						TL	Form
			mm	mm	mm	mm	mm	
EX-KRM 16/12	64720	100	M 16x1,5	M 12x1,5	9	20	27	A
EX-KRM 20/12	64721	100	M 20x1,5	M 12x1,5	9	24	16	B
EX-KRM 20/16	64722	100	M 20x1,5	M 16x1,5	9	24	27	A
EX-KRM 25/12	64723	100	M 25x1,5	M 12x1,5	10	29	17	B
EX-KRM 25/16	64724	100	M 25x1,5	M 16x1,5	10	29	17	B
EX-KRM 25/20	64725	100	M 25x1,5	M 20x1,5	10	29	17	B
EX-KRM 32/16	64726	50	M 32x1,5	M 16x1,5	12	36	19	B
EX-KRM 32/20	64727	50	M 32x1,5	M 20x1,5	12	36	19	B
EX-KRM 32/25	64728	50	M 32x1,5	M 25x1,5	12	36	19	B
EX-KRM 40/20	64729	25	M 40x1,5	M 20x1,5	12	46	19	B
EX-KRM 40/25	64730	25	M 40x1,5	M 25x1,5	12	46	19	B
EX-KRM 40/32	64731	25	M 40x1,5	M 32x1,5	12	46	19	B
EX-KRM 50/20	64732	5	M 50x1,5	M 20x1,5	14	55	21	B
EX-KRM 50/25	64733	5	M 50x1,5	M 25x1,5	14	55	21	B
EX-KRM 50/32	64734	5	M 50x1,5	M 32x1,5	14	55	21	B
EX-KRM 50/40	64735	5	M 50x1,5	M 40x1,5	14	55	21	B
EX-KRM 63/20	64736	5	M 63x1,5	M 20x1,5	15	68	22	B
EX-KRM 63/25	64737	5	M 63x1,5	M 25x1,5	15	68	22	B
EX-KRM 63/32	64738	5	M 63x1,5	M 32x1,5	15	68	22	B
EX-KRM 63/40	64739	5	M 63x1,5	M 40x1,5	15	68	22	B
EX-KRM 63/50	64740	5	M 63x1,5	M 50x1,5	15	68	22	B

KUNSTSTOFF
PLASTIC

MEMBRAN
MEMBRANE

MESSING
BRASS

DIN 89280

EDELSTAHL
STAINL. STEEL

EMV
EMC

ATEX
ATEX

VentilGLAND

DICHTUNGEN
SEALINGS

WERKZEUGE
TOOLS

TECHNIK
TECHNICS

INDEX
INDEX