



Part Number : [190030105](#)


Product Description : InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm²), Continuous Molded Strip, Tab 6.35 x 0.81 mm, Salmon

Series Number : 19003

Status : Active

Product Category : Quick Disconnects

Engineering Number : AA-2201C



Documents & Resources

Drawings

[Drawing 190030105_sd.pdf](#)

3D Models and Design Files

[3D Model 190030105_stp.zip](#)


Specifications

[Product Specification PS-19902-008-001.pdf](#)

[Product Specification PS-19902-011-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19003
Description	InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²), Continuous Molded Strip, Tab 6.35 x 0.81mm, Salmon
Comments	Funnel Entry
Product Family	Standard Quick-Disconnect Terminals
Product Name	InsulKrimp
Type	Quick Disconnect
UPC	800753128934

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Salmon
Flammability	94V-0
Gender	Female
Glow-Wire Capable	No

Insulated	Fully
Insulation	Nylon (PA)
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	0.916/g
Orientation	Straight
Packaging Type	Reel
Plating min - Mating	4.064µm
Plating min - Termination	4.064µm
Polarized to Mating Part	No
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	-65° to +105°C
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.43mm max.
Wire Size (AWG)	18, 20, 22

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
ACP Perishable Tool Kit used in ACP Presses that Process Continuous Molded Product	<u>0190280104</u>
Mini-Mac Applicator	<u>0638837000</u>