



ELECTRONICS, INC.
 44 FARRAND STREET
 BLOOMFIELD, NJ 07003
 (973) 748-5089
<http://www.nteinc.com>

NTE74LS240, NTE74LS241, NTE74LS244 Integrated Circuit TTL– Octal Buffer and Line Driver w/3–State Outputs

Description:

The NTE74LS240 (Inverting), NTE74LS241 (Non–Inverting), and NTE74LS244 (Non–Inverting) are octal buffers and line drivers in a 20–Lead DIP type package designed specifically to improve both the performance and density of three–state memory address drivers, clock drivers, and bus–oriented receivers and transmitters. The designer has a choice of selected combinations of inverting and non–inverting outputs, symmetrical \overline{G} (active–low output control) inputs, and complementary G and \overline{G} inputs. These devices feature high fan–out, improved fan–in, a 400mV noise margin, and can be used to drive terminated lines down to 133 ohms.

Features:

- 3–State Outputs Drive Bus Lines or Buffer Memory Address Registers
- PNP Inputs Reduce DC Loading
- Hysteresis at Inputs Improves Noise margins
- High Capacitive Load Drive Capability

Absolute Maximum Ratings: (Note 1)

Supply Voltage, V_{CC}	7V
Input Voltage, V_{IN}	7V
Off–State Output Voltage	5.5V
Operating Temperature Range, T_A	0°C to +70°C
Storage Temperature Range, T_{stg}	–65°C to +150°C

Note 1. Unless otherwise specified, all voltages are referenced to GND.

Recommended Operating Conditions:

Parameter	Symbol	Min	Typ	Max	Unit
Supply Voltage (Note 1)	V_{CC}	4.75	5.0	5.25	V
High-Level Input Voltage	V_{IH}	2	-	-	V
Low-Level Input Voltage	V_{IL}	-	-	0.8	V
High-Level Output Current	I_{OH}	-	-	-15	mA
Low-Level Output Current	I_{OL}	-	-	24	mA
Operating Temperature Range	T_A	0	-	+70	°C

Note 1. Unless otherwise specified, all voltages are referenced to GND.

Electrical Characteristics: (Note 2, Note 3)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit	
Input Clamp Voltage	V_{IK}	$V_{CC} = \text{MIN}, I_I = -18\text{mA}$	-	-	-1.5	V	
Hysteresis	$V_{T+} - V_{T-}$	$V_{CC} = \text{MIN}$	0.2	0.4	-	V	
High Level Output Voltage	V_{OH}	$V_{CC} = \text{MIN}, V_{IH} = 2\text{V}, V_{IL} = \text{MAX}, I_{OH} = -3\text{mA}$	2.4	3.4	-	V	
		$V_{CC} = \text{MIN}, V_{IH} = 2\text{V}, V_{IL} = 0.5\text{V}, I_{OH} = \text{MAX}$	2.0	-	-	V	
Low Level Output Voltage	V_{OL}	$V_{CC} = \text{MIN}, V_{IH} = 2\text{V}, V_{IL} = \text{MAX}$	$I_{OL} = 12\text{mA}$	-	-	0.4	V
			$I_{OL} = 24\text{mA}$	-	-	0.5	V
3-State Leakage Current	I_{OZH}	$V_{CC} = \text{MIN}, V_{IH} = 2\text{V}, V_{IL} = \text{MAX}$	$V_O = 2.7\text{V}$	-	-	20	μA
	I_{OZL}		$V_O = 0.4\text{V}$	-	-	-20	μA
Input Current	I_I	$V_{CC} = \text{MAX}, V_I = 7\text{V}$	-	-	0.1	mA	
High Level Input Current	I_{IH}	$V_{CC} = \text{MAX}, V_I = 2.7\text{V}$	-	-	20	μA	
Low Level Input Current	I_{IL}	$V_{CC} = \text{MAX}, V_{IL} = 0.4\text{V}$	-	-	-0.2	mA	
Short-Circuit Output Current	I_{OS}	$V_{CC} = \text{MAX}, \text{Note 4}$	-40	-	-225	mA	
Supply Current All Types	I_{CC}	$V_{CC} = \text{MAX}, \text{Output Open}$	Outputs High	-	17	27	mA
NTE74LS240			Outputs Low	-	26	44	mA
NTE74LS241, NTE74LS244				-	27	46	mA
NTE74LS240			All Outputs Disabled	-	29	50	mA
NTE74LS241, NTE74LS244				-	32	54	mA

Note 2. For conditions shown as MIN or MAX, use the appropriate value specified under "Recommended Operation Conditions".

Note 3. All typical values are at $V_{CC} = 5\text{V}, T_A = +25^\circ\text{C}$.


Note 4. Not more than one output should be shorted at a time, and the duration of the short-circuit should not exceed one second.

Switching Characteristics: ($V_{CC} = 5\text{V}, T_A = +25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	NTE74LS240			NTE74LS241, NTE74LS244			Unit
			Min	Typ	Max	Min	Typ	Max	
Propagation Delay Time	t_{PLH}	$R_L = 667\Omega, C_L = 45\text{pF}$	-	9	14	-	12	18	ns
	t_{PHL}		-	12	18	-	12	18	ns
Output Enable Time	t_{PZL}		-	20	30	-	20	30	ns
	t_{PZH}		-	15	23	-	15	23	ns
Output Disable Time	t_{PLZ}	$R_L = 667\Omega, C_L = 5\text{pF}$	-	10	20	-	10	20	ns
	t_{PHZ}		-	15	25	-	15	25	ns

Pin Connection Diagram

NTE74LS240, NTE74LS244



NTE74LS241

