




### Model Number

NBB2-V3-E2

### Features

- Basic series
- 2 mm flush
- 3-wire DC

### Connection



### Accessories

#### V3-WM

Female connector, M8, 3-pin, field attachable

#### V3-GM

Female connector, M8, 3-pin, field attachable


#### V3-WM-2M-PUR

Cable socket, M8, 3-pin, PUR cable

#### V3-GM-2M-PUR

Cable socket, M8, 3-pin, PUR cable

### Dimensions



### Technical Data

#### General specifications

Switching element function		PNP	NO
Rated operating distance	$s_n$	2 mm	
Installation		flush	
Output polarity		DC	
Assured operating distance	$s_a$	0 ... 1.62 mm	
Reduction factor $r_{AI}$		0.35	
Reduction factor $r_{Cu}$		0.2	
Reduction factor $r_{304}$		0.7	

#### Nominal ratings

Operating voltage	$U_B$	10 ... 30 V DC	
Switching frequency	$f$	0 ... 1000 Hz	
Reverse polarity protected		reverse polarity protected	
Short-circuit protection		pulsing	
Voltage drop	$U_d$	$\leq 3$ V	
Operating current	$I_L$	0 ... 100 mA	
Off-state current	$I_r$	0 ... 0.5 mA typ. 0.1 $\mu$ A at 25 °C	
No-load supply current	$I_0$	$\leq 15$ mA	
Indication of the switching state		LED, yellow	

#### Functional safety related parameters

MTTF <sub>d</sub>	3560 a
Mission Time ( $T_M$ )	20 a
Diagnostic Coverage (DC)	0 %

#### Ambient conditions

Ambient temperature	-25 ... 70 °C (-13 ... 158 °F)
---------------------	--------------------------------

#### Mechanical specifications

Connection type	cable PVC , 130 mm
Core cross-section	0.14 mm <sup>2</sup>
Housing material	PBT
Sensing face	PBT
Protection degree	IP67

#### Compliance with standards and directives

Standard conformity	
Standards	EN 60947-5-2:2007 IEC 60947-5-2:2007

#### Approvals and certificates

UL approval	cULus Listed, General Purpose
CSA approval	cCSAus Listed, General Purpose
CCC approval	Products with a maximum operating voltage of $\leq 36$ V do not bear a CCC marking because they do not require approval.