

INDICATOR LIGHT, 16MM, ROUND, PLASTIC,
TRANSPARENT, LAMPHOLDER W2 X 4.6D, WITH
INCANDESCENT LAMP 24V

Design of the product	Complete unit round
-----------------------	---------------------

Enclosure:

Number of control points	0
--------------------------	---

Actuator:

Design of the operating mechanism	indicator light
Product expansion optional Light source	Yes
Color <ul style="list-style-type: none"> • of the actuating element 	Clear
Material of the actuating element	plastic
Type of unlocking device	without
Number of switching positions	2

Front ring:

Product component front ring	No
------------------------------	----

Holder:

Material of the holder	Plastic
------------------------	---------

Contact block/ lampholder:

Mounting type	W2 x 4.6d with lamp
Number of lampholders	1
Number of switching elements	0

General technical data:

Product function <ul style="list-style-type: none"> • positive opening • EMERGENCY STOP function 	No No
Product component <ul style="list-style-type: none"> • Light source 	Yes
Type of voltage <ul style="list-style-type: none"> • of the operating voltage 	AC/DC
Vibration resistance <ul style="list-style-type: none"> • acc. to IEC 60068-2-6 	20 ... 200 Hz: 5g
Protection class IP	IP65
Equipment marking <ul style="list-style-type: none"> • acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750 	H

<ul style="list-style-type: none"> • acc. to DIN EN 61346-2 • acc. to DIN EN 81346-2 		P
Operating voltage		P
<ul style="list-style-type: none"> • Rated value 	V	5 ... 60

Supply voltage:

Type of voltage of the supply voltage		
<ul style="list-style-type: none"> • of the light source 		AC/DC
Supply voltage 1 of the light source with AC		
<ul style="list-style-type: none"> • at 50 Hz Rated value 	V	24
<ul style="list-style-type: none"> • at 60 Hz Rated value 	V	24
Supply voltage 1 of the light source for DC		
<ul style="list-style-type: none"> • Rated value 	V	24

Auxiliary circuit:

Number of NC contacts		
<ul style="list-style-type: none"> • for auxiliary contacts 		0
Number of NO contacts		
<ul style="list-style-type: none"> • for auxiliary contacts 		0
Number of CO contacts		
<ul style="list-style-type: none"> • for auxiliary contacts 		0

Connections/ Terminals:

Type of electrical connection		tab terminals
--------------------------------------	--	---------------




Ambient conditions:

Ambient temperature		
<ul style="list-style-type: none"> • during operation 	°C	-25 ... +60
<ul style="list-style-type: none"> • during storage 	°C	-40 ... +80

Installation/ mounting/ dimensions:

Mounting type		front mounting
Shape of the installation opening		round
Mounting diameter	mm	16

Certificates/ approvals:

General Product Approval	Declaration of Conformity	Test Certificates	other		
 CCC		 EG-Konf.	Special Test Certificate	Confirmation	Environmental Confirmations

other
other

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SB22246BH06>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3SB22246BH06/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SB22246BH06&lang=en

last modified:

09.03.2015