

## Revolving centring point

Flex, for interchangeable inserts



### Application:

For rough machining and fine turning in general turning operations.

### Execution:

- Body hardened and ground.

### Advantage:

- Very flexible thanks to interchangeable inserts.

### Delivery:

1x revolving centring point.



<b>Art. no.</b>	<b>22144 020</b>
<b>Brand</b>	RÖHM
<b>Manufacturer Part Number</b>	6 1030
<b>Morse taper size</b>	MK 2
<b>Programming size</b>	45 mm
<b>Programming size for housing</b>	43 mm
<b>Max. workpiece weight</b>	40 kg
<b>Concentricity tolerance</b>	0.01 mm
<b>Diameter of housing</b>	45 mm
<b>Gross Weight</b>	0.480 kg
<b>Product Group</b>	201

### EAN

4019208017174