

Stepped clamps




Application:

For supporting adjustable clamps.

Execution:

- Machine casting
- Painted
- Contact surface and step face-milled
- With clamping stages, each with a height difference of 7.5 mm

Art. no.	26145 030
Brand	AMF
Manufacturer Part Number	71381
Height	140 mm
Min. step height	102.5 mm
Width	100 mm
DIN	6318
Gross Weight	2.300 kg
Product Group	260



EAN

4020772071387