

Work mats made from PVC

Perforated design, height 12 mm

Application:


Ideal mats for workplaces with large amounts of chip waste, flexible with a variety of applications. Suitable for wet and dry areas.

Execution:

- Made of PVC, mesh opening 25 x 25 mm
- Woven PVC strands are provided on the upper and lower side with grooves for a firm grip
- Slip resistance rating B according to DIN 51097
- Fire protection class B2 according to DIN 54332 (B2) part of DIN 4102
- Loads up to 2000 kg/m²
- Resistant against mild acids and alkalis
- Fixed dimensions with yellow bevelled safety edges
- Sold by the metre without safety edges
- Special models on request

Advantage:

- Fluids and chips can fall through the mesh opening, thus they can be easily removed and cleaned
- Increases ergonomics at the workstation and reduces signs of physical fatigue



Art. no.	50225 170
Manufacturer Part Number	WS010701
Surface structure	Grooves / open
Material	PVC - Polyvinyl chloride
Length	1200 mm
Width	600 mm
Material thickness	12 mm
Mat design	Individual mat
Resistance against	Fats, Petrol, Coolant
Min. temperature resistance	-20 °C
Max. temperature resistance	60 °C
Suitable for wet areas	Yes
Antistatic	No
Anti-fatigue	Yes
Non-slip	Yes
Compliant with REACH	Yes
Colour	Black, Yellow
Gross Weight	3.435 kg
Product Group	5AD

EAN

5060087958477