

## AGWP10 Select cordless tapping machine

lithium-ion 18 volt



### Application:

for fast drilling and cleaning of threads.

### Execution:

- cordless screw taps with reversing transmission for automatic reversal of rotation direction when withdrawing drill spindle from screw hole
- high concentricity through zero-play connection between drilling shaft and thread chuck (B12 taper seat)
- metal gear head

### Delivery:

additional handle, plastic tool case, does not include tapping chuck



<b>Art. no.</b>	<b>71028 380</b>
<b>Brand</b>	FEIN
<b>Manufacturer Part Number</b>	71090162000
<b>Applications</b>	Heavy screw/drill application
<b>Model</b>	AGWP 10 Select
<b>Motor design</b>	Brushless motor
<b>Number of rechargeable batteries/batteries</b>	0
<b>Battery voltage</b>	18 V/AC
<b>Max. thread-cutting performance</b>	M10
<b>Idle speed left</b>	760 rpm
<b>Min./max. rotation speed from cutting at nominal load</b>	0-440 rpm
<b>Min./max. rotation speed at nominal load left-handed rotation</b>	0-670 rpm
<b>Clamping neck diameter</b>	43 mm
<b>Battery included</b>	No
<b>Width across corners</b>	23 mm
<b>With working lights</b>	No
<b>With rubber-coated handle</b>	No
<b>Gross Weight</b>	3.936 kg
<b>Product Group</b>	704

### EAN

4014586885537