

Cassini Radius


CASSINI RADIUS 400 IK10 1338LM 840 EM3 WHITE

4054901



Product features

- Ambient and decorative 400mm diameter LED bulkhead luminaire with halo backlight. Resistant to dust and water jet ingress, IP65, IK10, Class 1, 220-240V. 4000K, Switchable High Output or High efficiency mode, 701/1338 lm, 19 W, Drive current: 700mA, CRI 80, Integral 3 hour maintained emergency



PRODUCT OVERVIEW

Product name	CASSINI RADIUS 400 IK10 1338LM 840 EM3 WHITE
Technology	LED
Environment	Indoor
General application	Office
ETIM Class	EC002892
Warranty	5 years
Fixture luminous flux (lm)	701/1338
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Photobiological Risk Group	RG0
Total power consumption (W)	19
Product Voltage (V)	240
Electrical protection	Class I
Housing colour	White
IP rating	IP65
IK rating	IK10
Product EAN number	5026524549011

DATA TABLE

General data

Product name	CASSINI RADIUS 400 IK10 1338LM 840 EM3 WHITE
Technology	LED
Environment	Indoor
General application	Office
ETIM Class	EC002892
Warranty	5 years

Optical data

Cassini Radius

CASSINI RADIUS 400 IK10 1338LM 840 EM3 WHITE

4054901

Fixture luminous flux (lm)	701/1338
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Photobiological Risk Group	RG0

Electrical data

Total power consumption (W)	19
Mains voltage (V)	230-240V
Product Voltage (V)	240
Electrical protection	Class I
Drive current (mA)	700
Energy Efficiency Class (A->G) of contained light source	B
Nominal Frequency (Hz)	50/60Hz

Physical data

Housing colour	White
IP rating	IP65
IK rating	IK10
Nominal Product Width (mm)	400
Nominal Product Height (mm)	400
Max. Lamp Diameter (mm) - D	400
Weight (kg)	1.3

Packaging

Single packaging type	Carton
Product EAN number	5026524549011
Packaging single length / height (cm)	50.0
Packaging single width (cm)	50.0
Packaging single depth (cm)	20.0
DUN14 (outer)	05026524549011
Units per outer package	1
Packaging outer length / height (cm)	50.0
Packaging outer width (cm)	50.0
Packaging outer depth (cm)	20.0

PHOTOMETRY


Cassini Radius

CASSINI RADIUS 400 IK10 1338LM 840 EM3 WHITE
4054901

0.5	1.54	E(0°) E(C0)	97.0°	191 15
1.0	3.08	E(0°) E(C0)	97.0°	46 4
1.5	4.62	E(0°) E(C0)	97.0°	20 2
2.0	6.16	E(0°) E(C0)	97.0°	11 1
2.5	7.70	E(0°) E(C0)	97.0°	7 1
3.0	9.24	E(0°) E(C0)	97.0°	5 0

Distance [m] Cone diameter [m] Illuminance [lx]

— C0 - C180 (Half beam angle: 114.0°)



TECHNICAL DRAWINGS

