



Model Number

NJ4-12GM40-E3

Features

- 4 mm non-flush

Accessories

BF 12

Mounting flange, 12 mm

Technical Data

General specifications

Switching element function		PNP	NC
Rated operating distance	s_n	4 mm	
Installation		non-flush	
Output polarity		DC	
Assured operating distance	s_a	0 ... 3.24 mm	
Actual operating distance	s_r	3.6 ... 4.4 mm typ.	
Reduction factor r_{AI}		0.37	
Reduction factor r_{Cu}		0.36	
Reduction factor r_{304}		0.74	

Nominal ratings

Operating voltage	U_B	10 ... 60 V	
Switching frequency	f	0 ... 2000 Hz	
Hysteresis	H	1 ... 10 typ. 3 %	
Reverse polarity protection		reverse polarity protected	
Short-circuit protection		pulsing	
Voltage drop	U_d	≤ 3 V	
Voltage drop at I_L		1.2 ... 2.5 V	
Voltage drop $I_L = 100$ mA, switching element on U_d			
Operating current	I_L	0 ... 200 mA	
No-load supply current	I_0	≤ 9 mA	
Time delay before availability	t_v	≤ 20 ms	
Switching state indicator		LED, yellow	

Functional safety related parameters

MTTF _d	750 a
Mission Time (T_M)	20 a
Diagnostic Coverage (DC)	0 %

Ambient conditions

Ambient temperature	-25 ... 70 °C (-13 ... 158 °F)
Storage temperature	-40 ... 85 °C (-40 ... 185 °F)

Mechanical specifications

Connection type	cable PUR, 2 m
Core cross-section	0.34 mm ²
Housing material	Stainless steel 1.4305 / AISI 303
Sensing face	PBT
Degree of protection	IP67

General information

Scope of delivery	2 self locking nuts in scope of delivery
-------------------	--


Compliance with standards and directives

Standard conformity	
Standards	EN 60947-5-2:2007 IEC 60947-5-2:2007


Approvals and certificates

UL approval	cULus Listed, General Purpose
CSA approval	cCSAus Listed, General Purpose
CCC approval	Certified by China Compulsory Certification (CCC)

Dimensions



Electrical Connection



Release date: 2016-08-04 16:05 Date of issue: 2016-08-04 282951_eng.xml