

Innovations

and Spring-Summer Campaign 2020





Kraftform Turbo

Quadruples the screwdriving speed – in a purely mechanical way.

Many users would like to be able to carry out screwdriving processes faster without compromise. With a screwdriver that is precise, allows powerful screwdriving, and is much faster than a conventional screwdriver.

A part time universal gear is the solution: integrated in the handle of the screwdriver, it significantly increases the working speed.

The Kraftform Turbo accelerates the screwdriving in a purely mechanical way. The turbo function can either be switched on or off by pressing a button. Turning it off is

recommended for fine adjustment and final tightening or loosening of a high torque screw.

The robust steel design is maintenance-free and ensures a long product life. Thanks to the Rapidaptor bit holder, the Kraftform Turbo can be used with all conventional 1/4" hexagon bits for a wide variety of screw profiles.

With the Rapidaptor function the bits can be inserted directly and can be easily removed by pushing the sleeve forward – allowing single hand operation.

NEW



826 T Kraftform Turbo bit-holding screwdriver handle with Rapidaptor quick-release chuck



Application: Suitable for bits with 1/4" - external hexagon drive as per DIN ISO 1173-C 6,3 and E 6,3 and Wera connection series 1 and 4

Design: Connectable mechanic turbo function for quadrupling the screwdriving speed; robust, maintenance-free gear made of steel; 1/4" - hexagon socket mounting with Rapidaptor technology with rapid-in, rapid-out, rapid-spin, chuck-all and single-hand functions, magnetic

Handle: Kraftform with anti-roll protection, multi-component

		
	mm	
05057480001	1/4"	146

Kraftform Turbo



Faster screwdriving



The construction of the Kraftform Turbo allows a quadruplication of the speed when manually screwdriving - purely mechanical, without electricity!

With and without Turbo




If required, the turbo function can be activated by simply pressing a button. Turning it off is recommended for loosening or for fine adjustment and final tightening of the screw with a high torque.

Kraftform Kompakt Turbo

NEW

Kraftform Kompakt Turbo 1



folding pouch with 89 mm long bits


19-piece set

1 bit-holding Kraftform Turbo with Rapidaptor quick-release chuck

05057482001	
●	826 T Kraftform Turbo 1x 1/4"x146
⊕	851/4 Z PH 1x PH 1x89; 1x PH 2x89; 1x PH 3x89
⊕	855/4 Z PZ 1x PZ 1x89; 1x PZ 2x89; 1x PZ 3x89
⊕	867/4 Z TORX® 1x TX 10x89; 1x TX 15x89; 1x TX 20x89; 1x TX 25x89; 1x TX 30x89
○	840/4 Z Hex-Plus 1x 3,0x89; 1x 4,0x89; 1x 5,0x89; 1x 6,0x89
●	800/4 Z 1x 0,8x4,0x89; 1x 1,0x5,5x89; 1x 1,2x6,5x89

NEW

Kraftform Kompakt Turbo Imperial 1



folding pouch with 89 mm long bits

19-piece set

1 bit-holding Kraftform Turbo with Rapidaptor quick-release chuck

05057483001	
●	826 T Kraftform Turbo 1x 1/4"x146
⊕	851/4 Z PH 1x PH 1x89; 1x PH 2x89; 1x PH 3x89
⊕	867/4 Z TORX® 1x TX 10x89; 1x TX 15x89; 1x TX 20x89; 1x TX 25x89; 1x TX 30x89
○	840/4 Z Hex-Plus 1x 3/32"x89; 1x 1/8"x89; 1x 5/32"x89; 1x 3/16"x89
○	868/4 Square-Plus 1x # 1x89; 1x # 2x89; 1x # 3x89
●	800/4 Z 1x 0,8x4,0x89; 1x 1,0x5,5x89; 1x 1,2x6,5x89

Kraftform Turbo

Robust, maintenance-free gear made of steel



The robust steel design is maintenance-free and ensures a long product life.

Handle/interchangeable blade system



Thanks to the Rapidaptor bit holder, the Kraftform Turbo can be used with all conventional 1/4" bits.

Kraftform Turbo

Quadruples the screwdriving speed – in a purely mechanical way.

The Kraftform Turbo hand holder 827 T i and the individually tested (10,000v) Wera VDE interchangeable blades in the VDE version guarantee fast and safe working even under tension.

NEW

827 T i Kraftform Turbo blade holding handle



Application: For Wera VDE interchangeable blades only

Design: Connectable mechanic turbo function for quadrupling the screwdriving speed; robust, maintenance-free gear made of steel

Handle: Kraftform with anti-roll protection, multi-component


05057481001 ¹⁾	
●	mm
○	mm
●	9
○	125

¹⁾Available from May 2020

Kraftform Turbo i



Faster screwdriving




The construction of the Kraftform Turbo allows a quadruplication of the speed when manually screwdriving - purely mechanical, without electricity!

With and without Turbo



If required, the turbo function can be activated by simply pressing a button. Turning it off is recommended for loosening or for fine adjustment and final tightening of the screw with a high torque.

Handle/interchangeable blade system



With its 9 mm mounting, the Kraftform Turbo is suitable for all Wera Kraftform Kompakt VDE interchangeable blades. The "holder/interchangeable blade system" stands for flexible working with many screw profiles.



Kraftform Kompakt Turbo i

NEW

Kraftform Kompakt Turbo i 1



16-piece set

1 blade holding 817 Kraftform VDE handle and 1 blade holding 827 T i Kraftform Turbo handle; both for Wera VDE interchangeable blades only

14 VDE interchangeable blades (each 154 mm long) with reduced blade diameter (Articles KK 60 i 0,4x2,5 and KK 67 i TX 10 standard blade diameter) with integrated protective insulation, so that low-lying screw and spring elements can be reached and operated

05057484001		
●	827 T i Kraftform Turbo	1x 9x125
●	817 VDE	1x 9x102
⊕	KK 62 iS	1x PH 1x154; 1x PH 2x154
⊕	KK 65 iS PZ	1x PZ 1x154; 1x PZ 2x154
⊕	KK 65 iS PZ/S	1x # 1x154; 1x # 2x154
⊕	KK 67 i TORX®	1x TX 10x154
⊕	KK 67 iS TORX®	1x TX 15x154; 1x TX 20x154; 1x TX 25x154
⊖	KK 60 i	1x 0,4x2,5x154
⊖	KK 60 iS	1x 0,6x3,5x154; 1x 0,8x4,0x154; 1x 1,0x5,5x154

Available from May 2020

NEW

Kraftform Kompakt Turbo i Imperial 1



16-piece set

1 blade holding 817 Kraftform VDE handle and 1 blade holding 827 T i Kraftform Turbo handle; both for Wera VDE interchangeable blades only

14 VDE interchangeable blades (each 154 mm long) with reduced blade diameter (Articles KK 60 i 0,4x2,5 and KK 67 i TX 10 standard blade diameter) with integrated protective insulation, so that low-lying screw and spring elements can be reached and operated

05057485001		
●	827 T i Kraftform Turbo	1x 9x125
●	817 VDE	1x 9x102
⊕	KK 62 iS	1x PH 1x154; 1x PH 2x154
⊕	KK 62 i PH/S	1x # 1x154; 1x # 2x154
⊕	KK 67 i TORX®	1x TX 10x154
⊕	KK 67 iS TORX®	1x TX 15x154; 1x TX 20x154; 1x TX 25x154
⊕	KK 68 iS	1x # 1x154; 1x # 2x154
⊖	KK 60 i	1x 0,4x2,5x154
⊖	KK 60 iS	1x 0,6x3,5x154; 1x 0,8x4,0x154; 1x 1,0x5,5x154

Available from May 2020



Joker 6003 ring spanner

Mouth side with only 15° back-pivoting angle.
When things get tight.

As the installation space becomes increasingly tight during screwdriving, it remains necessary that tools evolve to enable users to work successfully. Narrow spaces require additional placement points of the tool. Can spanners be modified so that the placement possibilities of the tool increase?

The combination of the 7.5° pivoted mouth and the double hexagon geometry doubles the placement points. A repeated 180° turn of the wrench around the longitudinal axis during screwdriving provides four placement possibilities, and bolts or screw

heads can be "taken" every 15°.

The Joker 6003 with its smart mouth geometry significantly expands the range of uses in confined spaces. The Joker 6003 will automatically find the respective placement point after every turn.

The slim yet robust ring side is angled by 15° to the tool axis. The high-quality surface treatment achieves a high and long-lasting corrosion protection.

With Take it easy tool finder: colour coding by size.

Joker 6003




For very tight spaces




The Joker 6003 ring spanner with its special mouth geometry – a mouth side pivoted by 7.5° and the double hexagon geometry - doubles the placement possibilities when repeatedly turning the wrench 180° around the longitudinal axis. Bolts and

screw heads can be "taken" every 15°. The Joker 6003 will automatically find the respective placement point after every turn.

Angled ring side




The ring side is angled at 15° to the tool axis to prevent injury.



NEW

6003 Joker ring spanner



Application: hexagon screw heads and bolts

Design: ring spanner; mouth side pivoted by 7,5°, ring side pivoted by 15°; With Take it easy tool finder: Colour coding by size

		mm	mm	mm	mm	mm
05020200001		8	115	19	4,5	12,5
05020201001		10	125	22	5	15
05020202001		11	135	24,5	5	17
05020203001		12	148	26	5,5	18
05020204001		13	160	27	6	19
05020205001		14	167	29	6	20
05020206001		15	174	32	6	22
05020207001		16	182	35	6,5	23
05020208001		17	190	38	6,5	24,5
05020209001		18	210	39	7,5	26
05020210001		19	230	42	7,5	27,5

NEW

6003 Joker 5 Set 1 ring spanner set



Ring spanner set, mouth side pivoted by 7,5°

5-piece set

In roubust pouch

05020230001					
6003 Joker		1x 8x115; 1x 10x125; 1x 13x160; 1x 17x190; 1x 19x230			

NEW

6003 Joker 5 Imperial Set 1 ring spanner set, Imperial



Ring spanner set, mouth side pivoted by 7,5°


5-piece set

In roubust pouch

05020240001					
6003 Joker Imperial		1x 5/16"x115; 1x 3/8"x125; 1x 1/2"x160; 1x 9/16"x167; 1x 3/4"x230			

NEW

6003 Joker ring spanner, imperial




Application: hexagon screw heads and bolts

Design: ring spanner; mouth side pivoted by 7,5°, ring side pivoted by 15°; With Take it easy tool finder: Colour coding by size

		mm	mm	mm	mm	mm
05020211001		5/16"	115	19	4,5	12,5
05020212001		3/8"	125	22	5	15
05020213001		7/16"	135	24,5	5	17
05020214001		1/2"	160	26	6	19
05020215001		9/16"	167	29	6	20
05020216001		5/8"	182	35	6,5	23
05020217001		11/16"	210	40	7,5	26
05020218001		3/4"	230	42	7,5	27,5

NEW

6003 Joker 11 Set 1 ring spanner set



Ring spanner set, mouth side pivoted by 7,5°

11-piece set

In roubust pouch

05020231001					
6003 Joker		1x 8x115; 1x 10x125; 1x 11x135; 1x 12x148; 1x 13x160; 1x 14x167; 1x 15x174; 1x 16x182; 1x 17x190; 1x 18x210; 1x 19x230			

NEW

6003 Joker 8 Imperial Set 1 ring spanner set, Imperial



Ring spanner set, mouth side pivoted by 7,5°

8-piece set

In roubust pouch

05020241001					
6003 Joker Imperial		1x 5/16"x115; 1x 3/8"x125; 1x 7/16"x135; 1x 1/2"x160; 1x 9/16"x167; 1x 5/8"x182; 1x 11/16"x210; 1x 3/4"x230			



"Take it easy" tool finder



"Take it easy" tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).

Suitable for docking with the Wera 2go system



The Joker bags are suitable for attachment to walls, shelves, workshop trolleys and the Wera 2go system thanks to the hook and loop fastener system on the back.



Joker 6004 self-setting, adjustable spanner

Self-setting. Gripping. Ratcheting.

Many users wish to have a universal screwdriving tool with the widest possible range of applications. It should be a single tool for multiple metric and imperial dimensions.

It should automatically adjust to the different screw sizes. It should be safe to grab without damaging anything and allow for a high working speed.

The continuous and parallel jaws replace several single spanner dimensions. The required size is automatically and continuously set when attaching the tool to the hexagon bolt or screw.

The integrated lever mechanism securely clamps the hexagon screw or bolt between the jaws, which significantly reduces the risk of slipping or damage.

The ratchet function ensures fast and consistent screwdriving without removing the tool. Thanks to the corner-width rectangular prisms, a back-pivoting angle of only 30° can be realized.

The single-arm design in conjunction with the ratchet function and the corner-width prism make it possible to work even in confined spaces. The adjustable Joker 6004 is the universal screwdriving tool.




Automatically and continuously self-setting



With its automatically and continuously gripping parallel jaws the Joker spanner 6004 covers all dimensions in the respective field of application. The tool automatically finds the required size when placed on the bolt or screw, no setting required.



Gentle to the screw



The parallel smooth jaws of the Joker 6004 allow surface pressure and can thus prevent rounding of the bolt or screw head, which can occur during power transmission on corners.




Ratchet mechanism for fast work



The ratchet function in the mouth sees to fast and consistent screwdriving without removing the tool.

Low back-pivoting angle



Thanks to the corner-width rectangular prisms, a back-pivoting angle of only 30° can be realized.

Joker 6004

NEW

6004 Joker S self-setting spanner



Application: hexagon screw heads and bolts with wrench size 10–13 (metric) or 7/16"-1/2" (imperial)

Design: self-setting spanner with ratchet function; size-adjustable mouth side, parallel smooth jaws; with 30° back-pivoting angle due to the corner-width rectangular prisms in the mouth; hole for hanging

	mm	mm	mm	mm
0502010001	10-13	7/16"-1/2"	154	10

NEW

6004 Joker L self-setting spanner



Application: hexagon screw heads and bolts with wrench size 16–19 (metric) or 5/8"-3/4" (imperial)

Design: self-setting spanner with ratchet function; size-adjustable mouth side, parallel smooth jaws; with 30° back-pivoting angle due to the corner-width rectangular prisms in the mouth; hole for hanging

	mm	mm	mm	mm
05020101001	16-19	5/8"-3/4"	224	14



NEW

6004 Joker XXL self-setting spanner



Application: hexagon screw heads and bolts with wrench size 24–32 (metric) or 15/16"-1 1/4" (imperial)

Design: self-setting spanner with ratchet function; size-adjustable mouth side, parallel smooth jaws; with 30° back-pivoting angle due to the corner-width rectangular prisms in the mouth; hole for hanging

	mm	mm	mm	mm
05020102001	24-32	15/16"-1 1/4"	322	20

Joker 6002



6002 Joker Double open-ended wrenches



Application: Hexagon bolts and nuts

Design: Double open-ended wrench

	mm	mm	mm	mm	mm
05003760001	10	23	13	27	5,5
05003765001	17	37	19	42	8,5
05020260001 ¹⁾	20	48	22	51	10
05020261001 ¹⁾	22	48	24	51	10
05020262001 ¹⁾	24	51	27	60	11
05020263001 ¹⁾	27	63	32	66	12
05020264001 ¹⁾	30	63	32	66	12

¹⁾Available from May 2020

Holding function



The Joker's holding function means that nuts and bolts can be held in the jaw and easily positioned where they are needed. Fastening on to the thread can then be done quickly and safely, thanks to the innovative special stop-plate which holds the fastener. No more time-wasting searches for dropped nuts and bolts! After applying and positioning the nut or bolt, fastening can begin immediately – no additional tools required.

Integrated limit-stop



Constant re-positioning of the wrench? Difficulty holding fasteners in confined spaces? Easing off to avoid any risks of injury or fastener damage? That was yesterday. Today, the Joker prevents slipping off of the fastener head with its integrated limit-stop – no longer is the thumb needed to act as a depth stop. This makes applications much easier and allows significantly more force to be applied during fastening jobs.



Wera T-handle screwdrivers

With T-handle screwdrivers, particularly high torques can be transferred when working with manual screwdrivers.

We have been busy making working with these screwdriving tools pleasant and as gentle as possible.


Our solution is the ergonomic design of the T-handle screwdrivers and their 2-component construction. The handles fill the palm of the hand well, the fingers lie safely in the soft rounded handle recesses, the whole hand makes contact with the handle and friction losses between the hand and the handle are avoided.

Second arm




The additional short arm, which emerges laterally from the handle, allows the transmission of extremely high torques by using the long arm as a lever.

High torque transfer



By using the blade as an extension of your lower arm you can transfer particularly high torque.

NEW
454 T-handle hexdriver



Application: hexagon socket screws

Blade: round

Design: With long and short arm, Hex-Plus, bevelled, matte chrome-plated

Handle: T-shape, 2 components, with hole for hanging. With Take it easy tool finder: Colour coding by profiles (blue = hexagon socket) and size stamping.

	mm	mm	mm	mm	mm
05023330001	2	100	12	32	65
05023332001	2,5	100	12	32	65

NEW
454 HF T-handle hexagon screwdriver Hex-Plus with holding function



Application: hexagon socket screws

Blade: hexagon

Design: With long and short arm, Hex-Plus, bevelled, matte chrome-plated, with holding function for hexagon socket screws

Handle: T-shape, 2 components, with hole for hanging. With Take it easy tool finder: Colour coding by profiles (blue = hexagon socket) and size stamping.

	mm	mm	mm	mm	mm
05023334001	3	100	15	38	77
05023338001	4	100	15	38	77
05023339001	4	150	15	38	77
05023340001	4	200	15	38	77
05023342001	5	100	20	49	99
05023343001	5	150	20	49	99
05023344001	5	200	20	49	99
05023346001	6	100	20	49	99
05023347001	6	150	20	49	99
05023348001	6	200	20	49	99
05023350001	7	200	20	49	99
05023351001	8	100	20	49	99
05023352001	8	150	20	49	99
05023353001	8	200	20	49	99
05023354001	10	100	20	49	99
05023355001	10	200	20	49	99



“Take it easy” Tool Finder



Screwdrivers with “Take it easy” tool finder: colour coding according to profile and size stamp.



Hex-Plus



Hexagon socket screws are a problem, because the contact surfaces that transfer the force of the tool to the screw are very narrow. The consequence: the head of the screw can be damaged, usually rounding out the recess. Hex-Plus tools have larger contact surfaces to prevent this, driving from the

flats of the recess, rather than the corners. Good to know: Hex-Plus tools fit into every standard hexagon socket screw!




Holding function (HF) for hexagon socket screws



A resilient ball ensures the hexagon socket screw to be clamped on the tool tip. Especially helpful in hard to reach areas where you can not use your other hand to hold the screw.

NEW
454 HF T-handle hexagon screwdriver Hex-Plus with holding function, imperial



Application: hexagon socket screws


Blade: hexagon

Design: With long and short arm, Hex-Plus, bevelled, matte chrome-plated, with holding function for hexagon socket screws

Handle: T-shape, 2 components, with hole for hanging. With Take it easy tool finder: Colour coding by profiles (blue = hexagon socket) and size stamping.

	mm	mm	mm	mm	mm
05023359001	1/8"	150	15	38	77
05023360001	9/64"	150	15	38	77
05023361001	5/32"	150	15	38	77
05023362001	3/16"	150	20	49	99
05023363001	7/32"	150	20	49	99
05023364001	1/4"	150	15	49	99
05023365001	5/16"	150	20	49	99
05023366001	3/8"	150	20	49	99

NEW
495 T-handle socket wrench screwdrivers



Application: external hexagon screws


Blade: round

Design: matte chrome-plated

Handle: T-shape, 2 components, with hole for hanging. With handle markings by profile and size.

	mm	mm	mm	mm	mm
05023381001	5	230	38	77	9"
05023382001	5,5	230	38	77	9"
05023383001	6	230	38	77	9"
05023384001	7	230	49	99	9"
05023385001	8	230	49	99	9"
05023386001	9	230	49	99	9"
05023387001	10	230	49	99	9"
05023389001	11	230	49	99	9"
05023391001	12	230	49	99	9"
05023393001	13	230	49	99	9"

NEW
454 Imperial T-handle hexagon screwdriver Hex-Plus, imperial



Application: hexagon socket screws


Blade: round

Design: With long and short arm, Hex-Plus, bevelled, matte chrome-plated

Handle: T-shape, 2 components, with hole for hanging. With Take it easy tool finder: Colour coding by profiles (blue = hexagon socket) and size stamping.

	mm	mm	mm	mm	mm
05023356001	5/64"	150	12	32	65
05023357001	3/32"	150	12	32	65
05023358001	7/64"	150	12	32	65

NEW
467 TORX® HF T-handle screwdriver with holding function



Application: socket TORX® screws

Blade: round


Design: With long and short arm, with holding function for TORX® screws as per specification "Acument Intellectual Properties" on the long arm; matte chrome-plated

Handle: T-shape, 2 components, with hole for hanging. With Take it easy tool finder: Colour coding by profiles (green = TORX®) and size stamping.

	mm	mm	mm	mm	mm	mm
05023367001	TX 6	100	12	32	65	3,0
05023368001	TX 7	100	12	32	65	3,0
05023369001	TX 8	100	12	32	65	3,5
05023370001	TX 9	100	12	32	65	3,5
05023371001	TX 10	100	12	32	65	4,0
05023372001	TX 15	100	15	38	77	4,0
05023373001	TX 20	100	15	38	77	4,5
05023374001	TX 20	200	15	38	77	4,5
05023375001	TX 25	100	15	38	77	5,0
05023376001	TX 25	200	15	38	77	5,0
05023377001	TX 27	200	20	49	99	6,0
05023378001	TX 30	200	20	49	99	6,0
05023379001	TX 40	200	20	49	99	8,0
05023380001	TX 45	200	20	49	99	9,0



With useful plastic rack



Including useful rack for well-arranged storage of the screwdrivers.


Ergonomic 2-component T-handle



The ergonomically shaped 2-component T-handle with finger recesses and pleasant surface facilitates very high power transmission and fatigue-free working.

NEW

454/10 HF Set Imperial 1 screwdriver set T-handle screwdrivers Hex-Plus with holding function, imperial




Application: hexagon socket screws, with holding function from size 1/8"

Design: With Take it easy tool finder: Colour coding by profiles (blue = hexagon socket) and size stamping. 10-piece set in a box + 2 racks

NEW

454/7 HF Set 1 screwdriver set T-handle screwdrivers Hex-Plus with holding function




Application: hexagon socket screws, with holding function from size 3

Design: With Take it easy tool finder: Colour coding by profiles (blue = hexagon socket) and size stamping. 7-piece set in a box + 2 racks

05023450001	
○ 454	1x 2,5x100
○ 454 HF	1x 3x100; 1x 4x100; 1x 5x150; 1x 6x150; 1x 8x200; 1x 10x200
Rack	2x 190,0x50,0

NEW

467/7 TORX® HF Set 1 screwdriver set T-handle TORX® screwdrivers with holding function




Application: TORX®, with holding function for TORX® screws as per specification "Acument Intellectual Properties"

Design: With Take it easy tool finder: Colour coding by profiles (green = TORX®) and size stamping. 7-piece set in a box + 2 racks

05023452001	
⊕ 467 TORX® HF	1x TX 10x100; 1x TX 15x100; 1x TX 20x100; 1x TX 25x100; 1x TX 30x200; 1x TX 40x200; 1x TX 45x200
Rack	2x 190,0x50,0

NEW

Kraftform Kompakt 400



folding pouch with 89 mm long bits

17-piece set

1 hand holder 416 R T-handle with Rapidaptor quick-release chuck

05057470001	
⊕ 416 R	1x 1/4"x45
⊕ 851/4 Z PH	1x PH 2x89; 1x PH 3x89
⊕ 855/4 Z PZ	1x PZ 2x89; 1x PZ 3x89
⊕ 867/4 Z TORX®	1x TX 10x89; 1x TX 15x89; 1x TX 20x89; 1x TX 25x89; 1x TX 30x89; 1x TX 40x89
○ 840/4 Z Hex-Plus	1x 3,0x89; 1x 4,0x89; 1x 5,0x89; 1x 6,0x89; 1x 8,0x89
⊖ 800/4 Z	1x 1,0x5,5x89

Wera Stubbies

Especially small screwdrivers with short blades for hard to reach areas.

The 2-component Kraftform handle with its practical combination of hard and soft zones allows for a firm grip and precise working.

The blades have all the benefits of the Wera Bit technology. Special surface treatment of

the blades for high corrosion protection and optimum fitting accuracy in the screw.

The hexagon anti-roll protection prevents annoying rolling away of bits in the workplace.


Wera Stubby

Compact shape



With its compact handle shape and the short blade, the Kraftform Stubbies are particularly suitable for working in confined screwdriving situations.

Long life



The special surface treatment of the blades sees to a high level of corrosion protection and optimum fitting accuracy of the screw.



"Take it easy" Tool Finder



Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.



NEW

335 Stubby/carburetor screwdriver



Application: slotted screws

Blade: round

Design: matte chrome-plated

Handle: Kraftform with anti-roll protection, 2 components. With Take it easy tool finder: Colour coding by profiles (yellow = slotted) and size stamping.

	mm	mm	mm	mm	mm
05008840001	0,6	3,5	24,5	54	9/64"
05008841001	0,8	4,0	24,5	54	5/32"
05008842001	1,0	5,5	24,5	54	7/32"
05008843001	1,2	6,5	24,5	54	1/4"
05008844001	1,2	8,0	24,5	54	5/16"

NEW

355 PZ Phillips-head Stubby/carburetor screwdriver



Application: suitable for Pozidriv screws

Blade: round

Design: matte chrome-plated

Handle: Kraftform with anti-roll protection, 2 components. With Take it easy tool finder: Colour coding by profiles (black = Pozidriv) and size stamping.

	mm	mm	mm	mm
05008853001	PZ 1	25	54	4,5 1"
05008854001	PZ 2	25	54	6,0 1"
05008855001	PZ 3	25	54	8,0 1"

NEW

350 PH Phillips-head Stubby/carburetor screwdriver



Application: Phillips-head screws Phillips-Recess

Blade: round

Design: matte chrome-plated

Handle: Kraftform with anti-roll protection, 2 components. With Take it easy tool finder: Colour coding by profiles (red = Phillips) and size stamping.

	mm	mm	mm	mm
05008850001	PH 1	25	54	4,2 1"
05008851001	PH 2	25	54	5,2 1"
05008852001	PH 3	25	54	6,2 1"

NEW

367 TORX® Stubby screwdriver



Application: socket TORX® screws

Blade: round


Design: matte chrome-plated

Handle: Kraftform with anti-roll protection, 2 components. With Take it easy tool finder: Colour coding by profiles (green = TORX®) and size stamping.

	mm	mm	mm	mm
05008856001	TX 10	25	54	3,4 1"
05008857001	TX 15	25	54	3,7 1"
05008858001	TX 20	25	54	4,0 1"
05008859001	TX 25	25	54	4,5 1"
05008860001	TX 27	25	54	5,1 1"
05008861001	TX 30	25	54	5,6 1"
05008862001	TX 40	25	54	- 1"

NEW

Kraftform Kompakt Stubby 1



Textile box with 25 mm long bits
19-piece set
1 bit-holding 811/1 Stubby, 18 bits

05057471001	
●	811/1 Stubby 1x 1/4"
⊕	851/1 BTZ PH 1x PH 1x25; 1x PH 2x25
⊕	855/1 BTZ PZ 1x PZ 1x25; 1x PZ 2x25
⊕	867/1 TORX® 1x TX 10x25; 1x TX 15x25; 1x TX 20x25; BTZ 1x TX 25x25; 1x TX 30x25
○	840/1 BTZ 1x 2,0x25; 1x 2,5x25; 1x 3,0x25; 1x 4,0x25; Hex-Plus 1x 5,0x25; 1x 5,5x25
⊖	800/1 BTZ 1x 0,8x5,5x25; 1x 1,0x5,5x25; 1x 1,2x6,5x25

NEW

Kraftform Kompakt Stubby ESD 1




Textile box with 25 mm long bits
10-piece set
1 bit-holding 811/1 ESD Stubby, 9 bits

05057472001	
●	811/1 Stubby 1x 1/4"x54 ESD
⊕	851/1 Z PH 1x PH 0x25; 1x PH 1x25; 1x PH 2x25
⊕	851/1 J 1x PH 00x25x2,0
⊖	800/1 Z 1x 0,5x3,0x25; 1x 0,6x4,5x25; 1x 1,0x5,5x25; 1x 1,2x6,5x25; 1x 1,2x8,0x25

Wera Stubby



"Take it easy" tool finder



"Take it easy" tool finder with colour coding according to profiles and size stamp – for simple and rapid accessing of the required tool.

Compact shape



With its compact handle shape and the short blade, the Kraftform Stubbies are particularly suitable for working in confined screwdriving situations.



Wera ESD Tools



demanded by some technology companies.

The requirements for ESD-safe screwdrivers are specified in the European standard DIN EN 61340-5-1. This standard also includes a handle that has to be out of a defined conductive material. The Wera products in the ESD series satisfy these standards and the even more stringent requirements

High protection



The electric surface resistance of the Wera ESD material is $\leq 10^9$ ohm. This securely protects components against electrostatic energy and associated damage.

NEW

Stubby Set 1 screwdriver set



With Take it easy tool finder: Colour coding by profiles and size stamping.

Application: slotted screws and Phillips-head screws Phillips-Recess

Design: 5-piece set in a box

05008870001	
⊖	335 Stubby 1x 0,6x3,5x24,5; 1x 0,8x4,0x24,5; 1x 1,0x5,5x24,5
⊕	350 PH Stubby 1x PH 1x25; 1x PH 2x25

NEW

Stubby Set 2 screwdriver set



With Take it easy tool finder: Colour coding by profiles and size stamping.

Application: slotted screws and Phillips-head screws Pozidriv

Design: 5-piece set in a box

05008871001	
⊖	335 Stubby 1x 0,6x3,5x24,5; 1x 0,8x4,0x24,5; 1x 1,0x5,5x24,5
⊕	355 PZ Stubby 1x PZ 1x25; 1x PZ 2x25

NEW

Stubby Set 3 screwdriver set



With Take it easy tool finder: Colour coding by profiles and size stamping.


Application: slotted screws, Phillips-head screws and square head socket screws

Design: 5-piece set in a box

05008872001	
⊕	350 PH Stubby 1x PH 1x25; 1x PH 2x25
⊖	335 Stubby 1x 1,0x5,5x24,5
○	368 Stubby 1x # 01x25; 1x # 02x25

NEW

Stubby Set TX 1 screwdriver set TORX®



With Take it easy tool finder: Colour coding by profiles and size stamping.

Application: TORX® screws

Design: 5-piece set in a box

05008876001	
⊕	367 TORX® Stubby 1x TX 10x25; 1x TX 15x25; 1x TX 20x25; 1x TX 25x25; 1x TX 27x25

NEW

300/7 Mix 1 screwdriver set



With Take it easy tool finder: Colour coding by profiles and size stamping. 5 Lasertip screwdrivers with long blade, 2 Stubby screwdrivers with short blade

Application: slotted screws and Phillips-head screws Phillips-Recess

Design: 7-piece set in a box + rack

05008900001	
+	350 PH Stubby 1x PH 1x25 ¹⁾ ; 1x PH 2x25 ¹⁾
+	350 PH 1x PH 1x80; 1x PH 2x100
+	334 1x 1,2x6,5x150
-	335 1x 0,5x3,0x80 ¹⁾ ; 1x 1,0x5,5x125
-	Rack 1x 190,0x50,0

¹⁾without Lasertip

NEW

300/7 Mix 2 screwdriver set



With Take it easy tool finder: Colour coding by profiles and size stamping. 5 Lasertip screwdrivers with long blade, 2 Stubby screwdrivers with short blade

Application: slotted screws and Phillips-head screws Pozidriv

Design: 7-piece set in a box + rack

05008901001	
	Rack 1x 190,0x50,0
+	355 PZ Stubby 1x PZ 1x25 ¹⁾ ; 1x PZ 2x25 ¹⁾
+	355 PZ 1x PZ 1x80; 1x PZ 2x200
+	334 1x 1,2x6,5x150
-	335 1x 0,5x3,0x80 ¹⁾ ; 1x 1,0x5,5x125

¹⁾without Lasertip

Wera Stubby



Tangible ergonomics



The 2-component Kraftform handle allows high power transmission due to the non-slip, softer grip areas and high working speeds due to the hard grip areas, which allow a quick hand switch.



Lasertip prevents slipping out



the screw head. Slipping out becomes a thing of the past.

It happens time and time again that the tip slips out of the screw head when screwdriving, sometimes damaging valuable surfaces or even causing injury. The tips of the Wera Lasertip screwdrivers are microscopically roughened by means of a laser. This rough surface literally "bites" itself firmly into the screw head.



Smooth plastic sleeve



The rotating plastic sleeve allows for higher control during screwdriving. In addition, the surface of the rim is protected. The plastic sleeves are interchangeable.



Protection for wheel bolts



The internal plastic insert protects the surfaces of the wheel bolts.

Profile-friendly power transmission



The hexagon profile allows the transmission of high forces and puts less strain on the edges of bolts or screw heads than a double hexagon profile. Fine-toothed ratchets also make the use of a double hexagon profile superfluous, even in confined spaces, thanks to their small back-pivoting angle.



Impact wrench proof



The Wheel Impaktor sockets are designed for use with electric or pneumatic impact wrenches due to their robust Impaktor technology.

NEW

Wheel Impaktor C Set 1 Socket set, 1/2" drive



3-piece

3 Wheel Impaktor sockets with 1/2" drive. For use with impact wrenches, with rotating smooth plastic sleeve for higher working speed, better control during screwdriving and additional rim protection. Take it easy tool finder: Colour coding to enable the desired socket to be easily located.

05004595001	
●	8790 C Wheel Impaktor 1x 17,0x85,0x30,0; 1x 19,0x85,0x30,0; 1x 21,0x85,0x32,0

NEW

8790 C Wheel Impaktor Socket with 1/2" drive



Application: Hexagon headed bolts, screws and nuts

Design: For machine operation (impact), retaining pin hole, interchangeable rotating smooth plastic sleeve, plastic insert to protect the wheel-bolt surfaces; chrome-molybdenum, matt black finish. Take it easy tool finder: Colour coding to enable the desired socket to be easily located.

		mm	mm	mm
05004590001	●	17,0	85,0	30,0
05004591001	●	19,0	85,0	30,0
05004592001	●	21,0	85,0	32,0

NEW

9100 guitar tool set



The set contains tools necessary for setting up and maintenance/repair work concerning guitars.

Wera stainless steel L-keys with Hex-Plus profiles (sizes 1.5, 2.0, 2.5, 5.0 and imperial sizes 1/8", 5/32", 3/16"). Wera 89 mm long stainless steel bits for hexagon socket screws (sizes 1.5, 2.0, 2.5), Kraftform handle for 1/4" bits, 1/4" stainless steel bits for slotted screws (sizes 1.8x 12x41 mm, 0.6x3.5x89 mm, 1.2x 8.0x89 mm), Phillips-head screws (sizes PH 1x89 mm, PH 2x89 mm) and hexagon socket screws (size 0.05"x25 mm), Wera adapter for handle (1/4" hexagon mounting of the handle on 1/4" square head of the sockets), Wera Zyklop sockets (sizes 10 and 1/2"), stringer with 1/4" hexagon to be inserted in the handle, Knipex wire-cutting pliers, slip gauge, Input-Jacker, 2 plectrums.

05134015001		
●	815 R	1x 1/4"x119
⊕	3851/4	1x PH 1x89; 1x PH 2x89
⊖	3800/1 TS	1x 1,8x12,0x41
⊖	3800/4	1x 0,6x3,5x89; 1x 1,2x8,0x89
○	3840/1 TS	1x 0,05"x25x1"
○	3950 PKL	1x 1,5x90; 1x 2,0x101; 1x 2,5x112; 1x 3,0x123; 1x 4,0x137; 1x 5,0x154
○	3950 PKL inch	1x 1/8"x123; 1x 5/32"x137; 1x 3/16"x154
○	870/1	1x 1/4"x25 1)
●	8790 HMA	1x 10,0x23,0
●	8790 HMA	1x 1/2"x50,0
	Deep	
	9103	
	9105	
	9104	
	9001	
	9102	
	9110	
	KNIPEX 74 01	
	140	

Stainless against extraneous rust



The stainless steel bit 3800/1 (1.8 x 12 x 41mm) is ideal for adjusting the screws that secure the Bridge. Stainless steel prevents the formation of extraneous rust on stainless steel components.

Input-Jacker



The Input-Jacker included in the set allows the output socket to be safely positioned at installation and removal. The external hexagon bolt is loosened or tightened with the Zyklop socket.

Stringer for guitars



With the 1/4" hexagon, the stringer can be inserted in the Kraftform 815 R bit-holding screwdriver included in the set. The ergonomic shape of the handle makes it sit comfortably in the hand; the power can be charged precisely. Fits all guitar machine heads.

Angle wrench to adjust the steel bar in the guitar neck



The special Hex-Plus geometry of the angle wrench makes for a better fit of the tool in the screw, reducing the risk of slippage and damage, and significantly improving the power transmission.

NEW

8008 A Zyklop Mini 3 Ratchet with 1/4" drive



Application: 1/4" square sockets and 1/4" adaptors with square drive, equipped with ball lock

Design: Drop-forged full steel design, fine-tooth ratchet mechanism, small return angle of 6°, forward and reverse drive switch

Handle: Kraftform handle with proven Kraftform geometry provides perfectly designed finger contact zones, ergonomic ratchet head and handle

05003793001	1/4"	87,0
-------------	------	------

Zyklop Mini 3 Ratchet



The Zyklop Mini 3 ratchet is the ideal tool for screwdriving in confined spaces. The fine toothing (60 teeth) allows a very low return angle of only 6°; the knurled wheel allows fast screwdriving even when there is no room for pivoting movement.

Zyklop Mini 3 Ratchet



The Zyklop Mini 3 can withstand at least 65 Nm. That is far more power than can normally be transferred to such a small tool.



Individually tested



The individual testing at 10,000 volts, in accordance with IEC 60900, ensures safe working with loads up to 1,000 volts.



VDE-insulated screwdriver with reduced blade diameter



Reduced blade diameter with integrated protective insulation, allows sunken screws and spring elements to be accessed and actuated, individually tested as per IEC 60900.

NEW

165 iS PZ/S # 1 + 2 screwdriver set Kraftform Plus series 100. With reduced blade diameter



Application: combination profile Pozidriv/slotted

Design: 2-piece set in a box

05006470001	165 iS PZ/S	1x # 1x80; 1x # 2x100
-------------	-------------	-----------------------



NEW

Bit-Check 12 Diamond 1 SB



1 bit holder Rapidaptor with quick-release chuck, 11 Bit-Torsion bits for long service life, diamond-coated (BDC) for secure screw fit. The "Take it easy" Bit-Checks have bits with a sleeve which – from its colour and size designation – make it simple to access the right bit quickly.

05136392001	889/4/1 K	●○ 1x 1/4"x50	4013288 213976
	851/1 BDC PH	⊕ 1x PH 1x25; 2x PH 2x25	
	855/1 BDC PZ	⊕ 1x PZ 1x25; 2x PZ 2x25	
	867/1 TORX®	⊕ 1x TX 10x25; 1x TX 15x25; 1x TX 20x25; 1x TX 25x25; 1x TX 30x25	

NEW

Bit-Check 12 Wood 2 SB



1 universal bit holder with stainless steel sleeve, retaining ring, and strong permanent magnet, 11 bits, tough, for universal use.

05136391001	899/4/1	●○ 1x 1/4"x50	4013288 214027
	851/1 Z PH	⊕ 1x PH 2x25	
	855/1 Z PZ	⊕ 1x PZ 1x25; 2x PZ 2x25; 1x PZ 3x25	
	867/1 TORX®	⊕ 1x TX 10x25; 1x TX 15x25; 1x TX 20x25; 1x TX 25x25; 1x TX 30x25; 1x TX 40x25	



Rapidaptor holder



Rapid bit change without needing any additional tools. One-hand operation with a freely spinning sleeve for simplified guidance of the tool. Also available in a Bit-Torsion design.

At the workplace



The Bit-Checks can be positioned upright at the workplace so the tool is always quickly to hand.

NEW

Bit-Check 12 BiTorsion 1 SB



1 bit holder Rapidaptor with quick-release chuck, 11 Bit-Torsion bits for long service life, tough, for universal use. The "Take it easy" Bit-Checks have bits with a sleeve which – from its colour and size designation – make it simple to access the right bit quickly.

05136385001	889/4/1 K	●○ 1x 1/4"x50	4013288 213969
	851/1 BTZ PH	⊕ 1x PH 1x25; 2x PH 2x25	
	855/1 BTZ PZ	⊕ 1x PZ 1x25; 2x PZ 2x25	
	867/1 TORX®	⊕ 1x TX 10x25; 1x TX 15x25; 1x TX 20x25; 1x TX 25x25; 1x TX 30x25	

NEW

Bit-Check 12 Wood 1 SB



1 magnetic Rapidaptor quick-release bit holder with ringmagnet, 11 bits, Torsion-style design to reduce premature wear, extra-hard (TH).

05136390001	887/4 RR	●○ 1x 1/4"x57	4013288 214010
	851/1 TH PH	⊕ 1x PH 2x25	
	855/1 TH PZ	⊕ 1x PZ 1x25; 2x PZ 2x25; 1x PZ 3x25	
	867/1 TORX®	⊕ 1x TX 10x25; 1x TX 15x25; 1x TX 20x25; 1x TX 25x25; 1x TX 30x25; 1x TX 40x25	

NEW

Bit-Check 12 Metal 1 SB



1 universal bit holder with stainless steel sleeve, retaining ring, and strong permanent magnet, 11 bits, tough (Z), for universal use.

05136393001	899/4/1	●○ 1x 1/4"x50	4013288 214003
	851/1 Z PH	⊕ 1x PH 1x25; 1x PH 2x25	
	855/1 Z PZ	⊕ 1x PZ 1x25; 1x PZ 2x25	
	867/1 TORX®	⊕ 1x TX 15x25; 1x TX 20x25; 1x TX 25x25; 1x TX 30x25	
	840/1 Z Hex-Plus	○ 1x 3.0x25; 1x 4.0x25; 1x 5.0x25	

NEW

851/4 Z SB bits



Application: Phillips screws

Drive: 1/4" hexagon, suitable for DIN ISO 1173-F 6.3 bit holders

Design: Tough, for universal use

Part No.	Bit Type	Quantity	Length	Barcode
05136305001	851/4 Z PH	1x PH	1x152	213839
05136306001	851/4 Z PH	1x PH	2x152	213846
05136307001	851/4 Z PH	1x PH	3x152	213853

NEW

855/4 Z SB bits



Application: Suitable for Pozidriv screws

Drive: 1/4" hexagon, suitable for DIN ISO 1173-F 6.3 bit holders

Design: Tough, for universal use

Part No.	Bit Type	Quantity	Length	Barcode
05136308001	855/4 Z PZ	1x PZ	1x152	213860
05136309001	855/4 Z PZ	1x PZ	2x152	213877
05136310001	855/4 Z PZ	1x PZ	3x152	213884

NEW

867/4 Z SB Bits



Application: TORX® socket screws

Drive: 1/4" hexagon, suitable for DIN ISO 1173-F 6.3 bit holders

Design: Tough, for universal use

Part No.	Bit Type	Quantity	Length	Barcode
05136311001	867/4 Z TORX®	1x TX	10x152	213891
05136312001	867/4 Z TORX®	1x TX	15x152	213907
05136313001	867/4 Z TORX®	1x TX	20x152	213914
05136314001	867/4 Z TORX®	1x TX	25x152	213921
05136315001	867/4 Z TORX®	1x TX	30x152	213938
05136316001	867/4 Z TORX®	1x TX	40x152	213945

899/4/1 S Universal Bit Holder with strong retaining ring



Application: Suitable for 1/4" DIN ISO 1173-C 6,3 hexagon insert bits and Wera Series 1

Design: With stainless steel sleeve, strong retaining ring, and strong permanent magnet

Drive: 1/4" hexagon, suitable for power tools with DIN ISO 1173-F 6,3 receiver

Part No.	Length (mm)	Length (in)	Receiver Size (mm)	Receiver Size (in)
05160979001	200	8"	10,5	1/4"
05160981001	300	12"	10,5	1/4"

NEW

840/4 Z SB bits



Application: Hexagon socket screws

Drive: 1/4" hexagon, suitable for DIN ISO 1173-F 6.3 bit holders

Design: Hex-Plus, tough, for universal use

Part No.	Bit Type	Quantity	Length	Barcode
05136301001	840/4 Z Hex-Plus	1x	3.0x152	213792
05136302001	840/4 Z Hex-Plus	1x	4.0x152	213808
05136303001	840/4 Z Hex-Plus	1x	5.0x152	213815
05136304001	840/4 Z Hex-Plus	1x	6.0x152	213822



Tough-absorbing bits



Tough-absorbing Wera bits (Z) prevent any premature breakage of the drive tip.

Universal Bit Holder with strong retaining ring



The retaining ring (S = extra strong) and the strong permanent magnet ensure a particularly secure fitting of the bit in the holder.



8007 B VDE Zyklop ratchet, insulated, with switch lever, with 3/8" drive



Application: 3/8" square sockets as well as for 3/8" adaptors with square drive, with ball locking device

Design: Individually tested as per IEC 60900 at 10,000V for safe working at the approved voltage of 1,000V; slim design to enable work in very confined spaces; fine-tooth mechanism with 80 teeth for a return angle of only 4.5°; switch lever for convenient change of direction; secure socket locking function by push button

		mm
05004966001	3/8"	222,0

8100 SB VDE 1 Zyklop Ratchet set, insulated, switch lever, 3/8" drive, metric



17 pieces; in a surface-preserving, compact and extremely robust textile box; low volume and weight for simplified mobility. Fleece backing and hook and loop fastener system for easy attachment, e. g. on wall, shelf, workshop trolley and the Wera 2go tool transport system. Smooth rotating mechanism for safe storage and easy removal of the Zyklop VDE sockets.

1 Zyklop Ratchet 8007 B VDE, with switch lever, with 3/8" drive, 14 Zyklop VDE sockets, 2 Zyklop VDE extensions, one long, one short, all tools insulated, individually tested as per IEC 60900 at 10,000 V for safe working at the approved voltage of 1,000 V. The Zyklop VDE sockets and extensions offer increased safety through 2-component isolation with yellow insulation core, which becomes visible in case of damage to the outer red VDE insulation layer.

05004970001		
	8007 B VDE	1x 3/8"x222,0
	8790 B VDE	1x 6,0x46,0; 1x 7,0x46,0; 1x 8,0x46,0; 1x 9,0x46,0; 1x 10,0x46,0; 1x 11,0x46,0; 1x 12,0x46,0; 1x 13,0x46,0; 1x 14,0x46,0; 1x 15,0x46,0; 1x 16,0x46,0; 1x 17,0x46,0; 1x 18,0x46,0; 1x 19,0x46,0
	8794 SB VDE	1x 3/8"x91,0
	8794 LB VDE	1x 3/8"x166,0

For tight spaces



The extremely slim design of the Zyklop VDE ratchet makes it easy to work, even in confined spaces.

Ball lock



The ball lock ensures sockets and accessories are securely fitted, providing increased safety during operation. A short press on the release button allows the tool to be changed quickly.

8100 SA All-in Zyklop Speed Ratchet Set, 1/4" drive, with holding function, metric



42-piece set; in a surface-preserving, compact and extremely robust textile box; low volume and weight for simplified mobility. Non-woven reverse side and hook and loop strips for simple attachment e.g. to a wall, shelf, tool trolley and to the Wera 2go tool transport system. Fast and easy Twist to Unlock mechanism for secure storage and simple removal of the sockets.

1 Zyklop Speed Ratchet with 1/4" drive, 13 Zyklop sockets with 1/4" drive with fastener holding function, 9 Zyklop bit sockets for TORX® screws, with 1/4" drive, with holding function (sizes 2.0 and 2.5 without holding function) and Hex-Plus high torque geometry, 3 Zyklop bit sockets with 1/4" drive for Phillips screws, 3 Zyklop bit sockets with 1/4" drive for Pozidriv screws, 2 Zyklop bit sockets with 1/4" drive for slotted screws, "Take it easy" tool finder: Colour coding to enable the desired bit socket to be easily selected, 1 tool for the simple removal of nuts from sockets with holding function, 1 Zyklop extension (long) with free-turning sleeve, 1 wobble extension.

05003755001		
	8000 A	1x 1/4"x152,0
	8796 LA	1x 1/4"x150,0
	8794 A	1x 1/4"x56,0
	8790 HMA HF	1x 4,0x23,0; 1x 4,5x23,0; 1x 5,0x23,0; 1x 5,5x23,0; 1x 6,0x23,0; 1x 7,0x23,0; 1x 8,0x23,0; 1x 9,0x23,0; 1x 10,0x23,0; 1x 11,0x23,0; 1x 12,0x23,0; 1x 13,0x23,0; 1x 14,0x23,0
	8767 A HF	1x TX 8x28,0; 1x TX 9x28,0; 1x TX 10x28,0; 1x TX 15x28,0; 1x 3,7x3,7xTX 20x28,0; 1x 4,1x4,1xTX 25x28,0; 1x 4,8x4,8xTX 27x28,0; 1x 5,4x5,4xTX 30x28,0; 1x 6,5x6,5xTX 40x28,0
	8740 A	1x 2,0x28,0; 1x 2,5x28,0
	8740 A HF	1x 3,0x28,0; 1x 4,0x28,0; 1x 5,0x28,0; 1x 6,0x28,0; 1x 7,0x28,0; 1x 8,0x28,0
	8751 A	1x PH 1x28,0; 1x PH 2x28,0; 1x PH 3x28,0
	8755 A	1x PZ 1x28,0; 1x PZ 2x28,0; 1x PZ 3x28,0
	8700 A FL	1x 0,8x5,5x28,0; 1x 1,2x6,5x28,0
	ME1	1x 14,0x43,0



8100 SC 6 Zyklop Speed Ratchet Set, 1/2" drive, metric



8100 SA 6 Zyklop Speed Ratchet Set, 1/4" drive, metric



28-piece set; in a surface-preserving, compact and extremely robust textile box; low volume and weight for simplified mobility

1 Zyklop Speed Ratchet with 1/4" drive, 9 Zyklop sockets, 1 Zyklop extension (long) with free-turning sleeve, 1 wobble extension, 1 adaptor with quick-release chuck, 15 bits

Part Number	Description	Quantity
05004016001	8000 A	1x 1/4"x152,0
	8790 HMA	1x 5,0x23,0; 1x 5,5x23,0; 1x 6,0x23,0; 1x 7,0x23,0; 1x 8,0x23,0; 1x 10,0x23,0; 1x 11,0x23,0; 1x 12,0x23,0; 1x 13,0x23,0
	8794 LA	1x 1/4"x150,0
	8794 A	1x 1/4"x56,0
	8784 A1	1x 1/4"x1/4"x37,0
	851/4 TZ PH	1x PH 1x50; 1x PH 2x50; 1x PH 3x50
	855/4 TZ PZ	1x PZ 1x50; 1x PZ 2x50
	867/4 Z TORX®	1x TX 10x50; 1x TX 15x50; 1x TX 20x50; 1x TX 25x50; 1x TX 27x50; 1x TX 30x50
	840/4 Z Hex-Plus	1x 3,0x50; 1x 4,0x50; 1x 5,0x50; 1x 6,0x50

8100 SB 6 Zyklop Speed Ratchet Set, 3/8" drive, metric



29-piece set; in a surface-preserving, compact and extremely robust textile box; low volume and weight for simplified mobility

1 Zyklop Speed Ratchet with 3/8" drive, 9 Zyklop sockets, 1 Zyklop extension (long) with free-turning sleeve, 1 wobble extension, 1 adaptor with quick-release chuck, 16 bits

Part Number	Description	Quantity
05004046001	8000 B	1x 3/8"x199,0
	8790 HMB	1x 8,0x29,0; 1x 10,0x29,0; 1x 12,0x29,0; 1x 13,0x29,0; 1x 15,0x29,0; 1x 16,0x30,0; 1x 17,0x30,0; 1x 18,0x30,0; 1x 19,0x30,0
	8794 LB	1x 3/8"x200,0
	8794 B	1x 3/8"x76,0
	8784 B1	1x 1/4"x3/8"x44,0
	851/4 TZ PH	1x PH 1x50; 1x PH 2x50; 1x PH 3x50
	855/4 TZ PZ	1x PZ 1x50; 1x PZ 2x50; 1x PZ 3x50
	867/4 Z TORX®	1x TX 20x50; 1x TX 25x50; 1x TX 27x50; 1x TX 30x50; 1x TX 40x50
	840/4 Z Hex-Plus	1x 4,0x50; 1x 5,0x50; 1x 6,0x50; 1x 8,0x50
	800/4 Z	1x 1,0x5,5x50



Pivots freely



The ratchet head pivots freely and can be locked into any defined position by using the slide switch that is positioned on either side. It is even possible to work in very confined and difficult-to-access areas with enhanced hand clearance. The predefined locking at 0°, 15° and 90°, both to the right and

left, ensure safe working without any slipping of the ratchet head.



Low return angle



The reversible ratchet with 72 fine-pitched teeth has a low return angle of only 5°. This short stroke allows fast and precise work in all types of installation.



28-piece set; in a surface-preserving, compact and extremely robust textile box; low volume and weight for simplified mobility

1 Zyklop Speed Ratchet with 1/2" drive, 10 Zyklop sockets, 1 Zyklop extension (long) with free-turning sleeve, 1 wobble extension, 1 adaptor with quick-release chuck, 14 bits

Part Number	Description	Quantity
05004076001	8000 C	1x 1/2"x277,0
	8790 HMC	1x 10,0x37,0; 1x 11,0x37,0; 1x 12,0x37,0; 1x 13,0x37,0; 1x 14,0x37,0; 1x 15,0x37,0; 1x 16,0x37,0; 1x 17,0x37,0; 1x 18,0x37,0; 1x 19,0x37,0
	8794 LC	1x 1/2"x250,0
	8794 C	1x 1/2"x52,0
	8784 C2	1x 3/16"x1/2"x50,0
	851/2 Z PH	1x PH 2x32; 1x PH 3x32
	855/2 Z PZ	1x PZ 2x32; 1x PZ 3x32
	867/2 Z TORX®	1x TX 20x35; 1x TX 25x35; 1x TX 30x35; 1x TX 40x35; 1x TX 45x35; 1x TX 50x35
	840/2 Z	1x 5x30; 1x 6x30; 1x 8x30; 1x 10x30



8100 SA 7 Zyklop Metal Ratchet Set with push-through square, 1/4" drive, metric



28-piece set; in a surface-preserving, compact and extremely robust textile box; low volume and weight for simplified mobility

1 Zyklop Metal Ratchet with push-through square and 1/4" drive, 9 Zyklop sockets, 1 Zyklop extension (long) with free-turning sleeve, 1 wobble extension, 1 adaptor with quick-release chuck, 15 bits

8100 SB 7 Zyklop Metal Ratchet Set with push-through square, 3/8" drive, metric



29-piece set; in a surface-preserving, compact and extremely robust textile box; low volume and weight for simplified mobility

1 Zyklop Metal Ratchet with 3/8" drive, 9 Zyklop sockets, 1 Zyklop extension (long) with free-turning sleeve, 1 wobble extension, 1 adaptor with quick-release chuck, 16 bits

8100 SC 7 Zyklop Metal Ratchet Set with push-through square, 1/2" drive, metric



28-piece set; in a surface-preserving, compact and extremely robust textile box; low volume and weight for simplified mobility

1 Zyklop Metal Ratchet with push-through square and 1/2" drive, 10 Zyklop sockets, 1 Zyklop extension (long) with free-turning sleeve, 1 wobble extension, 1 adaptor with quick-release chuck, 14 bits

05004077001		
○	8003 C	1x 1/2"x281,0
●	8790 HMC	1x 10,0x37,0; 1x 11,0x37,0; 1x 12,0x37,0; 1x 13,0x37,0; 1x 14,0x37,0; 1x 15,0x37,0; 1x 16,0x37,0; 1x 17,0x37,0; 1x 18,0x37,0; 1x 19,0x37,0
○	8794 LC	1x 1/2"x250,0
○	8794 C	1x 1/2"x52,0
○	8784 C2	1x 5/16"x1/2"x50,0
+	851/2 Z PH	1x PH 2x32; 1x PH 3x32
+	867/2 Z TORX®	1x TX 20x35; 1x TX 25x35; 1x TX 27x35; 1x TX 30x35; 1x TX 40x35; 1x TX 45x35; 1x TX 50x35; 1x TX 55x35
○	840/2 Z	1x 5x30; 1x 6x30; 1x 8x30; 1x 10x30

05004017001		
○	8003 A	1x 1/4"x141,0
●	8790 HMA	1x 5,0x23,0; 1x 5,5x23,0; 1x 6,0x23,0; 1x 7,0x23,0; 1x 8,0x23,0; 1x 10,0x23,0; 1x 11,0x23,0; 1x 12,0x23,0; 1x 13,0x23,0
○	8794 LA	1x 1/4"x150,0
○	8794 A	1x 1/4"x56,0
○	8784 A1	1x 1/4"x1/4"x37,0
+	851/1 Z PH	1x PH 1x25; 1x PH 2x25; 1x PH 3x25
+	855/1 Z PZ	1x PZ 1x25; 1x PZ 2x25
+	867/1 TORX®	1x TX 10x25; 1x TX 15x25; 1x TX 20x25; 1x TX 25x25; 1x TX 27x25; 1x TX 30x25
○	840/1 Z Hex-Plus	1x 3,0x25; 1x 4,0x25; 1x 5,0x25; 1x 6,0x25

05004047001		
○	8003 B	1x 3/8"x222,0
●	8790 HMB	1x 8,0x29,0; 1x 10,0x29,0; 1x 12,0x29,0; 1x 13,0x29,0; 1x 15,0x29,0; 1x 16,0x30,0; 1x 17,0x30,0; 1x 18,0x30,0; 1x 19,0x30,0
○	8794 LB	1x 3/8"x200,0
○	8794 B	1x 3/8"x76,0
○	8784 B1	1x 1/4"x3/8"x44,0
+	851/1 Z PH	1x PH 1x25; 1x PH 2x25; 1x PH 3x25
+	855/1 Z PZ	1x PZ 1x25; 1x PZ 2x25
+	867/1 TORX®	1x TX 15x25; 1x TX 20x25; 1x TX 25x25; 1x TX 27x25; 1x TX 30x25; 1x TX 40x25
○	840/1 Z Hex-Plus	1x 3,0x25; 1x 4,0x25; 1x 5,0x25; 1x 6,0x25; 1x 8,0x25



Square drive



Smooth push-through mechanism, that cannot get lost.




Dual ratchet teeth



The dual-ratchet-teeth design means that a 76 fine-toothing division can be achieved from the 38 robust teeth with a return angle of only 4.7°.



Belt C Impaktor 1 socket set, 1/2" drive



9-piece; robust textile socket belt, including snap hook to enable secure fastening to a belt loop or pocket. Non-woven reverse side and hook and loop strips for simple attachment e.g. to a wall, shelf, tool trolley and to the Wera 2go tool transport system. Fast and easy Twist to Unlock mechanism for secure storage and simple removal of the sockets.

9 Impaktor sockets with 1/2" drive, with hexagonal profile and grooved socket. For use with electric or pneumatic powered impact wrenches with 12.5mm = 1/2" drive. "Take it easy" tool finder: Colour coding to enable the desired socket to be easily selected.

05004580001		
●	8790 C Impaktor	1x 13,0x38,0; 1x 14,0x38,0; 1x 15,0x38,0; 1x 16,0x38,0; 1x 17,0x38,0; 1x 18,0x38,0; 1x 19,0x38,0; 1x 20,0x38,0; 1x 21,0x38,0
	Belt C Impaktor 0/9 K30	1x 71,0x210,0 1x 30,0x200,0

For electric or pneumatic impact wrenches



The Impaktor technology ensures above-average service life of the Impaktor socket wrench plug-ins even under extreme conditions.

Profile-friendly power transmission



The hexagon profile allows the transmission of high forces and puts less strain on the edges of bolts or screw heads than a double hexagon profile. Fine-toothed ratchets also make the use of a double hexagon profile superfluous, even in confined spaces, thanks to their small back-pivoting angle.

8100 SA 8 Zyklop Metal Ratchet Set with switch lever, 1/4" drive, metric



28-piece set; in a surface-preserving, compact and extremely robust textile box; low volume and weight for simplified mobility

1 Zyklop Metal Ratchet with switch lever and 1/4" drive, 9 Zyklop sockets, 1 Zyklop extension (long) with free-turning sleeve, 1 wobble extension, 1 adaptor with quick-release chuck, 15 bits

05004018001		
●	8004 A	1x 1/4"x141,0
●	8790 HMA	1x 5,0x23,0; 1x 5,5x23,0; 1x 6,0x23,0; 1x 7,0x23,0; 1x 8,0x23,0; 1x 10,0x23,0; 1x 11,0x23,0; 1x 12,0x23,0; 1x 13,0x23,0
●	8794 LA	1x 1/4"x150,0
●	8794 A	1x 1/4"x56,0
●	8784 A1	1x 1/4"x1/4"x37,0
+	851/1 Z PH	1x PH 1x25; 1x PH 2x25; 1x PH 3x25
+	855/1 Z PZ	1x PZ 1x25; 1x PZ 2x25
+	867/1 TORX®	1x TX 10x25; 1x TX 15x25; 1x TX 20x25; 1x TX 25x25; 1x TX 27x25; 1x TX 30x25
○	840/1 Z Hex-Plus	1x 3,0x25; 1x 4,0x25; 1x 5,0x25; 1x 6,0x25

8100 SC 8 Zyklop Metal Ratchet Set with switch lever, 1/2" drive, metric



28-piece set; in a surface-preserving, compact and extremely robust textile box; low volume and weight for simplified mobility

1 Zyklop Metal Ratchet with switch lever and 1/2" drive, 10 Zyklop sockets, 1 Zyklop extension (long) with free-turning sleeve, 1 wobble extension, 1 adaptor with quick-release chuck, 14 bits

05004078001		
●	8004 C	1x 1/2"x281,0
●	8790 HMC	1x 10,0x37,0; 1x 11,0x37,0; 1x 12,0x37,0; 1x 13,0x37,0; 1x 14,0x37,0; 1x 15,0x37,0; 1x 16,0x37,0; 1x 17,0x37,0; 1x 18,0x37,0; 1x 19,0x37,0
●	8794 LC	1x 1/2"x250,0
●	8794 C	1x 1/2"x52,0
●	8784 C2	1x 5/16"x1/2"x50,0
+	851/2 Z PH	1x PH 2x32; 1x PH 3x32
+	867/2 Z TORX®	1x TX 20x35; 1x TX 25x35; 1x TX 27x35; 1x TX 30x35; 1x TX 40x35; 1x TX 45x35; 1x TX 50x35; 1x TX 55x35
○	840/2 Z	1x 5x30; 1x 6x30; 1x 8x30; 1x 10x30



Secure hold and easy removal



The all new smooth turning mechanism guarantees both secure and rattle-free storage, yet allows easy removal of the tool.



Practical nonwoven strips



The textile belt can be attached by means of the nonwoven reverse side and the hook and loop strips e.g. to a wall, shelf, tool trolley and to the Wera 2go tool transport system.



Zyklop Mini tool sets



Available in a set with the dependable Wera Bit-Check with socket adaptor and belt clip. Simple fitting and removal of tools. Very robust and a long service life.

Is such a small tool sufficiently resilient?



The Zyklop Mini 1 can withstand at least 65 Nm. That is far more power than can normally be transferred to such a small tool.

When is the Zyklop Mini 1 needed?



Particularly when the space is confined and there is not much room for the tool.

Tool-Check PLUS



28 bits, 1 bit-holding 813 suitable for the attachment of bits with 1/4" hexagon drive as per DIN ISO 1173-C 6.3 and Wera connection series 1, 1 Rapidaptor bit holder, 1 adaptor 870/1 (1/4" hexagon to 1/4" square), 7 sockets (1/4"); 1 Wera Bit Ratchet Zyklop Mini 1, drop-forged full steel design suitable for the attachment of bits with 1/4" hexagon drive as per DIN ISO 1173-C 6.3 and E 6.3 and Wera connection series 1 and 4; the use of 1/4" sockets is also possible with the application of the Wera adaptor 870/1

05056490001	8001 A	1x 1/4"x87,0
●	813	1x 1/4"x78
●	889/4/1 K	1x 1/4"x50
○	870/1	1x 1/4"x25 ¹⁾
●	8790 HMA	1x 5,5x23,0; 1x 6,0x23,0; 1x 7,0x23,0; 1x 8,0x23,0; 1x 10,0x23,0; 1x 12,0x23,0; 1x 13,0x23,0
+	851/1 TZ PH	2x PH 1x25; 3x PH 2x25; 1x PH 3x25
+	855/1 TH PZ	1x PZ 1x25; 3x PZ 2x25; 1x PZ 3x25
+	867/1 TZ TORX®	1x TX 10x25; 1x TX 15x25; 1x TX 20x25; 1x TX 25x25; 1x TX 30x25; 1x TX 40x25
+	867/1 Z TORX® B0	1x TX 10x25; 1x TX 15x25; 1x TX 20x25; 1x TX 25x25; 1x TX 30x25
○	840/1 Z Hex-Plus	1x 3,0x25; 1x 4,0x25; 1x 5,0x25; 1x 6,0x25; 1x 8,0x25
●	800/1 TZ	1x 1,0x5,5x25

¹⁾With friction ball; for manual nut spinner sockets



Hex-Plus



Hexagon screws can endure a problem because the contact surfaces delivering the power from the conventional tool, is transferred to the screw via very small surface areas. The consequence: the screw can become damaged (rounding out). Hex-Plus tools have a greater contact surface that

prevents this from happening! At the same time, as much as 20 % more torque can be applied. Good to know: Hex-Plus tools fit into every standard hexagon socket screw!

At the workplace



The Bit-Checks can be positioned upright at the workplace so the tool is always quickly to hand.

Bit-Check 30 Metal 1



1 universal bit holder with stainless steel sleeve, retaining ring, and strong permanent magnet, 29 bits, tough, for universal use.

05057434001	●	899/4/1	1x 1/4"x50
	+	851/1 Z PH	3x PH 1x25; 3x PH 2x25; 2x PH 3x25
	+	855/1 Z PZ	3x PZ 1x25; 3x PZ 2x25; 3x PZ 3x25
	+	867/1 TORX®	1x TX 10x25; 1x TX 15x25; 1x TX 20x25; 1x TX 25x25; 1x TX 30x25; 1x TX 40x25
	●	800/1 Z	1x 0,6x4,5x25; 1x 1,0x5,5x25; 1x 1,2x6,5x25
	○	840/1 Z Hex-Plus	1x 4,0x25; 1x 5,0x25; 1x 6,0x25

Bit-Check 30 Wood 2



1 universal bit holder with stainless steel sleeve, retaining ring, and strong permanent magnet, 29 bits, tough, for universal use.

05057432001	●	899/4/1	1x 1/4"x50
	+	851/1 Z PH	1x PH 2x25
	+	855/1 Z PZ	2x PZ 1x25; 5x PZ 2x25; 2x PZ 3x25
	+	867/1 TORX®	3x TX 10x25; 4x TX 15x25; 4x TX 20x25; 4x TX 25x25; 3x TX 30x25; 1x TX 40x25

Bit-Check 30 TX Universal 1



1 universal bit holder with stainless steel sleeve, retaining ring, and strong permanent magnet, 29 bits, tough, for universal use.

05057908001	●	899/4/1	1x 1/4"x50
	+	867/1 TORX®	3x TX 10x25; 5x TX 15x25; 8x TX 20x25; 7x TX 25x25; 4x TX 30x25; 2x TX 40x25



6000 Joker 4 Set 1 Set of ratcheting combination wrenches



Set of ratcheting combination wrenches
4-piece set
Durable pouch

05073290001	6000 Joker	1x 10x159; 1x 13x177; 1x 17x224; 1x 19x246
-------------	------------	--

6001 Joker Switch 4 Set 1 Set of ratcheting combination wrenches



Set of ratcheting combination wrenches, reversible
4-piece set
Durable pouch

05020090001	6001 Joker Switch	1x 10x159; 1x 13x179; 1x 17x225; 1x 19x246
-------------	-------------------	--

6001 Joker Switch 11 Set 1 Set of ratcheting combination wrenches



Set of ratcheting combination wrenches, reversible
11-piece set
Durable pouch

05020091001	6001 Joker Switch	1x 8x144; 1x 10x159; 1x 11x165; 1x 12x171; 1x 13x179; 1x 14x187; 1x 15x199; 1x 16x213; 1x 17x225; 1x 18x234; 1x 19x246
-------------	-------------------	--

6000 Joker 11 Set 1 of ratcheting combination wrenches



Set of ratcheting combination wrenches
11-piece set
Durable pouch

05020013001	6000 Joker	1x 8x144; 1x 10x159; 1x 11x165; 1x 12x170,7; 1x 13x177; 1x 14x188; 1x 15x200; 1x 16x212; 1x 17x224; 1x 18x235; 1x 19x246
-------------	------------	--



Holding function



The Joker's holding function means that nuts and bolts can be held in the jaw and easily positioned where they are needed. Fastening on to the thread can then be done quickly and safely, thanks to the innovative special stop-plate which holds the fastener. No more time-wasting searches

for dropped nuts and bolts! After applying and positioning the nut or bolt, fastening can begin immediately – no additional tools required.



Integrated limit-stop



Constant re-positioning of the wrench? Difficulty holding fasteners in confined spaces? Easing off to avoid any risks of injury or fastener damage? That was yesterday. Today, the Joker prevents slipping off of the fastener head with its integrated limit-stop – no longer is the thumb needed to

act as a depth stop. This makes applications much easier and allows significantly more force to be applied during fastening jobs.



Small return angle



Instead of 60°, the Joker only has a 30° return angle thanks to its unique double-hex design. Along with the Joker's straight neck, this means that flipping the wrench has become a thing of the past. With the Joker, you can now loosen and tighten nuts and bolts, in situations where conventional

tools fail. Particularly in confined spaces, where conventional open-jawed wrenches cannot be used. The combination of limit stop and small return angle enables effective work, even on screw pipe connections.



Wera 2go 2 Tool Container



1 dimensionally stable, robust Tool Container with hook and loop fastener system for the attachment of other Wera 2go components as well as Wera textile boxes and pouches with hook and loop fastener zones; high resistance against cuts and stabs; 1 handle and 1 Shoulder Strap with adjustable-width padding, adjustable in length, detachable; 1 removable Tool Quiver with handle and a variable hook and loop fastener partition for a division into as many as 5 inner sections.

05004351001		
Wera 2go Container	1x 355,0x330,0x115,0	
Wera 2go 6	1x 38,0x1470,0	
Wera 2go 4	1x 165,0x165,0x105,0	

Wera 2go 7 High Tool Box



1 sturdy, robust High Tool Box, with carrying handle, for storage and transport of long tools and spare parts. High resistance against cuts and stabs. With hook and loop fastener zones for docking onto the Wera 2go system.

Code	mm	mm	mm
05004356001	295,0	100,0	100,0

Versatile



Wera 2go Tool Container XL with inner and outer hook and loop fastener system. Individually configurable for greater mobility. Ideal also for the docking of Wera textile boxes and pouches equipped with hook and loop fastener zones. Easy insertion and removal. Hands remain free during transport.

during transport.

Wera 2go 2 XL Tool Container



Many tools can be taken in this particularly large tool container. Up to four Wera 2go 4 Tool Quivers can be stored in the XL container. This ensures order and clarity of contents.

Wera 2go 2 XL Tool Container



1 dimensionally stable, robust Tool Container for up to four Wera 2 go 4 Tool Quivers; with hook and loop fastener system for the attachment of other Wera 2go components as well as Wera textile boxes and pouches with hook and loop fastener zones; high resistance against cuts and stabs; 1 handle and 1 Shoulder Strap with adjustable-width padding, adjustable in length, detachable; 1 removable Tool Quiver with handle

05004357001		
Wera 2go XL Container	1x 455,0x330,0x170,0	
Wera 2go 6	1x 38,0x1470,0	
Wera 2go 4	1x 165,0x165,0x105,0	


Wera 2go 3 Tool Box



1 dimensionally stable and robust Tool Box, empty, equipped with handle for the storage and transport of tools and small parts; high resistance against cuts and stabs; comes with hook and loop fastener zone for docking with the Wera 2go system.

Code	mm	mm	mm
05004352001	130,0	325,0	80,0

Kraftform Kompakt 60



Pouch with 89 mm bits

17-piece set

1 Kraftform bitholding screwdriver 816 R with Rapidaptor quick-release chuck

05059295001		
816 R	1x 1/4"x119	
851/4 Z PH	1x PH 1x89; 1x PH 2x89; 1x PH 3x89	
855/4 Z PZ	1x PZ 1x89; 1x PZ 2x89; 1x PZ 3x89	
867/4 Z TORX® BO	1x TX 10x89; 1x TX 15x89; 1x TX 20x89; 1x TX 25x89; 1x TX 30x89	
800/4 Z	1x 1,0x5,5x89	
840/4 Z Hex-Plus	1x 3,0x89; 1x 4,0x89; 1x 5,0x89; 1x 6,0x89	

Kraftform Kompakt W 1 Maintenance



35-piece set; in surface-protecting, compact textile box, highly robust; low volume and weight for simplified mobility.

Compact tool set with the most important screwdriving tools for maintenance jobs both indoors as well as outdoors. VDE screwdriver handle including 12 VDE blades; 1 Joker double open-ended wrench with holding function, limit stop, small return angle and extremely high-grip toothing; incl. the incredibly fast 1/4" Zyklop Speed ratchet with accessories; 8 manual and power tool sockets in the dimensions 5.5-13, 1 universal bit holder; 7 25mm bits; 1 screw gripper to firmly hold screws; 1 voltage tester 247; textile box that is very robust and durable; can be positioned upright in the workshop shelf for tidy storage; additional surface protection thanks to the textile outer material; low weight and volume for simplified mobility.

05135926001	
●	817 VDE 1x 9x102
●	KK 60 i 1x 0,4x2,5x154
●	KK 60 iS 1x 0,6x3,5x154; 1x 0,8x4,0x154; 1x 1,0x5,5x154
+	KK 62 iS 1x PH 1x154; 1x PH 2x154
+	KK 65 iS PZ 1x PZ 1x154; 1x PZ 2x154
+	KK 67 i TORX® 1x TX 10x154
+	KK 67 iS 1x TX 15x154; 1x TX 20x154; 1x TX 25x154 TORX®
○	1440 1x 4,5 - 6,0x41,0
○	247 1x 0,5x3,0x70
○	6002 Joker Double 1x 10x13x167
○	8000 A 1x 1/4"x152,0
○	8784 A1 1x 1/4"x1/4"x37,0
○	8794 SA 1x 1/4"x75,0
○	8790 HMA 1x 5,5x23,0; 1x 6,0x23,0; 1x 7,0x23,0; 1x 8,0x23,0; 1x 10,0x23,0; 1x 11,0x23,0; 1x 12,0x23,0; 1x 13,0x23,0
○	893/4/1 K 1x 1/4"x50
+	855/1 Z PZ 1x PZ 1x25; 1x PZ 2x25
○	840/1 Z Hex-Plus 1x 3,0x25; 1x 4,0x25; 1x 5,0x25; 1x 6,0x25
+	867/1 TORX® 1x TX 25x25

Handle/interchangeable blade system – Kraftform Kompakt VDE




The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

Individually tested



Each Kraftform Kompakt VDE set has been tested individually at 10,000 volts, in accordance with IEC 60900. This ten-times-higher testing load guarantees safe working at their maximum permitted load of 1,000 volts.



Joker Ratcheting combination wrenches



The Joker's holding function means that nuts and bolts can be held in the jaw and easily positioned where they are needed. Fastening on to the thread can then be done quickly and safely, thanks to the innovative special stop-plate which holds the fastener. No more time-wasting searches

for dropped nuts and bolts! After applying and positioning the nut or bolt, fastening can begin immediately – no additional tools required.



Hollow shaft nutsetter



A screwdriver with a hollow shaft is needed whenever there are screwdriving jobs involving threaded rods i.e. the threaded rod through the nut can slip into the hollow shaft of the screwdriver.



Kraftform Kompakt SH 2 PlumbKit



15-piece set; in a surface-preserving, compact and extremely robust textile box; low volume and weight for simplified mobility.

1 Kraftform chiseldriver 932 A (slotted) with pound-thru hexagonal blade and integrated impact cap for screwdriving and light chiselling; 2 socket wrench screwdrivers 395 H0 with hollow shaft for tightening or loosening nuts on protruding threaded rods as well as fixed screws; 1 Kraftform Kompakt VDE handle, 4 Kraftform Kompakt VDE interchangeable blades with reduced blade diameter and integrated protective insulation, so low-lying screws can be accessed, individually tested as per IEC 60900; 1 voltage tester 247, 2 Joker Switch ratcheting combination wrenches with holding function for nuts and bolts, protecting against slippage, double hexagon geometry and extremely hard tips on the metal plate to protect against slippage at high torques, with a small return angle of 30°, switch lever for a comfortable direction change, ring end angled at 15° from the handle; 4 L-keys with Hex-Plus profile (prevents the rounding of hexagon socket screws), with holding function for hexagon socket screws, hexagonal ball-end on the long arm, BlackLaser surface, plastic sleeve, all L-keys are easily identified by their colour coding and size marking.

05136026001	
●	395 H0 1x 10,0x90; 1x 13,0x90
●	932 A 1x 1,2x7,0x125
○	6001 Joker Switch 1x 10x159; 1x 13x179
○	950 SPKL HF Multicolour 1x 3,0x123; 1x 4,0x137; 1x 5,0x154; 1x 6,0x172
●	817 VDE 1x 9x102
+	KK 62 iS 1x PH 1x154; 1x PH 2x154
●	KK 60 iS 1x 0,6x3,5x154; 1x 1,0x5,5x154
○	247 1x 0,5x3,0x70
○	K240 1x 50,0x240,0

^{*)} Product not available in the USA and Canada.

Kraftform Kompakt VDE 17 extra slim 1



17-piece set


2 Kraftform handles 817 VDE for Wera VDE interchangeable blades only

14 VDE interchangeable blades (each 154 mm long) with reduced blade diameter (articles KK 60 i 0,4x2,5 and KK 67 i TX 10 conventional diameter) with integrated protective insulation, allows sunken screws and spring elements to be accessed and actuated

1 pair of Knipex electrical installation pliers VDE 13 96 200; for cutting, stripping, gripping, bending, deburring and crimping. With pawl for gentle gripping. Chrome-plated for better rust protection, with insulated multi-component grip sheaths.

05136027001		
●	817 VDE	2x 9x102
+	KK 62 iS	1x PH 1x154; 1x PH 2x154
+	KK 65 iS PZ	1x PZ 1x154; 1x PZ 2x154
+	KK 65 iS PZ/S	1x # 1x154; 1x # 2x154
⊗	KK 67 i TORX®	1x TX 10x154
⊗	KK 67 iS TORX®	1x TX 15x154; 1x TX 20x154; 1x TX 25x154
⊖	KK 60 i	1x 0,4x2,5x154
⊖	KK 60 iS	1x 0,6x3,5x154; 1x 0,8x4,0x154; 1x 1,0x5,5x154
	KNIPLEX 13 96 200	
	K70	1x 50,0x70,0

Kraftform Kompakt VDE



conforming to the industrial standards.

The system "one handle – many interchangeable blades" makes Kraftform Kompakt VDE compact screwdriving sets for in-house as well as mobile electrical applications out of the sets. The belt pouch is practical for tidy storage and transportation. Also available with electrical cabinet keys

Kraftform Kompakt 20 Tool Finder 2 with pouch



Application: Suitable for 1/4" DIN ISO 1173-C 6.3 and E 6.3 hexagon socket insert bits and Wera Series 1 and 4

Design: Attachment, telescopic, Rapidaptor rapid-in, rapid-out, rapid-spin, chuck-all and single-hand technology; "Take it easy" tool finder: Output colour coding and large stamp to enable the desired bit to be easily located. Bits with high corrosion protection due to nickel chemical coating.

Handle: Kraftform with non-roll feature, multi-component, integrated magazine

05051017001		
●	889/4 R	1x 1/4"x100
+	851/1 BTZ PH	1x PH 1x25; 1x PH 2x25
+	855/1 BTZ PZ	1x PZ 1x25; 1x PZ 2x25
⊗	867/1 TORX® BTZ	1x TX 20x25; 1x TX 25x25
+	851/4 Z PH	1x PH 1x89; 1x PH 2x89
+	855/4 Z PZ	1x PZ 1x89; 1x PZ 2x89
⊗	867/4 Z TORX®	1x TX 20x89; 1x TX 25x89



Bicycle Set Torque 1




16 piece-set; in a surface protecting, compact and extremely robust textile box; low volume and weight for simplified mobility.

1 Click-Torque torque wrench A 5 with 1/4" square drive, covering a range of 2.5 Nm-25 Nm, accuracy ± 4% of the set value, as per DIN EN ISO 6789-1: 2017-07, for clockwise torque control, reversible ratchet, 45 teeth, easy setting and saving of the desired torque value, with audible and tactile locking when the scale values are reached (fine scale only in Newton meters), audible and tactile release mechanism when the set torque value is reached, ergonomic 2-component handle, 4 Zyklop sockets, with 1/4" drive, 4 Zyklop bit sockets for TORX® screws, with 1/4" drive, with holding function, 7 bit sockets for hexagon socket screws with 1/4" drive with holding function; Take it easy tool finder: Colour coding to enable the desired bit socket to be easily selected

05004180001		
	Click-Torque A 5	1x 1/4", 2,5-25 Nm
●	8790 HMA	1x 10,0x23,0; 1x 13,0x23,0; 1x 14,0x23,0; 1x 15,0x23,0
⊗	8767 A HF	1x TX 10x28,0; 1x 3,7x3; 7xTX 20x28,0; 1x 4,1x4; 1xTX 25x28,0; 1x 5,4x5; 4xTX 30x28,0
○	8740 A HF	1x 3,0x28,0; 1x 4,0x28,0; 1x 5,0x28,0; 1x 5,0x100,0; 1x 6,0x28,0; 1x 6,0x100,0; 1x 8,0x28,0



Click-Torque A 6 Set 1



20 piece-set; in a surface protecting, compact and extremely robust textile box; low volume and weight for simplified mobility.

1 Click-Torque A 6 torque wrench with 1/4" hexagon drive, covering a range of 2,5 Nm-25 Nm, accuracy ± 4% of the set value, as per DIN EN ISO 6789-1: 2017-07, for clockwise torque control, reversible ratchet, 45 teeth, easy setting and saving of the desired torque value, with audible and tactile locking when the scale values are reached (fine scale only in Newton meters), audible and tactile release mechanism when the set torque value is reached, ergonomic 2-component handle, 6 Zyklop sockets, 1 adapter 1/4" hexagon to 1/4" square, 1 Zyklop extension with free-turning sleeve, short, 11 bits

05130110001	Click-Torque A 6	1x 1/4", 2,5-25 Nm
+	851/4 TZ PH	1x PH 2x50
+	867/4 Z TORX®	1x TX 15x50; 1x TX 20x50; 1x TX 25x50; 1x TX 27x50; 1x TX 30x50; 1x TX 40x50
○	840/4 Z Hex-Plus	1x 3,0x50; 1x 4,0x50; 1x 5,0x50; 1x 6,0x50
○	870/1	1x 1/4"x25 ¹⁾
○	8794 SA	1x 1/4"x75,0
●	8790 HMA	1x 6,0x23,0; 1x 7,0x23,0; 1x 8,0x23,0; 1x 10,0x23,0; 1x 12,0x23,0; 1x 13,0x23,0
	K240	1x 50,0x240,0


¹⁾With friction ball; for manual nut spinner sockets

Click-Torque

Simple and safe



Easy setting and saving of the desired torque value; readable on the main and fine scales.




Simple setting



With audible and tactile clicks when adjusting the scale values.

Release mechanism



When the set torque value is reached, an audible and tactile mechanism triggers.



Bit sockets with retaining function for hexagon socket screws



The clamping of the screw is achieved by a flexible locking ball. The holding function is especially helpful in confined, hard-to-reach spaces, where there is no room for a second hand to secure the screw.

Click-Torque C 3 Set 1



13 piece-set; in a surface protecting, compact and extremely robust textile box; low volume and weight for simplified mobility.

1 Click-Torque torque wrench C 3 with 1/2" square drive, covering a range of 40 Nm-200 Nm, accuracy ± 3% of the set value, as per DIN EN ISO 6789-1: 2017-07, for clockwise torque control, reversible ratchet, 45 teeth, easy setting and saving of the desired torque value, with audible and tactile locking when the scale values are reached (fine scale only in Newton meters), audible and tactile release mechanism when the set torque value is reached, ergonomic 2-component handle, 4 Zyklop sockets, 4 Zyklop bit sockets with holding function for TORX® screws made according to Acument Intellectual Properties specifications, 3 Zyklop bit sockets with holding function for hexagon socket screws, 1 Zyklop extension with free-turning sleeve

05075680001	Click-Torque C 3	1x 1/2", 40-200 Nm
●	8790 HMC	1x 10,0x37,0; 1x 13,0x37,0; 1x 17,0x37,0; 1x 19,0x37,0
+	8767 C HF	1x 5,4xTX 30x60,0; 1x 6,5xTX 40x60,0; 1x TX 45x60,0; 1x TX 50x60,0
○	8740 C HF	1x 6,0x60,0; 1x 8,0x60,0; 1x 10,0x60,0
○	8794 SC	1x 1/2"x125,0



950/9 L Hex-Plus HF 1 L-key set, metric, chrome-plated, with holding function



9-piece set in a two-component clip

Application: Hexagon socket screws

Design: Chrome-plated

Tip: Hex-Plus, holding function for hexagon socket screws on long arm, sizes: 1,5, 2,0 and 2,5 without holding function

05022130001			
○	950 L	1x 1,5x90 ¹⁾ ; 1x 2,0x100; 1x 2,5x112	
○	950 L HF	1x 3,0x126; 1x 4,0x140; 1x 5,0x160; 1x 6,0x180; 1x 8,0x200; 1x 10,0x219	

¹⁾Regular hexagon



With retaining function on long arm



The clamping of the screw is achieved by a flexible locking ball. The holding function is especially helpful in confined, hard-to-reach spaces, where there is no room for a second hand to sec



Hex-Plus



Hexagon socket screws are a problem, because the contact surfaces that transfer the force of the tool to the screw are very narrow. The consequence: the head of the screw can be damaged, usually rounding out the recess. Hex-Plus tools have larger contact surfaces to prevent this, driving from the flats of the recess, rather than the corners. Good to know: Hex-Plus tools fit into every standard hexagon socket screw!

950/9 Hex-Plus Multicolour 1 SB Multicolour L-key set, metric, BlackLaser



9-piece set in a two-component clip

Application: Hexagon socket screws

Design: BlackLaser surface, durable plastic sleeve. The contrasting inscriptions on the colour-coded sleeves mean that it is easy to recognise the correct sizes and this makes it simpler to find the right tool.

Tip: Hex-Plus, ball-end hexagon on long arm

05073593001	950 SPKL Multicolour	○ 1x 1.5x90; 1x 2.0x101; 1x 2.5x112; 1x 3.0x123; 1x 4.0x137; 1x 5.0x154; 1x 6.0x172; 1x 8.0x195; 1x 10.0x224	4013288 165688
-------------	-----------------------------	--	-------------------

950/9 Hex-Plus Multicolour HF 1 L-key set, metric, BlackLaser, with holding function



9-piece set in a two-component clip

Application: Hexagon socket screws

Design: BlackLaser surface, durable plastic sleeve. The contrasting inscriptions on the colour-coded sleeves mean that it is easy to recognise the correct sizes and this makes it simpler to find the right tool.

Tip: Hex-Plus, ball-end hexagon on long arm, holding function for hexagon socket screws, sizes: 1,5, 2,0 and 2,5 without holding function

05022210001			
○	950 SPKL Multicolour	1x 1,5x90; 1x 2,0x101; 1x 2,5x112	
○	950 SPKL HF Multicolour	1x 3,0x123; 1x 4,0x137; 1x 5,0x154; 1x 6,0x172; 1x 8,0x195; 1x 10,0x224	

950/9 Hex-Plus Multicolour 2 L-key set, metric, BlackLaser



9-piece set in a two-component clip

Application: Hexagon socket screws

Design: BlackLaser surface, durable plastic sleeve. The contrasting inscriptions on the colour-coded sleeves mean that it is easy to recognise the correct sizes and this makes it simpler to find the right tool.

Tip: Hex-Plus, ball-end hexagon on long arm

05133164001			
○	950 SPKS Multicolour	1x 1,5x50; 1x 2,0x56; 1x 2,5x63; 1x 3,0x71; 1x 4,0x80; 1x 5,0x90; 1x 6,0x100; 1x 8,0x112; 1x 10,0x125	

3950/9 Hex-Plus Multicolour Stainless 1 L-key set, metric, stainless



9-piece set in a two-component clip

Application: Hexagon socket screws

Design: Stainless steel, durable plastic sleeve. The contrasting inscriptions on the colour-coded sleeves mean that it is easy to recognise the correct sizes and this makes it simpler to find the right tool.

Tip: Hex-Plus, ball-end hexagon on long arm

05022669001			
○	3950 SPKL Multicolour	1x 1,5x90; 1x 2,0x101; 1x 2,5x112; 1x 3,0x123; 1x 4,0x137; 1x 5,0x154; 1x 6,0x172; 1x 8,0x195; 1x 10,0x224	

950/9 Hex-Plus 1 SB L-key set, metric, chrome-plated



9-piece set in a two-component clip

Application: Hexagon socket screws

Design: Chrome-plated

Tip: Hex-Plus, ball-end hexagon on long arm

05073391001	950 PKL	1x 1.5x90 ¹⁾ ; 1x 2.0x100; 1x 2.5x112; 1x 3.0x126; 1x 4.0x140; 1x 5.0x160; 1x 6.0x180; 1x 8.0x200; 1x 10.0x219	030160
-------------	---------	---	--------

¹⁾ Regular hexagon

967/9 TX XL Multicolour 1 Multicolour L-key set for TORX® screws, long



9-piece set in a two-component clip

Application: TORX® socket screws

Design: Round, zinc-phosphated, durable plastic sleeve. The contrasting inscriptions on the colour-coded sleeves mean that it is easy to recognise the correct sizes and this makes it simpler to find the right tool.

Tip: TORX® on short arm, TORX® ball end on long arm, TX 8, TX 9, TX 10: without ball-end at the long arm

05024480001	967 SXL TORX® Multicolour	1x TX 8x90; 1x TX 9x101; 1x TX 10x112
	967 SPKXL TORX® Multicolour	1x TX 15x123; 1x TX 20x137; 1x TX 25x154; 1x TX 27x172; 1x TX 30x195; 1x TX 40x224

967/9 TX Multicolour HF 1 L-key set with holding function



9-piece set in a two-component clip

Application: TORX® socket screws

Design: Round, zinc-phosphated, durable plastic sleeve. The contrasting inscriptions on the colour-coded sleeves mean that it is easy to recognise the correct sizes and this makes it simpler to find the right tool.

Tip: Holding function for TORX® screws made according to Acument Intellectual Properties specifications, BlackLaser surface, durable plastic sleeve. The contrasting inscriptions on the colour-coded sleeves mean that it is easy to recognise the correct sizes and this makes it simpler to find the right tool.

05024179001	967 SL TORX® HF	1x TX 8x76; 1x TX 9x79; 1x TX 10x85; 1x TX 15x90; 1x TX 20x96; 1x TX 25x104; 1x TX 27x112; 1x TX 30x122; 1x TX 40x132
-------------	-----------------	---

950/9 Hex-Plus 6 SB



9-piece set in a two-component clip

Application: Hexagon socket screws

Design: BlackLaser surface

Tip: Hex-Plus, ball-end hexagon on long arm

05073596001	950 PKL BM	1x 1.5x90 ¹⁾ ; 1x 2.0x100; 1x 2.5x112; 1x 3.0x126; 1x 4.0x140; 1x 5.0x160; 1x 6.0x180; 1x 8.0x200; 1x 10.0x219
-------------	------------	---

¹⁾ Regular hexagon

967/9 TX XL Multicolour HF 1 L-key set with holding function, long



9-piece set in a two-component clip

Application: TORX® socket screws

Design: Zinc-phosphated, durable plastic sleeve. The contrasting inscriptions on the colour-coded sleeves mean that it is easy to recognise the correct sizes and this makes it simpler to find the right tool.

Tip: Holding function for TORX® screws made according to Acument Intellectual Properties specifications

05024470001	967 SXL TORX® HF Multicolour	1x TX 8x90; 1x TX 9x101; 1x TX 10x112; 1x TX 15x123; 1x TX 20x137; 1x TX 25x154; 1x TX 27x172; 1x TX 30x195; 1x TX 40x224
-------------	------------------------------	---

3967/9 TX SXL Multicolour HF Stainless 1 L-key set with holding function, stainless



9-piece set in a two-component clip

Application: TORX® socket screws

Design: Stainless steel, round

Tip: TORX® on short arm, holding function for TORX® screws made according to Acument Intellectual Properties specifications on long arm, durable plastic sleeve. The contrasting inscriptions on the colour-coded sleeves mean that it is easy to recognise the correct sizes and this makes it simpler to find the right tool.

05022689001	3967 SXL HF TORX® Multicolour	1x TX 8x90; 1x TX 9x101; 1x TX 10x112; 1x TX 15x123; 1x TX 20x137; 1x TX 25x154; 1x TX 27x172; 1x TX 30x195; 1x TX 40x224
-------------	-------------------------------	---



"Take it easy" tool finder system



"Take it easy" tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).



Ball tip



The spherical drive profile means that it is possible to swivel the axis of the tool to that of the screw, and therefore enable angled, "around-the-corner" screwdriving jobs.



With retaining function on long arm



The clamping of the screw is achieved by a flexible locking ball. The holding function is especially helpful in confined, hard-to-reach spaces, where there is no room for a second hand to sec

Secure hold and easy removal



The wear-resistant clip material ensures that the L-keys are securely held yet are easy to remove.

Kraftform Micro Big Pack 1 Screwdriver set for electronic applications



Take it easy tool finder: colour coding according to profile and size stamp.

Application: Slotted screws, Phillips-head, Phillips-Recess, TORX® Internal Transducers (TX 5, TX 6, TX 7, TX 8, TX 10 with holding function), Internal TORX PLUS® IPR, internal and external hex and Microstix® screws, 1 chip lifter to remove stuck components on circuit boards after soldering

Design: 25 pieces; in roll bag; suitable for Wera 2go

Part No.	Description
05134000001	
+	2050 PH Micro 1x PH 000x40 ¹⁾ 2); 1x PH 00x40 ¹⁾ 2); 1x PH 0x40 ³⁾
+	2067 TORX® 1x TX 5x40; 1x TX 6x40
+	2067 TORX® HF 1x TX 5x40; 1x TX 6x40; 1x TX 7x60; 1x TX 8x60; 1x TX 10x60
+	2067 TORX PLUS® IPR Micro 1x 1 IPRx40
○	2054 Micro 1x 0,9x40; 1x 1,3x40; 1x 1,5x60; 1x 2x60
○	2035 Micro 1x 0,23x1,5x40; 1x 0,30x1,8x60; 1x 0,35x2,5x40; 1x 0,40x2,0x60; 1x 0,40x2,5x80; 1x 0,50x3,0x80
●	2069 Micro 1x 4,0x60; 1x 5,5x60
▲	2072 1x mx40
●	1429 1x 1,0x3,5x50
	K240 1x 50,0x240,0

¹⁾ Optimised for Asian PH screws



²⁾ On the output side, the blade is turned to a nominal length of 10 mm.

³⁾ Size 0 modified according to JCIS 0 (Japanese Camera Industrial Standard)

NEW
Display Kraftform Micro 1



Kraftform Micro 12 Universal 1 Screwdriver set for electronic applications



Take it easy tool finder: colour coding according to profile and size stamp.

Application: Slotted and Phillips screws, TORX® socket screws, and Hexagon socket screws

Content: 12-piece set, in a belt pouch


Part No.	Description
05073675001	
+	2050 PH Micro 1x PH 00x60 ¹⁾ ; 1x PH 0x60 ²⁾
+	2067 TORX® HF 1x TX 5x40; 1x TX 6x40
○	2035 Micro 1x 0,23x1,5x40; 1x 0,30x1,8x60; 1x 0,40x2,0x60; 1x 0,50x3,0x80
○	2054 Micro 1x 0,9x40; 1x 1,5x60; 1x 2x60

¹⁾ Optimised for Asian PH screws

²⁾ Size 0 modified according to JCIS 0 (Japanese Camera Industrial Standard)



“Take it easy” Tool Finder



Screwdrivers with “Take it easy” tool finder: colour coding according to profile and size stamp.




The refined screwdriver for electronics technicians



The Kraftform Micro, with its three zones and their specific arrangement, satisfies these requirements perfectly. The free-turning cap that provides support for the hand works with these advantages, enabling quick and easy precision work.



The precision zone



The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.




The power zone



The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.



395 H0/3 Sanitary Nutdriver set



Application: Hexagon headed bolts, screws and nuts

Content: 3-piece set in display carton

TIP: The hollow shaft enables seized screws or those on long threads to be tightened and loosened

05134275001	
●	395 H0 1x 10,0x90; 1x 13,0x90; 1x 7/16"x90



Hollow shaft nutsetter



A screwdriver with a hollow shaft is needed whenever there are screwdriving jobs involving threaded rods i.e. the threaded rod through the nut can slip into the hollow shaft of the screwdriver.

With hollow shaft



The 395 H0 screwdrivers have a hollow shaft that can accommodate protruding threaded rods. This is particularly useful when installing/removing mixer taps on washbasins.



"Take it easy" Tool Finder




Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

Reduced contact pressure



Wera Lasertip reduces the contact pressure required and enhances force transfer – meaning less screwdriving effort is required. Screwdriving becomes safer and easier.

Kraftform Big Pack 300



Kraftform Plus – Series 300. With Lasertip blade and rack. Take it easy tool finder: colour coding according to profile and size stamp.

Application: Slotted, cross, Phillips-Recess, Pozidriv and TORX® screws

Content: 14-piece set in display carton

05105630001	
+	350 PH 1x PH 1x80; 1x PH 2x100; 1x PH 3x150
+	355 PZ 1x PZ 1x80; 1x PZ 2x100; 1x PZ 3x150
+	367 TORX® 1x TX 10x80; 1x TX 15x80; 1x TX 20x100; 1x TX 25x100; 1x TX 30x115
+	334 1x 1,2x6,5x150
+	335 1x 0,6x3,5x100; 1x 0,8x4,0x100
	Rack 2x 190,0x50,0

334/6 Rack screwdriver set Kraftform Plus Lasertip and rack



Lasertip round blades and rack. Take it easy tool finder: colour coding according to profile and size stamp.

Application: Slotted and Phillips screws

Content: 6-piece set and rack in display carton

05105650001	
+	350 PH 1x PH 1x80; 1x PH 2x100
+	334 1x 1,2x6,5x150
+	335 1x 0,5x3,0x80 ¹⁾ ; 1x 0,8x4,0x100; 1x 1,0x5,5x125

¹⁾without Lasertip

334/355/6 Rack screwdriver set Kraftform Plus Lasertip and rack



Lasertip round blades and rack. Take it easy tool finder: colour coding according to profile and size stamp.


Application: Slotted and Pozidriv screws

Content: 6-piece set and rack in display carton

05105656001	
+	355 PZ 1x PZ 1x80; 1x PZ 2x100
+	334 1x 1,2x6,5x150
+	335 1x 0,5x3,0x80 ¹⁾ ; 1x 0,8x4,0x100; 1x 1,0x5,5x125

¹⁾without Lasertip

Kraftform Big Pack 100 VDE



Kraftform: The safety screwdriver with Lasertip blade, voltage tester and rack. Take it easy tool finder: colour coding according to profile and size stamp.

Application: Slotted, Phillips, PlusMinus (Pozi driv/slotted), Pozi driv and TORX® screws

Content: 14-piece set in display carton

05105631001	
+	162 i PH VDE 1x PH 1x80; 1x PH 2x100
+	165 i PZ VDE 1x PZ 1x80; 1x PZ 2x100
+	165 i PZ/S VDE 1x # 1x80; 1x # 2x100
+	167 i TORX® VDE 1x TX 10x80; 1x TX 15x80; 1x TX 20x80
-	160 iS 1x 0,6x3,5x100
-	160 i VDE 1x 0,4x2,5x80 ¹⁾ ; 1x 0,8x4,0x100; 1x 1,0x5,5x125
-	247 1x 0,5x3,0x70
	Rack 2x 190,0x50,0

¹⁾ without Lasertip
²⁾ Product not available in the USA and Canada.

160 i/7 Rack screwdriver set Kraftform Plus Series 100, voltage tester and rack



Kraftform: The safety screwdriver with Lasertip blade, voltage tester and rack. Take it easy tool finder: colour coding according to profile and size stamp.

Application: Slotted and Phillips screws

Content: 7-piece set and rack in display carton

05006147001	
+	162 i PH VDE 1x PH 1x80; 1x PH 2x100
-	160 i VDE 1x 0,4x2,5x80 ¹⁾ ; 1x 0,6x3,5x100; 1x 0,8x4,0x100; 1x 1,0x5,5x125
-	247 1x 0,5x3,0x70

¹⁾ without Lasertip
²⁾ Product not available in the USA and Canada.

160 i/165 i/7 Rack screwdriver set Kraftform Plus Series 100, voltage tester and rack



Kraftform: The safety screwdriver with Lasertip blade, voltage tester and rack. Take it easy tool finder: colour coding according to profile and size stamp.

Application: Slotted and Pozi driv screws

Content: 7-piece set and rack in display carton

05006148001	
+	165 i PZ VDE 1x PZ 1x80; 1x PZ 2x100
-	160 i VDE 1x 0,4x2,5x80 ¹⁾ ; 1x 0,6x3,5x100; 1x 0,8x4,0x100; 1x 1,0x5,5x125
-	247 1x 0,5x3,0x70

¹⁾ without Lasertip
²⁾ Product not available in the USA and Canada.

Big Pack 900 Screwdriver set Kraftform Wera: Chiseldriver and rack



Application: Slotted, Phillips, Pozi driv and TORX® socket screws

Content: 13-piece set

05133285001	
+	917 SPH 1x PH 1x80; 1x PH 2x100; 1x PH 3x150
+	918 SPZ 1x PZ 1x80; 1x PZ 2x100; 1x PZ 3x150
-	932 A 1x 0,6x3,5x80 ¹⁾ ; 1x 0,8x4,5x90; 1x 1,0x5,5x100; 1x 1,2x7,0x125; 1x 1,6x9,0x150
+	977 TORX® 1x TX 20x90; 1x TX 25x100
	Rack 2x 190,0x50,0

¹⁾No throughout blade, no impact cap and no hexagon bolster

932/6 Screwdriver set Kraftform Wera: Chiseldriver and rack



Application: Slotted and Phillips screws

Content: 6-piece set and rack in display carton

05018282001	
+	917 SPH 1x PH 1x80; 1x PH 2x100
-	932 A 1x 0,6x3,5x80 ¹⁾ ; 1x 0,8x4,5x90; 1x 1,0x5,5x100; 1x 1,2x7,0x125

¹⁾No throughout blade, no impact cap and no hexagon bolster

932/918/6 Screwdriver set Kraftform Wera: Chiseldriver and rack



Application: Slotted and Pozi driv screws

Content: 6-piece set and rack in display carton

05018287001	
+	918 SPZ 1x PZ 1x80; 1x PZ 2x100
-	932 A 1x 0,6x3,5x80 ¹⁾ ; 1x 0,8x4,5x90; 1x 1,0x5,5x100; 1x 1,2x7,0x125

¹⁾No throughout blade, no impact cap and no hexagon bolster



Individually tested



Each Kraftform Kompakt VDE set has been tested individually at 10,000 volts, in accordance with IEC 60900. This ten-times-higher testing load guarantees safe working at their maximum permitted load of 1,000 volts.



Integrated impact cap



An integrated impact cap lengthens the service life and reduces the danger of splintering. Nevertheless, always wear protective goggles.



Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal

Phone: +49 (0)202 / 4045-0
Fax: +49 (0)202 / 4045 276
E-Mail: info@wera.de
www.wera.de

No liability for printing errors or mistakes
shall be assumed.

Wera Tools (UK) LTD.
Railway View
Clay Cross
Chesterfield
Derbyshire, S45 9FR

Phone: +44 (0)1246 / 277756
Fax: +44 (0)1246 / 273335
eMail: queries@wera-tools.co.uk
Internet: www.wera-tools.co.uk



EN 05 500802 020 - 0053701 - 01