

## CUBE20/67 INTERFACE

Cube20/67 system connection

For connection cables please see chapter "Connection Technology"

### [Link to Product](#)

#### Illustration



Product may differ from Image

#### Approvals



#### Internal communication

Current consumption max. 25 mA

#### Cube67 System supply

Cube67 system connection max. 10 m

I/O capacity modular Cube20/67 fieldbus station: Cube20 bus node + 15 Cube20/67 modules

Sensor supply US 24 V DC (18...30.2 V DC) EN 61131-2, max. 4 A

Actuator supply UA 24 V DC (18...30.2 V DC) EN 61131-2, max. 4 A

#### Connections

Fieldbus M12 (female) 6-pole

Sensor-system/actuator supply 4 × Spring clamp terminals, max. 2.5 mm<sup>2</sup> (max. 12 A)

I/O ports 8 × Spring clamp plug-in terminals, max. 2.5 mm<sup>2</sup>

**General data**

Protection	IP20
Mounting method	DIN-rail mountable (EN 60715)
Temperature range	0...+55 °C (storage temperature -20...+85 °C)
Dimensions H × W × D	117×56×47 mm

**Diagnostic**

Communication status	via LED
----------------------	---------

**Commercial data**

country of origin	DE
customs tariff number	85176200
minimum order quantity	1